

943-T4Y-2D-001-130E

([Home](#) : [Products](#) : [Sensors](#) : [Position Sensors](#) : [Ultrasonic Sensors](#) : [943](#))



Series 943, software programmable, 300 mm to 3500 mm [11.8 in to 137.7 in] scan distance, M30 plastic housing, switching 2 x PNP, 2 m [78.74]

Actual product
appearance may vary.

Product Specifications

Sensing Range	300 mm to 3500 mm [11.8 in to 137.7 in]
Range Type	Long range > 2,0 m [80.0 in] and up
Min. Sensing Distance of Test Target	300 mm [11.81]
Supply Voltage	12 Vdc to 30 Vdc
Beam Angle	8°
Oscillating Frequency	130 KHz
Integrated Temperature Compensation	Yes
Repeatability	0.2 %/2 mm
Output Type	Sw itching 2 x PNP
Sw itching Output Type	2 Outputs - Configure for Normally Open/Normally Closed
Max. Sw itching Frequency	1 Hz
Adjustment Method	Teach-in
Analog Output Slope Selection	Teach-in
Operating Temperature	-15 °C to 70 °C [5 °F to 158 °F]
Storage Temperature	-25 °C to 70 °C [-13 °F to 158 °F]
Maximum Output Current	500 mA
Hysteresis	0.01
Indicators	3 LED
Memory	EEPROM (non-volatile)
Current Consumption	< 80 mA
Circuit Protection	Reverse Polarity, voltage spikes on supply and output lines, short circuit on sw itching output
Housing Style	M30 plastic
Housing Material	Polyethyleneterephthalat
Sealing	IP67
Mounting	2 x M30 plastic nuts 36 mm
Sensing Face Material	Epoxy
Termination Type	Pre-w ired 2 m [78.74]
Availability	Global

Product Specifications

Normally Open/Normally Closed selection	Teach-in
UNSPSC Code	41111960
UNSPSC Commodity	41111960 Ultrasonic sensor
Series Name	943

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[943-T4Y-2D-001-130E](#)