

943-F4Y-2D-001-300E

([Home](#) : [Products](#) : [Sensors](#) : [Position Sensors](#) : [Ultrasonic Sensors](#) : [943](#))



Series 943, software programmable, 100 mm to 800 mm [3.9 in to 31.4 in.] scan distance, M18 plastic housing, switching 2 x PNP, 2 m [78.74]

Actual product appearance may vary.

Product Specifications

Sensing Range	100 mm to 800 mm [3.9 in to 31.4 in.]
Range Type	Short range < 1,0 m [39.0 in]
Min. Sensing Distance of Test Target	100 mm [3.94]
Supply Voltage	12 Vdc to 30 Vdc
Beam Angle	8°
Oscillating Frequency	300 KHz
Integrated Temperature Compensation	Yes
Repeatability	0.2 %/1 mm
Output Type	Sw itching 2 x PNP
Sw itching Output Type	2 Outputs - Configure for Normally Open/Normally Closed
Max. Sw itching Frequency	4.7 Hz
Adjustment Method	Teach-in
Analog Output Slope Selection	Teach-in
Operating Temperature	-15 °C to 70 °C [5 °F to 158 °F]
Storage Temperature	-25 °C to 70 °C [-13 °F to 158 °F]
Maximum Output Current	500 mA
Hysteresis	0.01
Indicators	3 LED
Memory	EEPROM (non-volatile)
Current Consumption	< 80 mA
Circuit Protection	Reverse Polarity, voltage spikes on supply and output lines, short circuit on sw itching output
Housing Style	M18 plastic
Housing Material	Polyethyleneterephthalat
Sealing	IP67
Mounting	2 x M18 plastic nuts 24 mm
Sensing Face Material	Epoxy
Termination Type	Pre-w ired 2 m [78.74]
Availability	Global

Product Specifications

Normally Open/Normally Closed selection	Teach-in
UNSPSC Code	41111960
UNSPSC Commodity	41111960 Ultrasonic sensor
Series Name	943

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[943-F4Y-2D-001-300E](#)