



.187 CENTERS SH-5 and SHE-5



PROBE SPECIFICATIONS

Minimum Centers: .187 (4.75)

Current Rating:

SHE-5: 23 amps continuous

SH-5: 39 amps continuous

(Individual probe in free air @ ambient temperature)

Spring Force: 18.7 oz. @ .170 (4.32) travel

Maximum Travel: .250 (6.35)

Working Travel: .170 (4.32)

Rated Force oz. (g)	Preload oz. (g)
18.7 (531)	7.2 (204)

MATERIALS

Barrel: High performance copper alloy, gold plated


Spring: Stainless steel

Plunger: Beryllium copper, gold plated


Ball: SH probe: Stainless steel

Receptacle: Copper alloy, gold plated


SHE-5 PLUNGER TIPS



SH-5 PLUNGER TIPS



.187 CENTER HIGH CURRENT PROBES



IDL current ratings are defined as the maximum current at which the temperature rise of the probe does not exceed 144°F (80°C) for a single probe in free air at ambient temperature for one hour.

RECEPTACLE OPTIONS

Part Number	Style	Receptacle Length	Probe/Receptacle Combined Length	Comments
RH-5-SC	Solder Cup	1.295 (32.89)	1.620 (41.15)	—

HOW TO ORDER: SPRING CONTACT PROBE

SHE **5** **A** **18.7** **G**

SERIES SIZE TIP STYLE SPRING FORCE PLATING OPTIONS

SERIES:
SHE: 23 AMPS
SH: 39 AMPS

RECEPTACLE

RH **5** **SC**

SERIES SIZE TERMINATION

TERMINATIONS:
SC: SOLDER CUP

VIEW UPDATES OF THIS INFORMATION AT WWW.IDINET.COM

Specifications subject to change without notice. Dimensions in inches (millimeters)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Smiths Interconnect:](#)

[SHE-5-A-18.7-G](#) [SHE-5-B-18.7-G](#) [SHE-5-B-18.7-G-N/L](#) [101056-017-926](#) [101056-014-926](#) [101043-013](#) [101057-003-952](#) [101056-012-926](#) [101057-002-952](#)