# smiths interconnect

# 0.075" Centers

Standard Spring Probes

**Board Test Fixture Probes & Receptacles** 



# Board Test Spring Probes

Smiths Interconnect offers a wide range of spring contact probes to meet your testing requirements and has long been recognized as the world's largest probe manufacturer. With over 60 different probe series that includes our standard Board Test Fixture Probes as well as our Specialty Test Probes, we provide a full portfolio designed for general purpose test on bare boards, loaded printed circuit boards, surface mount assemblies and other forms of test.

#### **MICRO SERIES PROBES**

The Micro probe series range in pitch from 0.20" (0.51 mm) to 0.030" (0.76 mm) pitch and are typically between half an inch to an inch in length.

#### STANDARD PROBES

Our standard probes range in pitch from 0.039" (1.00 mm) to 0.187" (4.75 mm). Within most series, there are multiple length and travel options, including more aggressive probes dimensionally equivalent to the standard probes.

#### **DOUBLE-ENDED PROBES & RECEPTACLES**

Double-ended probes feature both a top-side and bottomside compliant plunger. Double-ended receptacles are available with a permanent bottom-side plunger and a replaceable probe on the top side. They are also available with both a top and bottom-side replaceable probe.

#### **LEAD FREE PROBES**

The Lead Free probe series is based on our ICT Probe Series. The plunger material, plating and tip geometry have been optimized to provide less wear and contamination build-up while using a moderate spring force of 7 to 8 ounces.

#### **ICT PROBES**

The ICT probe design features a bifurcated barrel with four separate fingers. The barrel is compliant and formed against the plunger, thus eliminating any gap between the plunger and barrel. ICT probes are more accurate and stable in resistance than standard designs.

#### **ROTATOR PROBES**

Ideal for non-clean and lead-free applications, this aggressive probe rotates 90° at the rated travel, virtually drilling through contaminants with a low spring force.

#### HIGH CURRENT PROBES

We offer two different high current probe designs in four different pitches. The SH series features a bias ball, which is the most aggressive biasing technique to aid in assuring a low and consistent resistance, cycle after cycle. The SHE Series features a bias spring, an effective biasing technique for many applications.

#### **SWITCH PROBES**

A Switch Probe is a spring contact probe and receptacle that has two individual current paths. One current path is closed, the other is open and after a designated travel the second current path closes.

#### THERMOCOUPLE PROBES

The Thermocouple Probe is an ungrounded, thermally conductive probe used for the measurement of variations in temperature. We offer two Thermocouple Probes: Type T for up to 220°F, and Type K for up to 350°F.


#### **COAXIAL PROBES**

Our Coax Probes provide a low noise, controlled impedance signal path with reliable, easy connect/disconnect options. Our designs include a spring-loaded signal probe and a spring-loaded shielding plunger for the ground.

# S-1 Series

# 0.075 (1.91) Centers

For R-1 Series Receptacles see pg. 9



BeCu Tips	Diameter
90°	0.060 (1.52)
30°	0.026 → (0.66)
C	0.026 → (0.66)
D	0.040 → ← (1.02)
90°	0.060 (1.52)
F	0.060 → ← (1.52)
H	0.060 → ← (1.52)
	0.026 → ← (0.66)
45°	0.060 → ← (1.52)
60°	0.026 → (0.66)

#### **Probe Specifications**

Minimum Centers	0.075 (1.91)
Current Rating	Up to 3 Amps
Spring Force	2.00 oz (57 g), 3.80 oz (108 g), or 6.60 oz (187 g) @ 0.070 (1.78) travel
Preload Force	0.80 oz (23 g) (2.00 oz spring/stainless steel) 1.50 oz (43 g) (3.80 oz spring/stainless steel) 2.00 oz (57 g) (6.60 oz spring/music wire)
Typical Resistance	< 25 mΩ
Maximum Travel	0.100 (2.54)
Working Travel	0.070 (1.78)

#### **Materials**


Barrel	Nickel/silver, gold plated	
Spring	Stainless steel, or music wire, gold plated	
Plunger	Beryllium copper, gold plated over nickel, or Duralloy $^{\text{\tiny{TM}}}$	

S - 1 - A - 3.8 - G 1 2 3 4 5		
1 5	Series	S S X (1)
2 5	Size	1
3 T	Γiρ Style	A, B, C, D, E, F, H, J, K, U
4 5	Spring Force	2 oz 3.8 oz 6.6 oz
5 F	Plunger Plating	G Gold D Duralloy™

# SS-75 Series

# 0.075 (1.91) Centers

For R-1 Series Receptacles see pg. 9



# **BeCu Tips** Diameter 0.060 (1.52)0.026 (0.66)0.026 (0.66)0.040 (1.02)0.060 (1.52)0.060 (1.52)0.060 (1.52)0.026 (0.66)0.060 (1.52)0.026 (0.66)

#### **Probe Specifications**

Minimum Centers	0.075 (1.91)
Current Rating	Up to 3 Amps
Spring Force	2.40 oz (68 g) or 4.90 oz (139 g) @ 0.050 (1.27) travel
Preload Force	1.70 oz (48 g) (2.40 oz spring/stainless steel) 3.10 oz (88 g) (4.90 oz spring/stainless steel)
Typical Resistance	< 25 mΩ
Maximum Travel	0.050 (1.27)
Working Travel	0.050 (1.27)

#### **Materials**

Barrel	Nickel/silver, gold plated
Spring	Stainless steel, gold plated
Plunger	Beryllium copper, gold plated over nickel or Duralloy™


S S - 7 5 - A - 2.4 - G 1 2 3 4 5		
1 Series	S S S S X (1)	
2 Size	7 5	
3 Tip Style	A, B, C, D, E, F, H, J, K, U	
4 Spring Force	2. 4 oz 4. 9 oz	
5 Plunger Plating	<b>G</b> Gold <b>D</b> Duralloy™	

# ICT-075 & S-075 Series

# 0.075 (1.91) Centers

For R-075 Series Receptacles see pg. 10 For R-075-J-DE Wireless Series Receptacles see pg. 11

#### S-075 ICT-075



#### BeCu Tips Diameter

Dece Tips	Diomicco
90°	0.048 → ←
30°	0.025 → ← (0.64)
H	0.048 → ← (1.22)
HS	0.025 → ← (0.64)
	0.025 → ← (0.64)
60°	0.048 → ← (1.22)
60°	0.025 →
V8	0.048 → (1.22) 8 Pts.
	Diameter

# Steel Tips Diameter

Steel Tips	Didilietei
30°	0.025 (0.64)
NT	0.048 → (1.22)
60° S	0.025 → (0.64) ←
SP	0.025 → ← (0.64)
60°	0.025 → (0.64)

#### **Probe Specifications**

Minimum Centers	0.075 (1.91)
Current Rating	Up to 3 Amps
Spring Force	3.00 <sup>(1)</sup> oz (85 g), 5.00 oz (142 g), 7.00 oz (198 g), or 10.00 oz (283 g) @ 0.170 (4.32) travel
Preload Force	1.20 oz (34 g) (3.00 <sup>(1)</sup> oz spring) 2.00 oz (57 g) (5.00 oz spring) 2.90 oz (82 g) (7.00 oz spring) 3.30 oz (94 g) (10.00 oz spring)
Typical Resistance	< 25 mΩ
Maximum Travel	0.250 (6.35)
Working Travel	0.170 (4.32)

#### **Materials**


Barrel	ICT Series: Gold lined S Series: Gold plated I.D. and O.D.
Spring	Music wire, nickel plated
Plunger	Beryllium copper, or steel, gold plated over nickel

	1 C T - 0 7 5 1 2	3 4 5 6
1	Series	I C T (2) S
2	Size	0 7 5
3	Tip Style	A, B, H, HS, J, NT, S, SP, T, U, V8
4	Spring Force	3 oz <sup>(1)</sup> 5 oz 7 oz 1 0 oz
5	Plunger Plating	G Gold
6	Steel Plunger Option	S Steel

# Lead Free ICT-075 Series

#### 0.075 (1.91) Centers

For R-075 Series Receptacles see pg. 10 For R-075-J-DE Wireless Series Receptacles see pg. 11



# 90° 0.025 (0.64) 0.025

#### **Probe Specifications**

Minimum Centers	0.075 (1.91)
Current Rating	Up to 3 Amps
Spring Force	7.00 oz (198 g) @ 0.170 (4.32) travel
Typical Resistance	< 40 m $\Omega$ (against lead free surface)
Maximum Travel	0.250 (6.35)
Working Travel	0.170 (4.32)

#### **Materials**


Barrel	G2
Spring	Music wire, nickel plated
Plunger	Steel, Duralloy™ plated



# S-075 Rotator Series

# 0.075 (1.91) Centers

For R-075 Series Receptacles see pg. 10



# 

#### **Probe Specifications**

Minimum Centers	0.075 (1.91)
Current Rating	Up to 3 Amps
Spring Force	3.80 oz (108 g) or 6.60 oz (187 g) @ 0.170 (4.32) travel
Preload Force	0.50 oz (14 g) (3.80 oz spring) 1.60 oz (45 g) (6.60 oz spring)
Typical Resistance	< 25 mΩ
Maximum Travel	0.225 (5.72)
Working Travel	0.170 (4.32)
Rotation	90° @ 0.170 (4.32) travel

#### **Materials**


Barrel	G2		
Spring	Music wire, gold plated		
Plunger	Beryllium copper, Duralloy™ plated		

	S - 075 - L	M - 3. 8 - R T
	1 2	3 4 5
1	Series	S
2	Size	0 7 5
3	Tip Style	LM, S
4	Spring Force	3.8 oz 6.6 oz
5	Rotator	RT

# **ICT-L075 Series**

# 0.075 (1.91) Centers

For R-075 Series Receptacles see pg. 10 For R-075-J-DE Wireless Series Receptacles see pg. 11



0.040 (1.02)

### **Probe Specifications**

Minimum Centers	0.075 (1.91)
Current Rating	Up to 3 Amps
Spring Force	4.30 oz (122 g) @ 0.317 (8.05) travel
Preload Force	1.80 oz (51 g)
Typical Resistance	< 15 mΩ
Maximum Travel	0.400 (10.16)
Working Travel	0.317 (8.05)

#### **Materials**

Barrel	G2
Spring	Music wire, gold plated
Plunger	Beryllium copper, or steel, gold plated over nickel


I C T - L 0 7 5 -	· H - 4. 3 - G - S
1 2	3 4 5 6
1 Series	ICT
2 Size	L 0 7 5
3 Tip Style	HJSP
4 Spring Force	4. 3 oz
5 Plunger Plating	G Gold
6 Steel Plunger Option	S Steel

# **R-1 Series**

# 0.075 (1.91) Centers

For S-1 Series Probes see pg. 3 For SS-75 Series Probes see pg. 4

Part Number	Style/Termination	Receptacle or Terminal Length	Probe/Receptacle Combined Length		Notes
			S-1	SS- <b>7</b> 5	
R-1-CR	Crimp	0.695 (17.65)	0.875 (22.23)	0.825 (20.96)	_
R-1-SC	Solder Cup	0.695 (17.65)	0.875 (22.23)	0.825 (20.96)	_
R-1-RP	Round Post	1.070 (27.18)	1.250 (31.75)	1.200 (30.48)	0.375 post length – 0.025 dia.
R-1-WW-429	Wire Wrap	1.124 (28.55)	1.304 (33.12)	1.254 (31.85)	0.429 post length – 0.025 dia.



#### **Probe Specifications**


Minimum Centers	0.075 (1.91)	
Drill Size	1.45 mm	
Mounting Hole Size	0.055/0.057 (1.40/1.45)	
Recommended Wire	24-28 gage	
Materials	Nickel/silver, gold plated, gold plated post	
Tools		
Crimping Pliers	CP-1 (for 24-28 gage solid conductor)	
Insertion Tool	RT-1	
How to Order		
R	- 1 - WW - 4 2 9	
1	2 3	
1 Series	R	
2 Size	1	
2 Size	C R Crimp S C Solder Cup	
2 Size  3 Termination	C R Crimp S C Solder Cup  R P Round Post	

# R-075 Series

# 0.075 (1.91) Centers

For ICT-075/S-075 Series Probes see pg. 5 For S-075 Rotator Series Probes see pg. 7 For ICT-075 Lead Free Series Probes see pg. 6 For ICT-L075 Series Probes see pg. 8

Part Number Style/Termination	_Receptacle or	Probe/Receptacle Combined Length		Notes	
			ICT-075/S-075	ICT-L075	
R-075-CR	Crimp	1.170 (29.72)	1.500 (38.10)	1.650 (41.91)	_
R-075-SC	Solder Cup	1.170 (29.72)	1.500 (38.10)	1.650 (41.91)	_
R-075-RP	Round Post	1.545 (39.24)	1.875 (47.63)	2.025 (51.44)	0.375 post length – 0.025 dia.
R-075-WW-429	Wire Wrap	1.599 (40.61)	1.929 (49.00)	2.079 (52.81)	0.429 post length – 0.025 dia.




#### **Probe Specifications**

Minimum Centers	0.075 (1.91)		
Drill Size	1.45 mm		
Mounting Hole Size	0.055/0.057 (1.40/1.45)		
Recommended Wire	24-28 gage		
Materials	Nickel/silver, gold plated, gold plated post		
Tools			
Crimping Pliers	CP-1 (for 24-28 gage solid conductor)		
Insertion Tool	RT-1		
How to Order			
R -	0 7 5 - WW - 4 2 9		
1	2 3		
1 Series	R		
2 Size	0 7 5		
	C R Crimp S C Solder Cup		
3 Termination	R P Round Post		
	WW - 4 2 9 Wire wrap 0.429 post length		

# R-075-J-DE Series

#### 0.075 (1.91) Centers | Wireless Receptacle

For ICT-075/S-075 Series Probes see pg. 5 For ICT-L075 Series Probes see pg. 8 For ICT-075 Lead Free Series Probes see pg. 6



# BeCu Tips Diameter 0.020 → ← (0.51) ← 0.020 → ←

#### **Probe Specifications**

	Minimum Centers	0.075 (1.91)
	Drill Size	1.45 mm
	Mounting Hole Size	0.055/0.057 (1.40/1.45)
	Spring Force	2.70 oz (77 g) @ 0.070 (1.77) trəvel
	Maximum Travel	0.100 (2.54)
	Working Travel	0.070 (1.77)

#### **Materials**

Receptacle	Nickel/silver, gold lined inside
Spring	Music wire, gold plated
Plunger	Beryllium copper, gold plated over nickel

#### **TOOLS**

Insertion Tool	RT-1	
How to Order	How to Order	
R - 075 - J - DE 1 2 3 4		
1 Series	R	
2 Size	0 7 5	
1 Tip Style	J	
2 Termination	D E Double Ended	

# Global Support



# **Americas**

- Kansas City, KS +1 913 342 5544 info.us@smithsinterconnect.com
- Tampa, FL + 1 813 901 7200 info.tampa@smithsinterconnectinc.com
- Milpitas, CA +1 408 957 9607 x-1125 info.us@smithsinterconnect.com
- Kirkland, QC, Canada +1 514 842 5179 info.us@smithsinterconnect.com
- Salisbury, MD +1 800 780 2169 info.us@smithsinterconnect.com

# Europe

- Deggendorf, Germany +49 991 250 120 info.de@smithsinterconnect.com
- Rouen, France +33 2 3296 9176 info.fr@smithsinterconnect.com
- Dundee, UK +44 1382 427 200 info.dundee@smithsinterconnect.com
- Genova, Italy +39 0 10 60361 info.it@smithsinterconnect.com

# **Asia**

- Bangalore, India +91 080 4241 0529 info.in@smithsinterconnect.com
- Singapore +65 6846 1655 info.asia@smithsinterconnect.com
- Mianyang, China +86 816 231 5566 HSICSR@hf-smiths.com
- Suzhou, China +86 512 6273 1188 info.asia@smithsinterconnect.com
- Shanghai, China +86 21 2283 8008 info.asia@smithsinterconnect.com



# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### **Smiths Interconnect:**

R-075-RP S-075-VLT-7-G-S S-075-J-7-G S-075-SP-5-G-S S-075-B-7-G S-075-VT-7-G-S S-075-SP-7-G-S S-075-J-5-G S-075-UST-5-G-S S-075-W-7-G-S S-075-M-7-G-S S-075-M-7-G-S S-075-M-7-G-S S-075-M-7-G-S S-075-M-7-G-S S-075-M-7-G-S S-075-M-7-G-S S-075-M-7-G-S S-075-B-5-G-S S-075-B-7-G-S S-075-S-7-G-S S-075-S-7-G-S S-075-S-7-G-S S-075-M-7-G-S S-075-H-7-G S-075-T-7-G S-075-T-7-G S-075-T-7-G-S S-075-W-7-G-S S-075-W-7-G-