


2nd generation thinQ!™ SiC Schottky Diode

Features:

- Revolutionary Semiconductor Material - Silicon Carbide
- Switching Behaviour Benchmark
- No Reverse Recovery / No Forward Recovery
- Temperature Independent Switching Behaviour
- Qualified According to JEDEC¹⁾ Based on Target Applications

Applications:

- SMPS, PFC, snubber



Chip Type	V_R	I_{Fn}	Die Size	Package
IDC06S60CE	600V	6A	1.45 x 1.354 mm ²	sawn on foil

Mechanical Parameters

Mechanical Parameters		
Die size	1.45x 1.354	mm ²
Area total	1.96	
Anode pad size	1.213 x 1.117	
Thickness	355	µm
Wafer size	100	mm
Max. possible chips per wafer	3449	
Passivation frontside	Photoimide	
Pad metal	3200 nm AlSiCu	
Backside metal	Ni Ag –system	
Die bond	Electrically conductive epoxy glue and soft solder	
Wire bond	Al, ≤500µm	
Reject ink dot size	Ø 0.65mm; max 1.2mm	
Storage environment ¹⁾	for original and sealed MBB bags	Ambient atmosphere air, Temperature 17°C – 25°C, < 6 month
	for open MBB bags	Acc. to IEC60721-3-3: Atmosphere >99% Nitrogen or inert gas, Humidity <25%RH, Temperature 17°C – 25°C, < 6 month

¹⁾ Designed for storage conditions according to Infineon TR14 (Application Note "Storage of Products Supplied by Infineon Technologies")

Designed for climate condition under operation according to IEC60721-3-3, class 3K3



IDC06S60CE

Maximum Ratings

Parameter	Symbol	Condition	Value	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = 25^{\circ}\text{C}$	600	V
DC blocking voltage	V_{DC}		600	
Continuous forward current, limited by T_{vjmax}	I_F	$T_{vj} < 150^{\circ}\text{C}$	6	A
Surge non repetitive forward current, sine halfwave	$I_{F,SM}$	$T_C = 25^{\circ}\text{C}, t_p = 10\text{ ms}$	49	
		$T_C = 150^{\circ}\text{C}, t_p = 10\text{ ms}$		
Repetitive peak forward current, limited by thermal resistance R_{th}	$I_{F,RM}$	$T_C = 100^{\circ}\text{C}, T_{vj} = 150^{\circ}\text{C}, D = 0.1$	28	
Non-repetitive peak forward current	$I_{F,max}$	$T_C = 25^{\circ}\text{C}, t_p = 10\mu\text{s}$	210	A ² s
i^2t value	$\int i^2 dt$	$T_C = 25^{\circ}\text{C}, t_p = 10\text{ ms}$	12	
		$T_C = 150^{\circ}\text{C}, t_p = 10\text{ ms}$		
Operating junction and storage temperature range	T_{vj}, T_{stg}		-55...+175	$^{\circ}\text{C}$

Static Characteristics (tested on wafer), $T_{vj} = 25^{\circ}\text{C}$

Parameter	Symbol	Conditions	Value			Unit
			min.	Typ.	max.	
Reverse current	I_R	$V_R = 600\text{V}$		0.7	80	μA
Diode forward voltage	V_F	$I_F = 6\text{A}$		1.5	1.7	V

Static Characteristics (not subject to production test - verified by design / characterization)

Parameter	Symbol	Conditions	Value			Unit
			min.	Typ.	max.	
Reverse current	I_R	$V_R = 600\text{V}, T_{vj} = 150^{\circ}\text{C}$		3	800	μA
Diode forward voltage	V_F	$I_F = 6\text{A}, T_{vj} = 150^{\circ}\text{C}$		1.7	2.1	V



IDC06S60CE

Dynamic Characteristics (not subject to production test - verified by design / characterization)

Parameter	Symbol	Conditions		Value			Unit
				min.	Typ.	max.	
Total capacitive charge ³⁾	Q_C	$I_F \leq I_{F,max}$ $di/dt = 200 A/\mu s$ $V_R = 400 V$	$T_{vj} = 150^\circ C$		15		nC
Switching time ²⁾	t_c		$T_{vj} = 150^\circ C$			<10	ns
Total capacitance	C	$f = 1 MHz$	$V_R = 1 V$		280		pF
			$V_R = 300 V$		35		
			$V_R = 600 V$		35		

¹⁾ J-STD20 and JESD22

²⁾ t_c is the time constant for the capacitive displacement current waveform (independent from $T_{vj} = 150^\circ C$, I_{LOAD} and di/dt), different from t_{rr} , which is dependent on $T_{vj} = 150^\circ C$, I_{LOAD} , di/dt . No reverse recovery time constant t_{rr} due to absence of minority carrier inject.


³⁾ Only capacitive charge occurring, guaranteed by design (independent from T_{vj} , I_{LOAD} and di/dt).

Further Electrical Characteristics

Switching characteristics and thermal properties are depending strongly on module design and mounting technology and can therefore not be specified for a bare die.

This chip data sheet refers to the device data sheet	IDT06S60C	Rev. 2.1
--	-----------	----------

Chip Drawing



A: Anode pad



IDC06S60CE

Description

AQL 0,65 for visual inspection according to failure catalogue

Electrostatic Discharge Sensitive Device according to MIL-STD 883

Revision History

Version	Subjects (major changes since last revision)	Date

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2012 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[IDC06S60CE](#)