


## MOSFET

### 650V CoolMOS™ C7 Power Transistor


CoolMOS™ is a revolutionary technology for high voltage power MOSFETs, designed according to the superjunction (SJ) principle and pioneered by Infineon Technologies.

CoolMOS™ C7 series combines the experience of the leading SJ MOSFET supplier with high class innovation. The product portfolio provides all benefits of fast switching superjunction MOSFETs offering better efficiency, reduced gate charge, easy implementation and outstanding reliability.



### Features

- Increased MOSFET dv/dt ruggedness
- Better efficiency due to best in class FOM  $R_{DS(on)} * E_{oss}$  and  $R_{DS(on)} * Q_g$
- **ThinPAK** SMD Package with very low parasitic inductance to enable fast and reliable switching with minimum of size to increase power-density
- Easy to use/drive due to **driver source pin** for better control of the gate.
- Pb-free plating, halogen free mold compound
- Qualified for industrial grade applications according to JEDEC (J-STD20 and JESD22)



### Benefits

- Enabling higher system efficiency by lower switching losses
- Enabling higher frequency / increased power density solutions
- System cost / size savings due to reduced cooling requirements
- Higher system reliability due to lower operating temperatures



### Potential applications

PFC stages and hard switching PWM stages for e.g. Computing, Server, Telecom, UPS and Solar.

*Please note: For MOSFET paralleling the use of ferrite beads on the gate or separate totem poles is generally recommended.*

**Table 1 Key Performance Parameters**

| Parameter            | Value | Unit |
|----------------------|-------|------|
| $V_{DS} @ T_{j,max}$ | 700   | V    |
| $R_{DS(on),max}$     | 230   | mΩ   |
| $Q_{g,typ}$          | 20    | nC   |
| $I_{D,pulse}$        | 41    | A    |
| $E_{oss} @ 400V$     | 2.3   | μJ   |
| Body diode $di_F/dt$ | 55    | A/μs |

| Type / Ordering Code | Package   | Marking | Related Links  |
|----------------------|-----------|---------|----------------|
| IPL65R230C7          | PG-VSON-4 | 65C7230 | see Appendix A |

**Table of Contents**

Description ..... 1

Maximum ratings ..... 3

Thermal characteristics ..... 4

Electrical characteristics ..... 5

Electrical characteristics diagrams ..... 7

Test Circuits ..... 11

Package Outlines ..... 12

Appendix A ..... 13

Revision History ..... 14

Trademarks ..... 14

Disclaimer ..... 14

## 1 Maximum ratings

at  $T_j = 25^\circ\text{C}$ , unless otherwise specified

**Table 2 Maximum ratings**

| Parameter                              | Symbol        | Values |      |         | Unit             | Note / Test Condition                                                  |
|----------------------------------------|---------------|--------|------|---------|------------------|------------------------------------------------------------------------|
|                                        |               | Min.   | Typ. | Max.    |                  |                                                                        |
| Continuous drain current <sup>1)</sup> | $I_D$         | -      | -    | 10<br>7 | A                | $T_C=25^\circ\text{C}$<br>$T_C=100^\circ\text{C}$                      |
| Pulsed drain current <sup>2)</sup>     | $I_{D,pulse}$ | -      | -    | 41      | A                | $T_C=25^\circ\text{C}$                                                 |
| Avalanche energy, single pulse         | $E_{AS}$      | -      | -    | 48      | mJ               | $I_D=4.8\text{A}$ ; $V_{DD}=50\text{V}$                                |
| Avalanche energy, repetitive           | $E_{AR}$      | -      | -    | 0.24    | mJ               | $I_D=4.8\text{A}$ ; $V_{DD}=50\text{V}$                                |
| Avalanche current, single pulse        | $I_{AS}$      | -      | -    | 4.8     | A                | -                                                                      |
| MOSFET dv/dt ruggedness                | dv/dt         | -      | -    | 100     | V/ns             | $V_{DS}=0\dots400\text{V}$                                             |
| Gate source voltage (static)           | $V_{GS}$      | -20    | -    | 20      | V                | static;                                                                |
| Gate source voltage (dynamic)          | $V_{GS}$      | -30    | -    | 30      | V                | AC ( $f>1\text{ Hz}$ )                                                 |
| Power dissipation                      | $P_{tot}$     | -      | -    | 67      | W                | $T_C=25^\circ\text{C}$                                                 |
| Storage temperature                    | $T_{stg}$     | -40    | -    | 150     | $^\circ\text{C}$ | -                                                                      |
| Operating junction temperature         | $T_j$         | -40    | -    | 150     | $^\circ\text{C}$ | -                                                                      |
| Mounting torque                        | -             | -      | -    | n.a.    | Ncm              | -                                                                      |
| Continuous diode forward current       | $I_S$         | -      | -    | 10      | A                | $T_C=25^\circ\text{C}$                                                 |
| Diode pulse current <sup>2)</sup>      | $I_{S,pulse}$ | -      | -    | 41      | A                | $T_C=25^\circ\text{C}$                                                 |
| Reverse diode dv/dt <sup>3)</sup>      | dv/dt         | -      | -    | 1       | V/ns             | $V_{DS}=0\dots400\text{V}$ , $I_{SD}\leq I_S$ , $T_j=25^\circ\text{C}$ |
| Maximum diode commutation speed        | di/dt         | -      | -    | 55      | A/ $\mu\text{s}$ | $V_{DS}=0\dots400\text{V}$ , $I_{SD}\leq I_S$ , $T_j=25^\circ\text{C}$ |
| Insulation withstand voltage           | $V_{ISO}$     | -      | -    | n.a.    | V                | $V_{rms}$ , $T_C=25^\circ\text{C}$ , $t=1\text{min}$                   |

<sup>1)</sup> Limited by  $T_{j,max}$ .

<sup>2)</sup> Pulse width  $t_p$  limited by  $T_{j,max}$ .

<sup>3)</sup> Identical low side and high side switch with identical  $R_G$ .

## 2 Thermal characteristics

**Table 3 Thermal characteristics**

| Parameter                                              | Symbol     | Values |      |      | Unit | Note / Test Condition                                                                                                                                                               |
|--------------------------------------------------------|------------|--------|------|------|------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                        |            | Min.   | Typ. | Max. |      |                                                                                                                                                                                     |
| Thermal resistance, junction - case                    | $R_{thJC}$ | -      | -    | 1.87 | °C/W | -                                                                                                                                                                                   |
| Thermal resistance, junction - ambient                 | $R_{thJA}$ | -      | -    | 62   | °C/W | device on PCB, minimal footprint                                                                                                                                                    |
| Thermal resistance, junction - ambient for SMD version | $R_{thJA}$ | -      | 35   | 45   | °C/W | Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6cm <sup>2</sup> (one layer, 70µm thickness) copper area for drain connection and cooling. PCB is vertical without air stream cooling. |
| Reflow soldering temperature                           | $T_{sold}$ | -      | -    | 260  | °C   | reflow MSL2a                                                                                                                                                                        |

### 3 Electrical characteristics

at  $T_j=25^\circ\text{C}$ , unless otherwise specified

**Table 4 Static characteristics**

| Parameter                        | Symbol        | Values |                |            | Unit     | Note / Test Condition                                                                                       |
|----------------------------------|---------------|--------|----------------|------------|----------|-------------------------------------------------------------------------------------------------------------|
|                                  |               | Min.   | Typ.           | Max.       |          |                                                                                                             |
| Drain-source breakdown voltage   | $V_{(BR)DSS}$ | 650    | -              | -          | V        | $V_{GS}=0V$ , $I_D=1mA$                                                                                     |
| Gate threshold voltage           | $V_{(GS)th}$  | 3      | 3.5            | 4          | V        | $V_{DS}=V_{GS}$ , $I_D=0.24mA$                                                                              |
| Zero gate voltage drain current  | $I_{DSS}$     | -      | -              | 1          | $\mu A$  | $V_{DS}=650$ , $V_{GS}=0V$ , $T_j=25^\circ\text{C}$<br>$V_{DS}=650$ , $V_{GS}=0V$ , $T_j=150^\circ\text{C}$ |
| Gate-source leakage current      | $I_{GSS}$     | -      | -              | 100        | nA       | $V_{GS}=20V$ , $V_{DS}=0V$                                                                                  |
| Drain-source on-state resistance | $R_{DS(on)}$  | -      | 0.204<br>0.488 | 0.230<br>- | $\Omega$ | $V_{GS}=10V$ , $I_D=2.4A$ , $T_j=25^\circ\text{C}$<br>$V_{GS}=10V$ , $I_D=2.4A$ , $T_j=150^\circ\text{C}$   |
| Gate resistance                  | $R_G$         | -      | 1              | -          | $\Omega$ | $f=1MHz$ , open drain                                                                                       |

**Table 5 Dynamic characteristics**

| Parameter                                                  | Symbol       | Values |      |      | Unit | Note / Test Condition                                         |
|------------------------------------------------------------|--------------|--------|------|------|------|---------------------------------------------------------------|
|                                                            |              | Min.   | Typ. | Max. |      |                                                               |
| Input capacitance                                          | $C_{iss}$    | -      | 996  | -    | pF   | $V_{GS}=0V$ , $V_{DS}=400V$ , $f=250kHz$                      |
| Output capacitance                                         | $C_{oss}$    | -      | 14   | -    | pF   | $V_{GS}=0V$ , $V_{DS}=400V$ , $f=250kHz$                      |
| Effective output capacitance, energy related <sup>1)</sup> | $C_{o(er)}$  | -      | 29   | -    | pF   | $V_{GS}=0V$ , $V_{DS}=0...400V$                               |
| Effective output capacitance, time related <sup>2)</sup>   | $C_{o(tr)}$  | -      | 313  | -    | pF   | $I_D=\text{constant}$ , $V_{GS}=0V$ , $V_{DS}=0...400V$       |
| Turn-on delay time                                         | $t_{d(on)}$  | -      | 8    | -    | ns   | $V_{DD}=400V$ , $V_{GS}=13V$ , $I_D=2.4A$ ,<br>$R_G=10\Omega$ |
| Rise time                                                  | $t_r$        | -      | 5    | -    | ns   | $V_{DD}=400V$ , $V_{GS}=13V$ , $I_D=2.4A$ ,<br>$R_G=10\Omega$ |
| Turn-off delay time                                        | $t_{d(off)}$ | -      | 71   | -    | ns   | $V_{DD}=400V$ , $V_{GS}=13V$ , $I_D=2.4A$ ,<br>$R_G=10\Omega$ |
| Fall time                                                  | $t_f$        | -      | 22   | -    | ns   | $V_{DD}=400V$ , $V_{GS}=13V$ , $I_D=2.4A$ ,<br>$R_G=10\Omega$ |

**Table 6 Gate charge characteristics**

| Parameter             | Symbol        | Values |      |      | Unit | Note / Test Condition                            |
|-----------------------|---------------|--------|------|------|------|--------------------------------------------------|
|                       |               | Min.   | Typ. | Max. |      |                                                  |
| Gate to source charge | $Q_{GS}$      | -      | 5    | -    | nC   | $V_{DD}=400V$ , $I_D=2.4A$ , $V_{GS}=0$ to $10V$ |
| Gate to drain charge  | $Q_{gd}$      | -      | 6    | -    | nC   | $V_{DD}=400V$ , $I_D=2.4A$ , $V_{GS}=0$ to $10V$ |
| Gate charge total     | $Q_g$         | -      | 20   | -    | nC   | $V_{DD}=400V$ , $I_D=2.4A$ , $V_{GS}=0$ to $10V$ |
| Gate plateau voltage  | $V_{plateau}$ | -      | 5.0  | -    | V    | $V_{DD}=400V$ , $I_D=2.4A$ , $V_{GS}=0$ to $10V$ |

<sup>1)</sup>  $C_{o(er)}$  is a fixed capacitance that gives the same stored energy as  $C_{oss}$  while  $V_{DS}$  is rising from 0 to 400V

<sup>2)</sup>  $C_{o(tr)}$  is a fixed capacitance that gives the same charging time as  $C_{oss}$  while  $V_{DS}$  is rising from 0 to 400V

**Table 7 Reverse diode characteristics**

| Parameter                     | Symbol    | Values |      |      | Unit    | Note / Test Condition                  |
|-------------------------------|-----------|--------|------|------|---------|----------------------------------------|
|                               |           | Min.   | Typ. | Max. |         |                                        |
| Diode forward voltage         | $V_{SD}$  | -      | 0.8  | -    | V       | $V_{GS}=0V, I_F=2.4A, T_J=25^{\circ}C$ |
| Reverse recovery time         | $t_{rr}$  | -      | 414  | -    | ns      | $V_R=400V, I_F=10A, di_F/dt=55A/\mu s$ |
| Reverse recovery charge       | $Q_{rr}$  | -      | 3.1  | -    | $\mu C$ | $V_R=400V, I_F=10A, di_F/dt=55A/\mu s$ |
| Peak reverse recovery current | $I_{rrm}$ | -      | 13.6 | -    | A       | $V_R=400V, I_F=10A, di_F/dt=55A/\mu s$ |

## 4 Electrical characteristics diagrams







Diagram 5: Typ. output characteristics




$I_D = f(V_{DS})$ ;  $T_j = 25\text{ °C}$ ; parameter:  $V_{GS}$

Diagram 6: Typ. output characteristics




$I_D = f(V_{DS})$ ;  $T_j = 125\text{ °C}$ ; parameter:  $V_{GS}$

Diagram 7: Typ. drain-source on-state resistance




$R_{DS(on)} = f(I_D)$ ;  $T_j = 125\text{ °C}$ ; parameter:  $V_{GS}$

Diagram 8: Drain-source on-state resistance




$R_{DS(on)} = f(T_j)$ ;  $I_D = 2.4\text{ A}$ ;  $V_{GS} = 10\text{ V}$

**Diagram 9: Typ. transfer characteristics**




$I_D = f(V_{GS})$ ;  $V_{DS} = 20$  V; parameter:  $T_j$

**Diagram 10: Typ. gate charge**




$V_{GS} = f(Q_{gate})$ ;  $I_D = 2.4$  A pulsed; parameter:  $V_{DD}$

**Diagram 11: Forward characteristics of reverse diode**




$I_F = f(V_{SD})$ ; parameter:  $T_j$

**Diagram 12: Avalanche energy**




$E_{AS} = f(T_j)$ ;  $I_D = 4.8$  A;  $V_{DD} = 50$  V

**Diagram 13: Drain-source breakdown voltage**




$V_{BR(DSS)} = f(T_J); I_D = 1 \text{ mA}$

**Diagram 14: Typ. capacitances**



$C = f(V_{DS}); V_{GS} = 0 \text{ V}; f = 250 \text{ kHz}$


**Diagram 15: Typ. Coss stored energy**




$E_{oss} = f(V_{DS})$

## 5 Test Circuits


**Table 8 Diode characteristics**



**Table 9 switching times (ss)**



**Table 10 Unclamped inductive load (ss)**



## 6 Package Outlines




Figure 1 Outline PG-VSON-4, dimensions in mm/inches

## **7 Appendix A**

### **Table 11 Related Links**

- IFX CoolMOS™ C7 Webpage: [www.infineon.com](http://www.infineon.com)
- IFX CoolMOS™ C7 application note: [www.infineon.com](http://www.infineon.com)
- IFX CoolMOS™ C7 simulation model: [www.infineon.com](http://www.infineon.com)
- IFX Design tools: [www.infineon.com](http://www.infineon.com)

## Revision History

IPL65R230C7

**Revision: 2017-08-29, Rev. 2.1**

Previous Revision

| Revision | Date       | Subjects (major changes since last revision) |
|----------|------------|----------------------------------------------|
| 2.0      | 2013-04-29 | Release of final version                     |
| 2.1      | 2017-08-29 | Updated MSL; style updated                   |

### Trademarks of Infineon Technologies AG

AURIX™, C166™, CanPAK™, CIPOS™, CoolGaN™, CoolMOS™, CoolSET™, CoolSiC™, CORECONTROL™, CROSSAVE™, DAVE™, DI-POL™, DrBlade™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPACK™, EconoPIM™, EiceDRIVER™, eupec™, FCOS™, HITFET™, HybridPACK™, Infineon™, ISOFACE™, IsoPACK™, i-Wafer™, MIPAQ™, ModSTACK™, my-d™, NovalithIC™, OmniTune™, OPTIGA™, OptiMOS™, ORIGA™, POWERCODE™, PRIMARION™, PrimePACK™, PrimeSTACK™, PROFET™, PRO-SiL™, RASIC™, REAL3™, ReverSave™, SatRIC™, SIEGET™, SiPMOS™, SmartLEWIS™, SOLID FLASH™, SPOC™, TEMPFET™, thinQ!™, TRENCHSTOP™, TriCore™.

Trademarks updated August 2015

### Other Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

### We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to:

**erratum@infineon.com**

**Published by**  
**Infineon Technologies AG**  
**81726 München, Germany**  
**© 2017 Infineon Technologies AG**  
**All Rights Reserved.**

### Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

### Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (**www.infineon.com**).

### Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[IPL65R230C7](#)