

XHP™3 module with Emitter Controlled 4 diode**Features**

- Electrical features
 - $V_R = 4500\text{ V}$
 - $I_F = 450\text{ A}$, $I_{FRM} = 900\text{ A}$
 - High dynamic robustness
- Mechanical features
 - Package with CTI > 600
 - AlSiC base plate for increased thermal cycling capability
 - High creepage and clearance distances
 - Housing material compliant with the classification R23 (HL3) of the EN45545-2 “Fire protection of railway vehicles”
 - Package with enhanced insulation of 10.4 kV AC 60 s

**Potential applications**

- Traction drives
- Medium-voltage converters

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068


Description

Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	Diode, Inverter	3
3	Characteristics diagrams	5
4	Circuit diagram	7
5	Package outlines	8
6	Module label code	9
	Revision history	10
	Disclaimer	11

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50 \text{ Hz}$, $t = 1 \text{ min}$	10.4	kV
Partial discharge extinction voltage	V_{isol}	RMS, $f = 50 \text{ Hz}$, $Q_{PD} \text{ typ. } 10 \text{ pC}$	5.1	kV
DC stability	$V_{CE(D)}$	$T_{vj} = 25 \text{ °C}$, 100 Fit	2900	V
Material of module baseplate			AlSiC	
Creepage distance	d_{Creep}	terminal to heatsink	53.0	mm
Creepage distance	d_{Creep}	terminal to terminal	53.0	mm
Clearance	d_{Clear}	terminal to heatsink	36.0	mm
Clearance	d_{Clear}	terminal to terminal	26.0	mm
Comparative tracking index	CTI		> 600	

Table 2 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Stray inductance module	L_{sCE}				25		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	$T_C = 25\text{ }^{\circ}\text{C}$, per switch			0.33		mΩ
Storage temperature	T_{stg}			-40		150	°C
Mounting torque for module mounting	M	- Mounting according to valid application note	M6, Screw	4.25		5.75	Nm
Terminal connection torque	M	- Mounting according to valid application note	M3, Screw	0.9		1.1	Nm
			M8, Screw	8		10	
Weight	G				700		g

2 Diode, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = -40 \text{ °C}$	4500	V
		$T_{vj} = 150 \text{ °C}$	4500	
Continuous DC forward current	I_F		450	A
Repetitive peak forward current	I_{FRM}	$t_P = 1 \text{ ms}$	900	A

(table continues...)

Table 3 (continued) Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
I^2t - value	I^2t	$t_p = 10 \text{ ms}, V_R = 0 \text{ V}$	$T_{vj} = 125 \text{ °C}$	kA^2s
			$T_{vj} = 150 \text{ °C}$	
Maximum power dissipation	P_{RQM}	$T_{vj} = 150 \text{ °C}$	1500	kW
Minimum turn-on time	t_{onmin}		10	μs

Table 4 Characteristic values


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 450 \text{ A}, V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$	2.60	3.05	V
			$T_{vj} = 125 \text{ °C}$	2.50	2.95	
			$T_{vj} = 150 \text{ °C}$	2.45	2.90	
Peak reverse recovery current	I_{RM}	$V_{CC} = 2800 \text{ V}, I_F = 450 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 4900 \text{ A}/\mu\text{s} (T_{vj} = 150 \text{ °C})$	$T_{vj} = 25 \text{ °C}$	925		A
			$T_{vj} = 125 \text{ °C}$	920		
			$T_{vj} = 150 \text{ °C}$	920		
Recovered charge	Q_r	$V_{CC} = 2800 \text{ V}, I_F = 450 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 4900 \text{ A}/\mu\text{s} (T_{vj} = 150 \text{ °C})$	$T_{vj} = 25 \text{ °C}$	405		μC
			$T_{vj} = 125 \text{ °C}$	780		
			$T_{vj} = 150 \text{ °C}$	900		
Reverse recovery energy	E_{rec}	$V_{CC} = 2800 \text{ V}, I_F = 450 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 4900 \text{ A}/\mu\text{s} (T_{vj} = 150 \text{ °C})$	$T_{vj} = 25 \text{ °C}$	690		mJ
			$T_{vj} = 125 \text{ °C}$	1400		
			$T_{vj} = 150 \text{ °C}$	1650		
Thermal resistance, junction to case	R_{thJC}	per diode			44.9	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per diode, $\lambda_{grease} = 1 \text{ W}/(\text{m}\cdot\text{K})$		19.8		K/kW
Temperature under switching conditions	$T_{vj op}$		-40		150	°C

Note: Dynamic data valid in conjunction with FF450R45T3E4_B5 module

3 Characteristics diagrams

Forward characteristic (typical), Diode, Inverter


$I_F = f(V_F)$



Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$


$R_{Gon} = 0.39 \Omega, V_{CE} = 2800 \text{ V}$



Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$


$V_{CE} = 2800 \text{ V}, I_F = 450 \text{ A}$



Safe operating area (SOA), Diode, Inverter


$I_R = f(V_R)$

$T_{vj} = 150^\circ\text{C}$



Transient thermal impedance, Diode, Inverter

$Z_{th} = f(t)$






Figure 1

6 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example			
			
71549142846550549911530		71549142846550549911530	

Figure 3



Revision history

Revision history

Document revision	Date of release	Description of changes
1.00	2023-06-15	Initial version

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-06-15

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2023 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference

IFX-ABF407-001

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[DD450S45T3E4B5BPSA1](#)