



| | | |
|--|------------|-----------|
| V_{DSS} | 30 | V |
| R_{DS(on)} max (@ V _{GS} = 10V) | 3.8 | mΩ |
| Qg (typical) | 15 | nC |
| Rg (typical) | 2.5 | Ω |
| I_D (@T _{C (Bottom)} = 25°C) | 77 | A |



Applications

- Battery Operated DC Motor Inverter MOSFET

Features

| |
|--|
| Low R _{DS(on)} (< 3.8mΩ) |
| Low Thermal Resistance to PCB (< 3.4°C/W) |
| 100% Rg tested |
| Low Profile (< 1.0 mm) |
| Industry-Standard Pinout |
| Compatible with Existing Surface Mount Techniques |
| RoHS Compliant Containing no Lead, no Bromide and no Halogen |
| MSL1, Industrial Qualification |

results in
⇒

Benefits

| |
|-----------------------------------|
| Lower Conduction Losses |
| Enable better thermal dissipation |
| Increased Reliability |
| Increased Power Density |
| Multi-Vendor Compatibility |
| Easier Manufacturing |
| Environmentally Friendlier |
| Increased Reliability |

| Orderable part number | Package Type | Standard Pack | | Note |
|-----------------------|--------------------|---------------|----------|------------------|
| | | Form | Quantity | |
| IRFHM830TRPbF | PQFN 3.3mm x 3.3mm | Tape and Reel | 4000 | |
| IRFHM830TR2PbF | PQFN 3.3mm x 3.3mm | Tape and Reel | 400 | EOL notice # 259 |

Absolute Maximum Ratings

| Symbol | Parameter | Max. | Units |
|---|---|--------------|-------|
| V _{DS} | Drain-to-Source Voltage | 30 | V |
| V _{GS} | Gate-to-Source Voltage | ± 20 | |
| I _D @ T _A = 25°C | Continuous Drain Current, V _{GS} @ 10V | 21 | A |
| I _D @ T _A = 70°C | Continuous Drain Current, V _{GS} @ 10V | 17 | |
| I _D @ T _{C(Bottom)} = 25°C | Continuous Drain Current, V _{GS} @ 10V ⑥ | 77 | |
| I _D @ T _{C(Bottom)} = 100°C | Continuous Drain Current, V _{GS} @ 10V ⑥ | 49 | |
| I _{DM} | Pulsed Drain Current ① | 308 | |
| P _D @ T _A = 25°C | Power Dissipation ⑤ | 2.7 | W |
| P _D @ T _{C(Bottom)} = 25°C | Power Dissipation ⑤ | 37 | |
| | Linear Derating Factor ⑤ | 0.022 | W/°C |
| T _J T _{STG} | Operating Junction and Storage Temperature Range | -55 to + 150 | °C |

Notes ① through ⑥ are on page 9


Static @ T_J = 25°C (unless otherwise specified)

| Symbol | Parameter | Min. | Typ. | Max. | Units | Conditions |
|-------------------------------------|---|------|------|------|-------|--|
| BV _{DSS} | Drain-to-Source Breakdown Voltage | 30 | — | — | V | V _{GS} = 0V, I _D = 250μA |
| ΔBV _{DSS} /ΔT _J | Breakdown Voltage Temp. Coefficient | — | 0.02 | — | V/°C | Reference to 25°C, I _D = 1mA |
| R _{DS(on)} | Static Drain-to-Source On-Resistance | — | 3.0 | 3.8 | mΩ | V _{GS} = 10V, I _D = 20A ③ |
| | | — | 4.8 | 6.0 | | V _{GS} = 4.5V, I _D = 20A ③ |
| V _{GS(th)} | Gate Threshold Voltage | 1.35 | 1.8 | 2.35 | V | V _{DS} = V _{GS} , I _D = 50μA |
| ΔV _{GS(th)} | Gate Threshold Voltage Coefficient | — | -6.3 | — | mV/°C | |
| I _{DSS} | Drain-to-Source Leakage Current | — | — | 1 | μA | V _{DS} = 24V, V _{GS} = 0V |
| | | — | — | 150 | | V _{DS} = 24V, V _{GS} = 0V, T _J = 125°C |
| I _{GSS} | Gate-to-Source Forward Leakage | — | — | 100 | nA | V _{GS} = 20V |
| | Gate-to-Source Reverse Leakage | — | — | -100 | | V _{GS} = -20V |
| g _{fs} | Forward Transconductance | 52 | — | — | S | V _{DS} = 15V, I _D = 20A |
| Q _g | Total Gate Charge | — | 31 | — | nC | V _{GS} = 10V, V _{DS} = 15V, I _D = 20A |
| Q _g | Total Gate Charge | — | 15 | 23 | | V _{DS} = 15V V _{GS} = 4.5V I _D = 20A See Fig.17 & 18 |
| Q _{gs1} | Pre-V _{th} Gate-to-Source Charge | — | 3.8 | — | | |
| Q _{gs2} | Post-V _{th} Gate-to-Source Charge | — | 2.0 | — | | |
| Q _{gd} | Gate-to-Drain Charge | — | 5.0 | — | | |
| Q _{godr} | Gate Charge Overdrive | — | 4.2 | — | | |
| Q _{sw} | Switch Charge (Q _{gs2} + Q _{gd}) | — | 7.0 | — | nC | V _{DS} = 16V, V _{GS} = 0V |
| Q _{oss} | Output Charge | — | 9.7 | — | | |
| R _G | Gate Resistance | — | 2.5 | — | Ω | |
| t _{d(on)} | Turn-On Delay Time | — | 12 | — | ns | V _{DD} = 15V, V _{GS} = 4.5V I _D = 20A R _G = 1.8Ω See Fig.15 |
| t _r | Rise Time | — | 25 | — | | |
| t _{d(off)} | Turn-Off Delay Time | — | 13 | — | | |
| t _f | Fall Time | — | 9.2 | — | | |
| C _{iss} | Input Capacitance | — | 2155 | — | pF | V _{GS} = 0V |
| C _{oss} | Output Capacitance | — | 350 | — | | V _{DS} = 25V |
| C _{rss} | Reverse Transfer Capacitance | — | 160 | — | | f = 1.0MHz |

Avalanche Characteristics







| Symbol | Parameter | Typ. | Max. | Units |
|-------------------------------------|---------------------------------|------|------|-------|
| E _{AS} (Thermally limited) | Single Pulse Avalanche Energy ② | — | 82 | mJ |
| I _{AR} | Avalanche Current ① | — | 20 | A |






Diode Characteristics







| Symbol | Parameter | Min. | Typ. | Max. | Units | Conditions |
|-----------------|--|------|------|------|-------|--|
| I _S | Continuous Source Current (Body Diode) | — | — | 37 | A | MOSFET symbol showing the integral reverse p-n junction diode.  |
| I _{SM} | Pulsed Source Current (Body Diode) ① | — | — | 308 | | |
| V _{SD} | Diode Forward Voltage | — | — | 1.0 | V | T _J = 25°C, I _S = 20A, V _{GS} = 0V ③ |
| t _{rr} | Reverse Recovery Time | — | 17 | 26 | ns | T _J = 25°C, I _F = 20A, V _{DD} = 15V di/dt = 300A/μs ③ |
| Q _{rr} | Reverse Recovery Charge | — | 23 | 35 | nC | |

Thermal Resistance

| Symbol | Parameter | Typ. | Max. | Units |
|---------------------------|-----------------------|------|------|-------|
| R _{θJC} (Bottom) | Junction-to-Case ④ | — | 3.4 | °C/W |
| R _{θJC} (Top) | Junction-to-Case ④ | — | 37 | |
| R _{θJA} | Junction-to-Ambient ⑤ | — | 46 | |
| R _{θJA} (<10s) | Junction-to-Ambient ⑤ | — | 31 | |


Fig 1. Typical Output Characteristics

Fig 2. Typical Output Characteristics

Fig 3. Typical Transfer Characteristics

Fig 4. Normalized On-Resistance vs. Temperature

Fig 5. Typical Capacitance vs. Drain-to-Source Voltage

Fig 6. Typical Gate Charge vs. Gate-to-Source Voltage


Fig 7. Typical Source-Drain Diode Forward Voltage

Fig 8. Maximum Safe Operating Area

Fig 9. Maximum Drain Current vs. Case Temperature

Fig 10. Threshold Voltage Vs. Temperature

Fig 11. Maximum Effective Transient Thermal Impedance, Junction-to-Case


Fig 12. On-Resistance vs. Gate Voltage

Fig 13. Maximum Avalanche Energy vs. Drain Current

Fig 14a. Unclamped Inductive Test Circuit

Fig 14b. Unclamped Inductive Waveforms

Fig 15a. Switching Time Test Circuit

Fig 15b. Switching Time Waveforms





Fig 16. Peak Diode Recovery dv/dt Test Circuit for N-Channel HEXFET® Power MOSFETs




Fig 17. Gate Charge Test Circuit






Fig 18. Gate Charge Waveform

PQFN 3.3 x 3.3 Outline “B” Package Details



| SYMBOL | COMMON | | | |
|--------|----------|-------|------------|--------|
| | MM | | INCH | |
| | MIN. | MAX. | MIN. | MAX. |
| A | 0.70 | 1.05 | 0.0276 | 0.0413 |
| A1 | 0.12 | 0.39 | 0.0047 | 0.0154 |
| b | 0.25 | 0.39 | 0.0098 | 0.0154 |
| D | 3.20 | 3.45 | 0.1260 | 0.1358 |
| D1 | 3.00 | 3.20 | 0.1181 | 0.1417 |
| D2 | 1.69 | 2.20 | 0.0665 | 0.0866 |
| E | 3.20 | 3.40 | 0.1260 | 0.1339 |
| E1 | 3.00 | 3.20 | 0.1181 | 0.1417 |
| E2 | 2.15 | 2.59 | 0.0846 | 0.1020 |
| e | 0.65 BSC | | 0.0256 BSC | |
| L | 0.15 | 0.55 | 0.0059 | 0.0217 |
| M | 0.59 | — | 0.0232 | — |
| O | 9Deg | 12Deg | 9Deg | 12Deg |

PQFN 3.3 x 3.3 Outline “G” Package Details




| DIM | MILLIMETERS | | INCHES | |
|-----|-------------|------|------------|-------|
| | MIN | MAX | MIN | MAX |
| A | 0.80 | 0.90 | .0315 | .0354 |
| A1 | 0.12 | 0.22 | .0047 | .0086 |
| b | 0.22 | 0.42 | .0087 | .0165 |
| b1 | 0.05 | 0.15 | .0020 | .0059 |
| D | 3.30 BSC | | .1299 BSC | |
| D1 | 3.10 BSC | | .1220 BSC | |
| D2 | 2.29 | 2.69 | .0902 | .1059 |
| E | 3.30 BSC | | .1299 BSC | |
| E1 | 3.10 BSC | | .1220 BSC | |
| E2 | 1.85 | 2.05 | .0728 | .0807 |
| e | 0.65 BSC | | .0255 BSC | |
| j | 0.15 | 0.35 | .0059 | .0137 |
| k | 0.75 | 0.95 | .0295 | .0374 |
| n | 0.15 | 0.35 | .0059 | .0137 |
| M | NOM. 0.20 | | NOM. .0078 | |
| P | 9° | 11° | 9° | 11° |

For more information on board mounting, including footprint and stencil recommendation, please refer to application note AN-1136: <http://www.irf.com/technical-info/appnotes/an-1136.pdf>

For more information on package inspection techniques, please refer to application note AN-1154: <http://www.irf.com/technical-info/appnotes/an-1154.pdf>


Note: For the most current drawing please refer to website at <http://www.irf.com/packaging>

PQFN 3.3 x 3.3 Part Marking



Note: For the most current drawing please refer to website at <http://www.irf.com/packaging>

PQFN 3.3 x 3.3 Tape and Reel



Note: All dimension are in nominal

| Package Type | Reel Diameter (inch) | QTY | Reel Width W1 (mm) | Ao (mm) | Bo (mm) | Ko (mm) | P1 (mm) | W (mm) | Pin 1 Quadrant |
|--------------|----------------------|------|--------------------|---------|---------|---------|---------|--------|----------------|
| 3.3x3.3 | 13 | 4000 | 12.4 | 3.60 | 3.60 | 1.20 | 8.00 | 12 | Q1 |

Note: For the most current drawing please refer to website at <http://www.irf.com/packaging>

Qualification Information

| | | |
|-----------------------------------|---|--|
| Qualification Level | Industrial (per JEDEC JESD47F [†] guidelines) | |
| Moisture Sensitivity Level | PQFN 3.3mm x 3.3mm | MSL1 (per JEDEC J-STD-020D [†]) |
| RoHS Compliant | Yes | |

† Applicable version of JEDEC standard at the time of product release.

Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature.
- ② Starting $T_J = 25^{\circ}\text{C}$, $L = 0.41\text{mH}$, $R_G = 50\Omega$, $I_{AS} = 12\text{A}$.
- ③ Pulse width $\leq 400\mu\text{s}$; duty cycle $\leq 2\%$.
- ④ R_{θ} is measured at T_J of approximately 90°C .
- ⑤ When mounted on 1 inch square PCB (FR-4). Please refer to AN-994 for more details:
<http://www.irf.com/technical-info/appnotes/an-994.pdf>
- ⑥ Rating refers to the product only with datasheet specified absolute maximum values, maintaining case temperature at 25°C . For higher case temperature please refer to Diagram 9. De-rating will be required based on the actual environmental conditions.

Revision History

| Date | Rev. | Comments |
|------------|------|--|
| 12/16/2013 | 2.1 | <ul style="list-style-type: none"> Updated ordering information to reflect the End-Of-Life (EOL) of the mini-reel option (EOL notice #259). Updated data sheet with the new IR corporate template. |
| 06/06/2014 | 2.2 | <ul style="list-style-type: none"> Updated schematic on page1 Updated part marking on page 7. Updated Tape and Reel on page 8. |
| 09/25/2015 | 2.3 | <ul style="list-style-type: none"> Updated package outline to reflect the PCN # (67-PCN90-Public-R2) for "option B" and added package outline for "option G" on page 7 Updated "IFX" logo on all pages. |
| 03/17/2021 | 2.4 | <ul style="list-style-type: none"> Updated datasheet based on IFX template. Updated Datasheet based on new current rating and application note : App-AN_1912_PL51_2001_180356 Removed "HEXFET[®] Power MOSFET" added "IR MOSFET[™]" "-page1 |

Trademarks of Infineon Technologies AG

μHVIC™, μIPM™, μPFC™, AU-ConvertIR™, AURIX™, C166™, CanPAK™, CIPOS™, CIPURSE™, CoolDP™, CoolGaN™, COOLiR™, CoolMOS™, CoolSET™, CoolSiC™, DAVE™, DI-POL™, DirectFET™, DrBlade™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPACK™, EconoPIM™, EiceDRIVER™, eupec™, FCOS™, GaNpowIR™, HEXFET™, HITFET™, HybridPACK™, iMOTION™, IRAM™, ISOFACE™, IsoPACK™, LEDriviR™, LITIX™, MIPAQ™, ModSTACK™, my-d™, NovalithIC™, OPTIGA™, OptiMOS™, ORIGA™, PowIRaudio™, PowIRstage™, PrimePACK™, PrimeSTACK™, PROFET™, PRO-SiL™, RASiC™, REAL3™, SmartLEWIS™, SOLID FLASH™, SPOC™, StrongIRFET™, SupIRBuck™, TEMPFET™, TRENCHSTOP™, TriCore™, UHVIC™, XHP™, XMC™

Trademarks updated November 2015

Other Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2016-04-16

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2016 Infineon Technologies AG.

All Rights Reserved.

Do you have a question about this document?

Email: erratum@infineon.com

Document reference

ifx1

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or **characteristics ("Beschaffenheitsgarantie")**.

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document **is subject to customer's compliance with its obligations** stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in **customer's applications**.

The data contained in this document is exclusively intended for technically trained staff. It is the **responsibility of customer's technical departments** to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, **Infineon Technologies' products may** not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[IRFHM830TRPBF](#)