



OptiMOS™ P3 Power-Transistor
Features

- single P-Channel (Logic Level)
- Enhancement mode
- Qualified according JEDEC¹⁾ for target applications
- 175 °C operating temperature
- Pb-free; RoHS compliant
- applications: load switch, HS-switch
- Halogen-free according to IEC61249-2-21


Product Summary

V_{DS}	-30	V
$R_{DS(on),max}$	$V_{GS} = 10V$	4.2
	$V_{GS} = 4.5V$	6.8
I_D	-70	A


PG-TO252-3


Type	Package	Marking	Lead free	Packing
IPD042P03L3 G	PG-TO252-3	042P03L	Yes	non dry

Maximum ratings, at $T_j=25\text{ °C}$, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	I_D	$T_C=25\text{ °C}$	-70	A
		$T_C=100\text{ °C}$	-70	
Pulsed drain current	$I_{D,pulse}$	$T_C=25\text{ °C}^{2)}$	-280	
Avalanche energy, single pulse	E_{AS}	$I_D=-70\text{ A}$, $R_{GS}=25\text{ }\Omega$	269	mJ
Gate source voltage	V_{GS}		± 20	V
Power dissipation	P_{tot}	$T_C=25\text{ °C}$	150	W
Operating and storage temperature	T_j , T_{stg}		-55 ... 175	°C
ESD class		JESD22-A114 HBM	class 2 (2 kV - < 4 kV)	
Soldering temperature			260	°C
IEC climatic category; DIN IEC 68-1			55/175/56	

¹⁾ J-STD20 and JESD22

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Thermal characteristics

Thermal resistance, junction - case	R_{thJC}		-	-	1.0	K/W
Thermal resistance, junction - ambient	R_{thJA}	6 cm ² cooling area ²⁾	-	-	50	

Electrical characteristics, at $T_j=25\text{ }^{\circ}\text{C}$, unless otherwise specified

Static characteristics

Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS}=0\text{ V}, I_D=-250\mu\text{A}$	-30	-	-	V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=-270\mu\text{A}$	-2.0	-1.5	-1.0	
Zero gate voltage drain current	I_{DSS}	$V_{DS}=-30\text{ V}, V_{GS}=0\text{ V}, T_j=25\text{ }^{\circ}\text{C}$	-	-	-1	μA
		$V_{DS}=-30\text{ V}, V_{GS}=0\text{ V}, T_j=175\text{ }^{\circ}\text{C}$	-	-	-300	
Gate-source leakage current	I_{GSS}	$V_{GS}=-20\text{ V}, V_{DS}=0\text{ V}$	-	-10	-100	nA
Drain-source on-state resistance	$R_{DS(on)}$	$V_{GS}=-4.5\text{ V}, I_D=-70\text{ A}$	-	4.6	6.8	m Ω
		$V_{GS}=-10\text{ V}, I_D=-70\text{ A}$	-	3.5	4.2	
Gate resistance	R_G		-	2.4	-	Ω
Transconductance	g_{fs}	$ V_{DS} >2 I_D R_{DS(on)max}, I_D=-70\text{ A}$	65	130	-	S

²⁾ Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 μm thick) copper area for drain connection. PCB is vertical in still air.

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Dynamic characteristics

Input capacitance	C_{iss}	$V_{GS}=0\text{ V}, V_{DS}=-15\text{ V},$ $f=1\text{ MHz}$	-	9290	12400	pF
Output capacitance	C_{oss}		-	3570	4750	
Reverse transfer capacitance	C_{rss}		-	150	220	
Turn-on delay time	$t_{d(on)}$	$V_{DD}=-15\text{ V}, V_{GS}=-10\text{ V}, I_D=-70\text{ A},$ $R_{G,ext}=6\ \Omega$	-	21	33	ns
Rise time	t_r		-	167	251	
Turn-off delay time	$t_{d(off)}$		-	89	134	
Fall time	t_f		-	22	33	

Gate Charge Characteristics³⁾


Gate to source charge	Q_{gs}	$V_{DD}=-15\text{ V}, I_D=-70\text{ A},$ $V_{GS}=0\text{ to }-10\text{ V}$	-	31	41	nC
Gate charge at threshold	$Q_{g(th)}$		-	15	20	
Gate to drain charge	Q_{gd}		-	14	21	
Switching charge	Q_{sw}		-	30	42	
Gate charge total	Q_g		-	131	175	
Gate plateau voltage	$V_{plateau}$		-	3.3	-	V
Output charge	Q_{oss}	$V_{DD}=-15\text{ V}, V_{GS}=0\text{ V}$	-	84	111	nC

Reverse Diode

Diode continuous forward current	I_S	$T_C=25\text{ °C}$	-	-	70	A
Diode pulse current	$I_{S,pulse}$		-	-	280	
Diode forward voltage	V_{SD}	$V_{GS}=0\text{ V}, I_F=-70\text{ A},$ $T_J=25\text{ °C}$	-	-	-1.1	V
Reverse recovery time	t_{rr}	$V_R=15\text{ V}, I_F= I_S ,$ $di_F/dt=100\text{ A}/\mu\text{s}$	-	54	68	ns
Reverse recovery charge	Q_{rr}		-	61	76	nC


1 Power dissipation

$$P_{\text{tot}} = f(T_C); t_p \leq 10 \text{ s}$$



2 Drain current


$$I_D = f(T_C); |V_{GS}| \geq 10 \text{ V}; t_p \leq 10 \text{ s}$$



3 Safe operating area

$$I_D = f(V_{DS}); T_C = 25 \text{ °C}^1; D = 0$$


parameter: t_p



4 Max. transient thermal impedance


$$Z_{\text{thJS}} = f(t_p)$$

parameter: $D = t_p/T$




5 Typ. output characteristics

 $I_D = f(V_{DS}); T_j = 25^\circ\text{C}$

parameter: V_{GS}



6 Typ. drain-source on resistance

 $R_{DS(on)} = f(I_D); T_j = 25^\circ\text{C}$


parameter: V_{GS}


7 Typ. transfer characteristics

 $I_D = f(V_{GS}); |V_{DS}| > 2|I_D|R_{DS(on)max}$


parameter: T_j


8 Typ. forward transconductance

 $g_{fs} = f(I_D); T_j = 25^\circ\text{C}$



9 Drain-source on-state resistance

$$R_{DS(on)} = f(T_j); I_D = -30 \text{ A}; V_{GS} = -10 \text{ V}$$




10 Typ. gate threshold voltage

$$V_{GS(th)} = f(T_j); V_{GS} = V_{DS}; I_D = -270 \text{ μA}$$



11 Typ. capacitances


$$C = f(V_{DS}); V_{GS} = 0 \text{ V}; f = 1 \text{ MHz}$$



12 Forward characteristics of reverse diode


$$I_F = f(V_{SD})$$

parameter: T_j




13 Avalanche characteristics

 $I_{AS}=f(t_{AV}); R_{GS}=25\ \Omega$


parameter: $T_{j(\text{start})}$


14 Typ. gate charge


 $V_{GS}=f(Q_{gate}); I_D=-70\ \text{A pulsed}$

parameter: V_{DD}


15 Drain-source breakdown voltage


 $V_{BR(DSS)}=f(T_j); I_D=-250\ \mu\text{A}$


16 Gate charge waveforms




Package Outline


PG-TO252-3



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	2.16	2.41	0.085	0.095
A1	0.00	0.15	0.000	0.006
b	0.64	0.89	0.025	0.035
b2	0.65	1.15	0.026	0.045
b3	5.00	5.50	0.197	0.217
c	0.46	0.60	0.018	0.024
c2	0.46	0.98	0.018	0.039
D	5.97	6.22	0.235	0.245
D1	5.02	5.84	0.198	0.230
E	6.40	6.73	0.252	0.265
E1	4.70	5.21	0.185	0.205
e	2.29		0.090	
e1	4.57		0.180	
N	3		3	
H	9.40	10.48	0.370	0.413
L	1.18	1.70	0.046	0.067
L3	0.90	1.25	0.035	0.049
L4	0.51	1.00	0.020	0.039
F1	10.50	10.70	0.413	0.421
F2	6.30	6.50	0.248	0.256
F3	2.10	2.30	0.083	0.091
F4	5.70	5.90	0.224	0.232
F5	5.66	5.86	0.223	0.231
F6	1.10	1.30	0.043	0.051

DOCUMENT NO.
Z8B00003328

SCALE


EUROPEAN PROJECTION


ISSUE DATE
19-10-2007

REVISION
03

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2008 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[IPD042P03L3 G](#) [IPD042P03L3GBTMA1](#) [IPD042P03L3GATMA1](#)