

DSO-8 / TSON-8 CAN Demoboard

User Manual

[Family
overview](#)[Support](#)

About this document

Scope and purpose

This document provides description and information for the DSO-8 / TSON-8 CAN Demoboard. This demoboard can be used for all Infineon 8-pin standard CAN transceivers.

An overview of all products that can be evaluated by the DSO-8 / TSON-8 Demoboard can be found in the family overview link above.

Note: The following information is given as a hint for the implementation of our devices only and shall not be regarded as a description or warranty of a certain functionality, condition or quality of the device.

Intended audience

This document is intended for engineers who develop applications.

Table of contents

About this document..... 1

Table of contents..... 2

1 Summary 3

2 General Function..... 4

3 Schematic and PCB Layout 5

Revision history..... 7

1 Summary

This document is guideline for the HS CAN transceiver demoboard DSO-8/ TSON-8 from Infineon Technologies AG and provides information for the proper usage of the demoboard.

The demoboard can be used for all standard HS CAN transceiver on the market, which fulfill the OEM required standard pinout for DSO-8 or TSON-8 package (see Figure 1).




Figure 1 Pin-out of standard 8-pin CAN transceiver

2 General Function

The demoboard can be used for various test cases and various HS CAN transceiver. Power supply failures can be simulated as well as different modes of operation. A configurable bus load on CANH and CANL allows to evaluate the signal form depending on the bus load (standard termination and split termination).

The demoboard should be used to evaluate existing and new CAN transceivers on the market. Advantages, risks and disadvantages of competitor devices versus Infineon devices can be tested and measured.



Figure 2 Photo of the DSO-8 / TSON-8 CAN Demoboard

3 Schematic and PCB Layout




Figure 3 Schematic of DSO-8 / TSON-8 CAN Demoboard




Figure 4 PCB layout of TLE925X demoboard (Top + Bottom)

Table 1 Bill of Material

Part	Value	Device	Package
C1	100nF	Capacitor	C0805
C2	4.7nF	Capacitor	trough hole capacitor (0.05 inch diameter)
C7	100nF	Capacitor	C0805
C8	n.b.	Optional Capacitor	C0805
JP1	-	Header Row	
JP1	-	Header Row	
JP5	-	GND Connection for Oscilloscope	
R1	60	Resistor	trough hole resistor (0.05 inch diameter)
R2	60	Resistor	trough hole resistor (0.05 inch diameter)
TP1 - TP7		Test Points	p1-13 (0.05 inch diameter)
US1	100μH	Common Mode Choke	5.9mm x 3.4mm
US3		CAN Transceiver (e.g. TLE9251V)	PG-DSO-8 / PGTSON-8
X1 - X3		Connector	W237-132 (0.2 inch pitch)

Revision history

Revision	Date of release	Description of changes
1.1	2022-03-15	Editorial changes, inserting hyperlinks, updating of applicable products
1.0	2018-07-31	Initial release

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2022-03-15

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2022 Infineon Technologies AG.

All Rights Reserved.

Do you have a question about this document?

Email: erratum@infineon.com

Document reference

Z8F62791012

IMPORTANT NOTICE

The information contained in this application note is given as a hint for the implementation of the product only and shall in no event be regarded as a description or warranty of a certain functionality, condition or quality of the product. Before implementation of the product, the recipient of this application note must verify any function and other technical information given herein in the real application. Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind (including without limitation warranties of non-infringement of intellectual property rights of any third party) with respect to any and all information given in this application note.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[DSO8CANBOARDTOBO1](#)