

IRF1010ZPbF  
IRF1010ZSPbF  
IRF1010ZLPbF


### Features

- Advanced Process Technology
- Ultra Low On-Resistance
- 175°C Operating Temperature
- Fast Switching
- Repetitive Avalanche Allowed up to  $T_{jmax}$
- Lead-Free

### Description

This HEXFET® Power MOSFET utilizes the latest processing techniques to achieve extremely low on-resistance per silicon area. Additional features of this design are a 175°C junction operating temperature, fast switching speed and improved repetitive avalanche rating. These features combine to make this design an extremely efficient and reliable device for use in a wide variety of applications.


### HEXFET® Power MOSFET



$$V_{DS} = 55V$$

$$R_{DS(on)} = 7.5m\Omega$$

$$I_D = 75A$$



TO-220AB  
IRF1010ZPbF

D²Pak  
IRF1010ZSPbF

TO-262  
IRF1010ZLPbF

### Absolute Maximum Ratings

|                              | Parameter                                                  | Max.                     | Units |
|------------------------------|------------------------------------------------------------|--------------------------|-------|
| $I_D$ @ $T_C = 25^\circ C$   | Continuous Drain Current, $V_{GS}$ @ 10V (Silicon Limited) | 94                       | A     |
| $I_D$ @ $T_C = 100^\circ C$  | Continuous Drain Current, $V_{GS}$ @ 10V                   | 66                       |       |
| $I_D$ @ $T_C = 25^\circ C$   | Continuous Drain Current, $V_{GS}$ @ 10V (Package Limited) | 75                       |       |
| $I_{DM}$                     | Pulsed Drain Current ①                                     | 360                      |       |
| $P_D$ @ $T_C = 25^\circ C$   | Power Dissipation                                          | 140                      | W     |
|                              | Linear Derating Factor                                     | 0.90                     | W/°C  |
| $V_{GS}$                     | Gate-to-Source Voltage                                     | $\pm 20$                 | V     |
| $E_{AS}$ (Thermally limited) | Single Pulse Avalanche Energy ②                            | 130                      | mJ    |
| $E_{AS}$ (Tested)            | Single Pulse Avalanche Energy Tested Value ⑥               | 180                      |       |
| $I_{AR}$                     | Avalanche Current ①                                        | See Fig.12a, 12b, 15, 16 | A     |
| $E_{AR}$                     | Repetitive Avalanche Energy ⑤                              |                          | mJ    |
| $T_J$                        | Operating Junction and                                     | -55 to + 175             | °C    |
| $T_{STG}$                    | Storage Temperature Range                                  |                          |       |
|                              | Soldering Temperature, for 10 seconds                      | 300 (1.6mm from case)    |       |
|                              | Mounting Torque, 6-32 or M3 screw ⑦                        | 10 lbf•in (1.1N•m)       |       |

### Thermal Resistance


|                 | Parameter                            | Typ. | Max. | Units |
|-----------------|--------------------------------------|------|------|-------|
| $R_{\theta JC}$ | Junction-to-Case                     | —    | 1.11 | °C/W  |
| $R_{\theta CS}$ | Case-to-Sink, Flat Greased Surface ⑦ | 0.50 | —    |       |
| $R_{\theta JA}$ | Junction-to-Ambient ⑦                | —    | 62   |       |
| $R_{\theta JA}$ | Junction-to-Ambient (PCB Mount) ⑧    | —    | 40   |       |


## Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

|                                 | Parameter                            | Min. | Typ.  | Max. | Units | Conditions                                                 |
|---------------------------------|--------------------------------------|------|-------|------|-------|------------------------------------------------------------|
| $V_{(BR)DSS}$                   | Drain-to-Source Breakdown Voltage    | 55   | —     | —    | V     | $V_{GS} = 0V, I_D = 250\mu A$                              |
| $\Delta V_{(BR)DSS}/\Delta T_J$ | Breakdown Voltage Temp. Coefficient  | —    | 0.049 | —    | V/°C  | Reference to $25^\circ\text{C}$ , $I_D = 1mA$              |
| $R_{DS(on)}$                    | Static Drain-to-Source On-Resistance | —    | 5.8   | 7.5  | mΩ    | $V_{GS} = 10V, I_D = 75A$ ③                                |
| $V_{GS(th)}$                    | Gate Threshold Voltage               | 2.0  | —     | 4.0  | V     | $V_{DS} = V_{GS}, I_D = 250\mu A$                          |
| $g_{fs}$                        | Forward Transconductance             | 33   | —     | —    | S     | $V_{DS} = 25V, I_D = 75A$                                  |
| $I_{DSS}$                       | Drain-to-Source Leakage Current      | —    | —     | 20   | μA    | $V_{DS} = 55V, V_{GS} = 0V$                                |
|                                 |                                      | —    | —     | 250  |       | $V_{DS} = 55V, V_{GS} = 0V, T_J = 125^\circ\text{C}$       |
| $I_{GSS}$                       | Gate-to-Source Forward Leakage       | —    | —     | 200  | nA    | $V_{GS} = 20V$                                             |
|                                 | Gate-to-Source Reverse Leakage       | —    | —     | -200 |       | $V_{GS} = -20V$                                            |
| $Q_g$                           | Total Gate Charge                    | —    | 63    | 95   | nC    | $I_D = 75A$                                                |
| $Q_{gs}$                        | Gate-to-Source Charge                | —    | 19    | —    |       | $V_{DS} = 44V$                                             |
| $Q_{gd}$                        | Gate-to-Drain ("Miller") Charge      | —    | 24    | —    |       | $V_{GS} = 10V$ ③                                           |
| $t_{d(on)}$                     | Turn-On Delay Time                   | —    | 18    | —    | ns    | $V_{DD} = 28V$                                             |
| $t_r$                           | Rise Time                            | —    | 150   | —    |       | $I_D = 75A$                                                |
| $t_{d(off)}$                    | Turn-Off Delay Time                  | —    | 36    | —    |       | $R_G = 6.8\Omega$                                          |
| $t_f$                           | Fall Time                            | —    | 92    | —    | nH    | $V_{GS} = 10V$ ③                                           |
| $L_D$                           | Internal Drain Inductance            | —    | 4.5   | —    |       | Between lead,                                              |
| $L_S$                           | Internal Source Inductance           | —    | 7.5   | —    |       | 6mm (0.25in.)<br>from package<br>and center of die contact |
| $C_{iss}$                       | Input Capacitance                    | —    | 2840  | —    | pF    | $V_{GS} = 0V$                                              |
| $C_{oss}$                       | Output Capacitance                   | —    | 420   | —    |       | $V_{DS} = 25V$                                             |
| $C_{rss}$                       | Reverse Transfer Capacitance         | —    | 250   | —    |       | $f = 1.0MHz$                                               |
| $C_{oss}$                       | Output Capacitance                   | —    | 1630  | —    |       | $V_{GS} = 0V, V_{DS} = 1.0V, f = 1.0MHz$                   |
| $C_{oss}$                       | Output Capacitance                   | —    | 360   | —    |       | $V_{GS} = 0V, V_{DS} = 44V, f = 1.0MHz$                    |
| $C_{oss\ eff.}$                 | Effective Output Capacitance         | —    | 560   | —    |       | $V_{GS} = 0V, V_{DS} = 0V \text{ to } 44V$ ④               |


## Source-Drain Ratings and Characteristics

|          | Parameter                                 | Min.                                                                      | Typ. | Max. | Units | Conditions                                                              |
|----------|-------------------------------------------|---------------------------------------------------------------------------|------|------|-------|-------------------------------------------------------------------------|
| $I_S$    | Continuous Source Current<br>(Body Diode) | —                                                                         | —    | 75   | A     | MOSFET symbol<br>showing the<br>integral reverse<br>p-n junction diode. |
| $I_{SM}$ | Pulsed Source Current<br>(Body Diode) ①   | —                                                                         | —    | 360  |       |                                                                         |
| $V_{SD}$ | Diode Forward Voltage                     | —                                                                         | —    | 1.3  | V     | $T_J = 25^\circ\text{C}, I_S = 75A, V_{GS} = 0V$ ③                      |
| $t_{rr}$ | Reverse Recovery Time                     | —                                                                         | 22   | 33   | ns    | $T_J = 25^\circ\text{C}, I_F = 75A, V_{DD} = 25V$                       |
| $Q_{rr}$ | Reverse Recovery Charge                   | —                                                                         | 15   | 23   | nC    | $di/dt = 100A/\mu s$ ③                                                  |
| $t_{on}$ | Forward Turn-On Time                      | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S+L_D$ ) |      |      |       |                                                                         |







**Fig 1.** Typical Output Characteristics



**Fig 2.** Typical Output Characteristics




**Fig 3.** Typical Transfer Characteristics




**Fig 4.** Typical Forward Transconductance Vs. Drain Current

# IRF1010Z/S/LPbF


International  
**IR** Rectifier




**Fig 5.** Typical Capacitance Vs. Drain-to-Source Voltage






**Fig 6.** Typical Gate Charge Vs. Gate-to-Source Voltage



**Fig 7.** Typical Source-Drain Diode Forward Voltage




**Fig 8.** Maximum Safe Operating Area




# IRF1010Z/S/LPbF


International  
**IR** Rectifier




**Fig 12a.** Unclamped Inductive Test Circuit




**Fig 12b.** Unclamped Inductive Waveforms




**Fig 13a.** Basic Gate Charge Waveform



**Fig 13b.** Gate Charge Test Circuit




**Fig 12c.** Maximum Avalanche Energy Vs. Drain Current




**Fig 14.** Threshold Voltage Vs. Temperature

[www.irf.com](http://www.irf.com)



**Fig 15.** Typical Avalanche Current Vs. Pulsewidth



**Fig 16.** Maximum Avalanche Energy Vs. Temperature


**Notes on Repetitive Avalanche Curves , Figures 15, 16:**  
(For further info, see AN-1005 at [www.irf.com](http://www.irf.com))

1. Avalanche failures assumption:  
Purely a thermal phenomenon and failure occurs at a temperature far in excess of  $T_{jmax}$ . This is validated for every part type.
2. Safe operation in Avalanche is allowed as long as  $T_{jmax}$  is not exceeded.
3. Equation below based on circuit and waveforms shown in Figures 12a, 12b.
4.  $P_{D(ave)}$  = Average power dissipation per single avalanche pulse.
5. BV = Rated breakdown voltage (1.3 factor accounts for voltage increase during avalanche).
6.  $I_{av}$  = Allowable avalanche current.
7.  $\Delta T$  = Allowable rise in junction temperature, not to exceed  $T_{jmax}$  (assumed as 25°C in Figure 15, 16).  
 $t_{av}$  = Average time in avalanche.  
 $D$  = Duty cycle in avalanche =  $t_{av} \cdot f$   
 $Z_{thJC}(D, t_{av})$  = Transient thermal resistance, see figure 11)


$$P_{D(ave)} = \frac{1}{2} (1.3 \cdot BV \cdot I_{av}) = \Delta T / Z_{thJC}$$

$$I_{av} = 2\Delta T / [1.3 \cdot BV \cdot Z_{th}]$$


$$E_{AS(AR)} = P_{D(ave)} \cdot t_{av}$$



**Fig 17. Peak Diode Recovery  $dv/dt$  Test Circuit for N-Channel HEXFET® Power MOSFETs**



**Fig 18a. Switching Time Test Circuit**




**Fig 18b. Switching Time Waveforms**



## TO-220AB Package Outline

Dimensions are shown in millimeters (inches)



### NOTES:

- 1.- DIMENSIONING AND TOLERANCING AS PER ASME Y14.5 M- 1994.
- 2.- DIMENSIONS ARE SHOWN IN INCHES (MILLIMETERS).
- 3.- LEAD DIMENSION AND FINISH UNCONTROLLED IN L1.
- 4.- DIMENSION D, D1 & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED .005" (0.127) PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 5.- DIMENSION b1, b3 & c1 APPLY TO BASE METAL ONLY.
- 6.- CONTROLLING DIMENSION - INCHES.
- 7.- THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS E, H1, D2 & E1.
- 8.- DIMENSION E2 X H1 DEFINE A ZONE WHERE STAMPING AND SINGULATION IRREGULARITIES ARE ALLOWED.
- 9.- OUTLINE CONFORMS TO JEDEC TO-220, EXCEPT A2 (max.) AND D2 (min.) WHERE DIMENSIONS ARE DERIVED FROM THE ACTUAL PACKAGE OUTLINE.

| SYMBOL | DIMENSIONS  |       |          |      | NOTES |
|--------|-------------|-------|----------|------|-------|
|        | MILLIMETERS |       | INCHES   |      |       |
|        | MIN.        | MAX.  | MIN.     | MAX. |       |
| A      | 3.56        | 4.83  | .140     | .190 |       |
| A1     | 0.51        | 1.40  | .020     | .055 |       |
| A2     | 2.03        | 2.92  | .080     | .115 |       |
| b      | 0.38        | 1.01  | .015     | .040 |       |
| b1     | 0.38        | 0.97  | .015     | .038 | 5     |
| b2     | 1.14        | 1.78  | .045     | .070 |       |
| b3     | 1.14        | 1.73  | .045     | .068 | 5     |
| c      | 0.36        | 0.61  | .014     | .024 |       |
| c1     | 0.36        | 0.56  | .014     | .022 | 5     |
| D      | 14.22       | 16.51 | .560     | .650 | 4     |
| D1     | 8.38        | 9.02  | .330     | .355 |       |
| D2     | 11.68       | 12.88 | .460     | .507 | 7     |
| E      | 9.65        | 10.67 | .380     | .420 | 4,7   |
| E1     | 6.86        | 8.89  | .270     | .350 | 7     |
| E2     | -           | 0.76  | -        | .030 | 8     |
| e      | 2.54 BSC    |       | .100 BSC |      |       |
| e1     | 5.08 BSC    |       | .200 BSC |      |       |
| H1     | 5.84        | 6.86  | .230     | .270 | 7,8   |
| L      | 12.70       | 14.73 | .500     | .580 |       |
| L1     | 3.56        | 4.06  | .140     | .160 | 3     |
| HP     | 3.54        | 4.08  | .139     | .161 |       |
| Q      | 2.54        | 3.42  | .100     | .135 |       |

### LEAD ASSIGNMENTS

#### HEXCEL

- 1 - GATE
- 2 - DRAIN
- 3 - SOURCE

#### JEDEC GAPPAGE

- 1 - GATE
- 2 - COLLECTOR
- 3 - EMITTER


#### DIODES

- 1 - ANODE
- 2 - CATHODE
- 3 - ANODE

## TO-220AB Part Marking Information

EXAMPLE: THIS IS AN IRF1010  
LOT CODE 1789  
ASSEMBLED ON WW 19, 2000  
IN THE ASSEMBLY LINE "C"

Note: "P" in assembly line position  
indicates "Lead - Free"



### Notes:


1. For an Automotive Qualified version of this part please see <http://www.irf.com/product-info/datasheets/data/auirf1010z.pdf>
2. For the most current drawing please refer to IR website at <http://www.irf.com/package/>

# IRF1010Z/S/LPbF

International  
**IR** Rectifier

## D<sup>2</sup>Pak (TO-263AB) Package Outline

Dimensions are shown in millimeters (inches)



| SYMBOL | DIMENSIONS  |       |          |      | NOTES |
|--------|-------------|-------|----------|------|-------|
|        | MILLIMETERS |       | INCHES   |      |       |
|        | MIN.        | MAX.  | MIN.     | MAX. |       |
| A      | 4.06        | 4.83  | .160     | .190 | 5     |
| A1     | 0.00        | 0.254 | .000     | .010 |       |
| b      | 0.51        | 0.99  | .020     | .039 |       |
| b1     | 0.51        | 0.89  | .020     | .035 |       |
| b2     | 1.14        | 1.78  | .045     | .070 | 5     |
| b3     | 1.14        | 1.73  | .045     | .068 |       |
| c      | 0.38        | 0.74  | .015     | .029 |       |
| c1     | 0.38        | 0.58  | .015     | .023 | 5     |
| c2     | 1.14        | 1.65  | .045     | .065 | 3     |
| D      | 8.38        | 9.65  | .330     | .380 |       |
| D1     | 6.86        | —     | .270     | —    |       |
| E      | 9.65        | 10.67 | .380     | .420 | 3,4   |
| E1     | 6.22        | —     | .245     | —    | 4     |
| e      | 2.54 BSC    |       | .100 BSC |      | 4     |
| H      | 14.61       | 15.88 | .575     | .625 |       |
| L      | 1.78        | 2.79  | .070     | .110 |       |
| L1     | —           | 1.65  | —        | .066 |       |
| L2     | —           | 1.78  | —        | .070 |       |
| L3     | 0.25 BSC    |       | .010 BSC |      | 4     |
| L4     | 4.78        | 5.28  | .188     | .208 |       |

### LEAD ASSIGNMENTS

#### DIODES

- 1.— ANODE (TWO DIE) / OPEN (ONE DIE)
- 2.— CATHODE
- 3.— ANODE

#### HEXFET

- 1.— GATE
- 2.— DRAIN
- 3.— SOURCE

#### IGBTs, CoPACK

- 1.— GATE
- 2.— COLLECTOR
- 3.— EMITTER


### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [0.005] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY AT DATUM H.
4. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSION E, L1, D1 & E1.
5. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
6. DATUM A & B TO BE DETERMINED AT DATUM PLANE H.
7. CONTROLLING DIMENSION: INCH.
8. OUTLINE CONFORMS TO JEDEC OUTLINE TO-263AB.


## D<sup>2</sup>Pak (TO-263AB) Part Marking Information

EXAMPLE: THIS IS AN IRF530S WITH  
LOT CODE 8024  
ASSEMBLED ON WW 02, 2000  
IN THE ASSEMBLY LINE "L"

Note: "P" in assembly line position  
indicates "Lead - Free"



OR




### Notes:

1. For an Automotive Qualified version of this part please see <http://www.irf.com/product-info/datasheets/data/auirf1010z.pdf>
2. For the most current drawing please refer to IR website at <http://www.irf.com/package/>

## TO-262 Package Outline

Dimensions are shown in millimeters (inches)



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [0.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
4. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSION E, L1, D1 & E1.
5. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
6. CONTROLLING DIMENSION: INCH.
7. OUTLINE CONFORM TO JEDEC TO-262 EXCEPT A1(max.), b(min.) AND D1(min.) WHERE DIMENSIONS DERIVED THE ACTUAL PACKAGE OUTLINE.

| SYMBOL | DIMENSIONS  |       |          |      | NOTES |
|--------|-------------|-------|----------|------|-------|
|        | MILLIMETERS |       | INCHES   |      |       |
|        | MIN.        | MAX.  | MIN.     | MAX. |       |
| A      | 4.06        | 4.83  | .160     | .190 | 5     |
| A1     | 2.03        | 3.02  | .080     | .119 |       |
| b      | 0.51        | 0.99  | .020     | .039 |       |
| b1     | 0.51        | 0.89  | .020     | .035 |       |
| b2     | 1.14        | 1.78  | .045     | .070 |       |
| b3     | 1.14        | 1.73  | .045     | .068 | 5     |
| c      | 0.38        | 0.74  | .015     | .029 |       |
| c1     | 0.38        | 0.58  | .015     | .023 | 5     |
| c2     | 1.14        | 1.65  | .045     | .065 |       |
| D      | 8.38        | 9.65  | .330     | .380 | 3     |
| D1     | 6.86        | —     | .270     | —    | 4     |
| E      | 9.65        | 10.67 | .380     | .420 | 3, 4  |
| E1     | 6.22        | —     | .245     | —    | 4     |
| e      | 2.54 BSC    |       | .100 BSC |      | 4     |
| L      | 13.46       | 14.10 | .530     | .555 |       |
| L1     | —           | 1.65  | —        | .065 |       |
| L2     | 3.56        | 3.71  | .140     | .146 |       |

### LEAD ASSIGNMENTS

#### HEXFET

- 1.- GATE
- 2.- DRAIN
- 3.- SOURCE
- 4.- DRAIN


#### IGBTs, CoPACK

- 1.- GATE
- 2.- COLLECTOR
- 3.- EMITTER
- 4.- COLLECTOR


## TO-262 Part Marking Information

EXAMPLE: THIS IS AN IRL3103L  
LOT CODE 1789  
ASSEMBLED ON WW 19, 1997  
IN THE ASSEMBLY LINE "C"

Note: "P" in assembly line position  
indicates "Lead - Free"



OR



### Notes:


1. For an Automotive Qualified version of this part please see <http://www.irf.com/product-info/datasheets/data/auirf1010z.pdf>
2. For the most current drawing please refer to IR website at <http://www.irf.com/package/>

# IRF1010Z/S/LPbF

International  
**IR** Rectifier

## D<sup>2</sup>Pak Tape & Reel Information

Dimensions are shown in millimeters (inches)



**TO-220AB package is not recommended for Surface Mount Application.**

### Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature. (See fig. 11).
- ② Limited by  $T_{Jmax}$ , starting  $T_J = 25^\circ\text{C}$ ,  $L = 0.05\text{mH}$ ,  $R_G = 25\Omega$ ,  $I_{AS} = 75\text{A}$ ,  $V_{GS} = 10\text{V}$ . Part not recommended for use above this value.
- ③ Pulse width  $\leq 1.0\text{ms}$ ; duty cycle  $\leq 2\%$ .
- ④  $C_{oss}$  eff. is a fixed capacitance that gives the same charging time as  $C_{oss}$  while  $V_{DS}$  is rising from 0 to 80%  $V_{DSS}$ .
- ⑤ Limited by  $T_{Jmax}$ ; see Fig.12a, 12b, 15, 16 for typical repetitive avalanche performance.
- ⑥ This value determined from sample failure population. 100% tested to this value in production.
- ⑦ This is only applied to TO-220AB package.
- ⑧ This is applied to D<sup>2</sup>Pak, when mounted on 1" square PCB (FR-4 or G-10 Material). For recommended footprint and soldering techniques refer to application note #AN-994.

Data and specifications subject to change without notice.  
This product has been designed and qualified for the Industrial market.  
Qualification Standards can be found on IR's Web site.

International  
**IR** Rectifier

**IR WORLD HEADQUARTERS:** 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105  
TAC Fax: (310) 252-7903

Visit us at [www.irf.com](http://www.irf.com) for sales contact information. 07/2010

[www.irf.com](http://www.irf.com)

## IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

## WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[IRF1010ZSPBF](#) [IRF1010ZPBF](#) [IRF1010ZSTRLPBF](#)