

## DirectFET™ dual P-Channel Power MOSFET ②

Typical values (unless otherwise specified)


| $V_{DSS}$    |          | $V_{GS}$  | $R_{DS(on)}$ |           | $R_{DS(on)}$  |
|--------------|----------|-----------|--------------|-----------|---------------|
| -30V max     |          | ±20V max  | 5.3mΩ @ -10V |           | 9.0mΩ @ -4.5V |
| $Q_{g\ tot}$ | $Q_{gd}$ | $Q_{gs2}$ | $Q_{rr}$     | $Q_{oss}$ | $V_{gs(th)}$  |
| 32nC         | 15nC     | 3.2nC     | 62nC         | 23nC      | -1.8V         |

### Applications

- Isolation Switch for Input Power or Battery Application

### Features and Benefits

- Environmentally Friendly Product
- RoHS Compliant Containing no Lead, no Bromide and no Halogen
- Dual Common-Drain P-Channel MOSFETs Provides High Level of Integration and Very Low  $R_{DS(on)}$



Applicable DirectFET Outline and Substrate Outline (see p.7,8 for details)①

|    |    |    |  |    |    |    |    |           |  |  |
|----|----|----|--|----|----|----|----|-----------|--|--|
| SQ | SX | ST |  | MQ | MX | MT | MP | <b>MC</b> |  |  |
|----|----|----|--|----|----|----|----|-----------|--|--|

### Description

The IRF9395MTRPbF combines the latest HEXFET® P-Channel Power MOSFET Silicon technology with the advanced DirectFET™ packaging to achieve the lowest on-state resistance in a package that has the footprint of a SO-8 and only 0.6 mm profile. The DirectFET package is compatible with existing layout geometries used in power applications, PCB assembly equipment and vapor phase, infra-red or convection soldering techniques, when application note AN-1035 is followed regarding the manufacturing methods and processes. The DirectFET package allows dual sided cooling to maximize thermal transfer in power systems, improving previous best thermal resistance by 80%.

| Orderable part number | Package Type         | Standard Pack |          | Note                          |
|-----------------------|----------------------|---------------|----------|-------------------------------|
|                       |                      | Form          | Quantity |                               |
| IRF9395MTRPbF         | DirectFET Medium Can | Tape and Reel | 4800     | "TR" suffix                   |
| IRF9395MTR1PbF        | DirectFET Medium Can | Tape and Reel | 1000     | "TR1" suffix EOL notice # 264 |

### Absolute Maximum Ratings

|                                  | Parameter                                  | Max. | Units |
|----------------------------------|--------------------------------------------|------|-------|
| $V_{DS}$                         | Drain-to-Source Voltage                    | -30  | V     |
| $V_{GS}$                         | Gate-to-Source Voltage                     | ±20  | V     |
| $I_D$ @ $T_A = 25^\circ\text{C}$ | Continuous Drain Current, $V_{GS}$ @ 10V ③ | -14  | A     |
| $I_D$ @ $T_A = 70^\circ\text{C}$ | Continuous Drain Current, $V_{GS}$ @ 10V ③ | -11  | A     |
| $I_D$ @ $T_C = 25^\circ\text{C}$ | Continuous Drain Current, $V_{GS}$ @ 10V ④ | -75  | A     |
| $I_{DM}$                         | Pulsed Drain Current ⑤                     | -110 | A     |




Fig 1. Typical On-Resistance vs. Gate Voltage




Fig 2. Typical Total Gate Charge vs. Gate-to-Source Voltage

#### Notes:

- Click on this section to link to the appropriate technical paper.
- Click on this section to link to the DirectFET Website.
- Surface mounted on 1 in. square Cu board, steady state.

- $T_C$  measured with thermocouple mounted to top (Drain) of part.
- Repetitive rating; pulse width limited by max. junction temperature.

**Static @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**

|                                | Parameter                             | Min. | Typ.  | Max. | Units                      | Conditions                                                                                                          |
|--------------------------------|---------------------------------------|------|-------|------|----------------------------|---------------------------------------------------------------------------------------------------------------------|
| $BV_{DSS}$                     | Drain-to-Source Breakdown Voltage     | -30  | —     | —    | V                          | $V_{GS} = 0V, I_D = -250\mu A$                                                                                      |
| $\Delta BV_{DSS}/\Delta T_J$   | Breakdown Voltage Temp. Coefficient   | —    | 0.012 | —    | V/ $^\circ\text{C}$        | Reference to $25^\circ\text{C}, I_D = -1.0\text{mA}$                                                                |
| $R_{DS(on)}$                   | Static Drain-to-Source On-Resistance  | —    | 5.3   | 7.0  | $\text{m}\Omega$           | $V_{GS} = -10V, I_D = -14A$ ⑥                                                                                       |
|                                |                                       | —    | 9.0   | 11.9 |                            | $V_{GS} = -4.5V, I_D = -11A$ ⑥                                                                                      |
| $V_{GS(th)}$                   | Gate Threshold Voltage                | -1.3 | -1.8  | -2.4 | V                          | $V_{DS} = V_{GS}, I_D = -50\mu A$                                                                                   |
| $\Delta V_{GS(th)}/\Delta T_J$ | Gate Threshold Voltage Coefficient    | —    | -6.1  | —    | $\text{mV}/^\circ\text{C}$ |                                                                                                                     |
| $I_{DSS}$                      | Drain-to-Source Leakage Current       | —    | —     | -1.0 | $\mu A$                    | $V_{DS} = -24V, V_{GS} = 0V$                                                                                        |
|                                |                                       | —    | —     | -150 |                            | $V_{DS} = -24V, V_{GS} = 0V, T_J = 125^\circ\text{C}$                                                               |
| $I_{GSS}$                      | Gate-to-Source Forward Leakage        | —    | —     | -100 | $\text{nA}$                | $V_{GS} = -20V$                                                                                                     |
|                                | Gate-to-Source Reverse Leakage        | —    | —     | 100  |                            | $V_{GS} = 20V$                                                                                                      |
| $g_{fs}$                       | Forward Transconductance              | 40   | —     | —    | S                          | $V_{DS} = -15V, I_D = -11A$                                                                                         |
| $Q_g$                          | Total Gate Charge                     | —    | 64    | —    | $\text{nC}$                | $V_{DS} = -15V, V_{GS} = -10V, I_D = -11A$<br><br>$V_{DS} = -15V$<br>$V_{GS} = -4.5V$<br>$I_D = -11A$<br>See Fig.15 |
| $Q_g$                          | Total Gate Charge                     | —    | 32    | —    |                            |                                                                                                                     |
| $Q_{gs1}$                      | Pre- $V_{th}$ Gate-to-Source Charge   | —    | 6.5   | —    |                            |                                                                                                                     |
| $Q_{gs2}$                      | Post - $V_{th}$ Gate-to-Source Charge | —    | 3.2   | —    |                            |                                                                                                                     |
| $Q_{gd}$                       | Gate-to-Drain Charge                  | —    | 15    | —    |                            |                                                                                                                     |
| $Q_{godr}$                     | Gate Charge Overdrive                 | —    | 7.3   | —    |                            |                                                                                                                     |
| $Q_{sw}$                       | Switch charge ( $Q_{gs2} + Q_{gd}$ )  | —    | 18.2  | —    |                            |                                                                                                                     |
| $Q_{oss}$                      | Output Charge                         | —    | 23    | —    | $\text{nC}$                | $V_{DS} = -16V, V_{GS} = 0V$                                                                                        |
| $R_G$                          | Gate Resistance                       | —    | 15    | —    | $\Omega$                   |                                                                                                                     |
| $t_{d(on)}$                    | Turn-On Delay Time                    | —    | 16    | —    | $\text{ns}$                | $V_{DD} = -15V, V_{GS} = -4.5V$ ⑥<br>$I_D = -11A$<br>$R_G = 1.8\Omega$<br>See Fig.17                                |
| $t_r$                          | Rise Time                             | —    | 142   | —    |                            |                                                                                                                     |
| $t_{d(off)}$                   | Turn-Off Delay Time                   | —    | 76    | —    |                            |                                                                                                                     |
| $t_f$                          | Fall Time                             | —    | 121   | —    |                            |                                                                                                                     |
| $C_{iss}$                      | Input Capacitance                     | —    | 3241  | —    | $\text{pF}$                | $V_{GS} = 0V$<br>$V_{DS} = -15V$<br>$f = 1.0\text{KHz}$                                                             |
| $C_{oss}$                      | Output Capacitance                    | —    | 820   | —    |                            |                                                                                                                     |
| $C_{rss}$                      | Reverse Transfer Capacitance          | —    | 466   | —    |                            |                                                                                                                     |

**Diode Characteristics**

|          | Parameter                                 | Min. | Typ. | Max. | Units | Conditions                                                              |
|----------|-------------------------------------------|------|------|------|-------|-------------------------------------------------------------------------|
| $I_S$    | Continuous Source Current<br>(Body Diode) | —    | —    | -57  | A     | MOSFET symbol<br>showing the<br>integral reverse<br>p-n junction diode. |
| $I_{SM}$ | Pulsed Source Current<br>(Body Diode) ⑤   | —    | —    | -110 |       |                                                                         |
| $V_{SD}$ | Diode Forward Voltage                     | —    | —    | -1.2 | V     | $T_J = 25^\circ\text{C}, I_S = -11A, V_{GS} = 0V$ ⑥                     |
| $t_{rr}$ | Reverse Recovery Time                     | —    | 43   | 65   | ns    | $T_J = 25^\circ\text{C}, I_F = -11A, V_{DD} = -15V$                     |
| $Q_{rr}$ | Reverse Recovery Charge                   | —    | 62   | 93   | nC    | $di/dt = 260A/\mu s$ ⑥                                                  |

**Notes:**


 ⑥ Pulse width  $\leq 400\mu s$ ; duty cycle  $\leq 2\%$ .

### Absolute Maximum Ratings

|                                  | Parameter                  | Max.         | Units            |
|----------------------------------|----------------------------|--------------|------------------|
| $P_D$ @ $T_A = 25^\circ\text{C}$ | Power Dissipation ③        | 2.1          | W                |
| $P_D$ @ $T_A = 70^\circ\text{C}$ | Power Dissipation ③        | 1.3          |                  |
| $P_D$ @ $T_C = 25^\circ\text{C}$ | Power Dissipation ④        | 57           |                  |
| $T_P$                            | Peak Soldering Temperature | 270          | $^\circ\text{C}$ |
| $T_J$                            | Operating Junction and     | -40 to + 150 |                  |
| $T_{STG}$                        | Storage Temperature Range  |              |                  |

### Thermal Resistance




|                    | Parameter                | Typ. | Max. | Units               |
|--------------------|--------------------------|------|------|---------------------|
| $R_{\theta JA}$    | Junction-to-Ambient ③    | —    | 60   | $^\circ\text{C/W}$  |
| $R_{\theta JA}$    | Junction-to-Ambient ⑦    | 12.5 | —    |                     |
| $R_{\theta JA}$    | Junction-to-Ambient ⑧    | 20   | —    |                     |
| $R_{\theta JC}$    | Junction-to-Case ④,⑨     | —    | 2.2  |                     |
| $R_{\theta J-PCB}$ | Junction-to-PCB Mounted  | 1.0  | —    |                     |
|                    | Linear Derating Factor ③ | 0.02 |      | W/ $^\circ\text{C}$ |



**Fig 3.** Maximum Effective Transient Thermal Impedance, Junction-to-Ambient ①

#### Notes:







- ⑦ Used double sided cooling, mounting pad with large heatsink.  
 ⑧ Mounted on minimum footprint full size board with metalized back and with small clip heatsink.  
 ⑨  $R_\theta$  is measured at  $T_J$  of approximately  $90^\circ\text{C}$ .














③ Surface mounted on 1 in. square Cu board (still air).


⑧ Mounted to a PCB with small clip heatsink (still air)

⑨ Mounted on minimum footprint full size board with metalized back and with small clip heatsink (still air)


**Fig 4.** Typical Output Characteristics

**Fig 5.** Typical Output Characteristics

**Fig 6.** Typical Transfer Characteristics

**Fig 7.** Normalized On-Resistance vs. Temperature

**Fig 8.** Typical Capacitance vs. Drain-to-Source Voltage

**Fig 9.** Typical On-Resistance vs. Drain Current and Gate Voltage




**Fig 15a.** Gate Charge Test Circuit

**Fig 15b.** Gate Charge Waveform

**Fig 16a.** Unclamped Inductive Test Circuit

**Fig 16b.** Unclamped Inductive Waveforms

**Fig 17a.** Switching Time Test Circuit

**Fig 17b.** Switching Time Waveforms




**Fig 18. Diode Reverse Recovery Test Circuit for N-Channel HEXFET® Power MOSFETs**

## DirectFET™ Board Footprint, MC Outline (Medium Size Can, C-Designation).

Please see DirectFET application note AN-1035 for all details regarding the assembly of DirectFET.


This includes all recommendations for stencil and substrate designs.



Note: For the most current drawing please refer to IR website at: <http://www.irf.com/package/>


## DirectFET™ Outline Dimension, MC Outline (Medium Size Can, C-Designation).

Please see DirectFET application note AN-1035 for all details regarding the assembly of DirectFET. This includes all recommendations for stencil and substrate designs.




| DIMENSIONS |        |      |          |       |
|------------|--------|------|----------|-------|
| CODE       | METRIC |      | IMPERIAL |       |
|            | MIN    | MAX  | MIN      | MAX   |
| A          | 6.25   | 6.35 | 0.246    | 0.250 |
| B          | 4.80   | 5.05 | 0.189    | 0.201 |
| C          | 3.85   | 3.95 | 0.152    | 0.156 |
| D          | 0.35   | 0.45 | 0.014    | 0.018 |
| E          | 0.58   | 0.62 | 0.023    | 0.024 |
| F          | 0.58   | 0.62 | 0.023    | 0.024 |
| G          | 0.58   | 0.62 | 0.023    | 0.024 |
| H          | 1.18   | 1.22 | 0.047    | 0.048 |
| J          | 0.56   | 0.60 | 0.022    | 0.023 |
| J1         | 1.98   | 2.02 | 0.078    | 0.079 |
| K          | 1.02   | 1.06 | 0.040    | 0.041 |
| L          | 2.22   | 2.26 | 0.088    | 0.089 |
| M          | 0.59   | 0.70 | 0.023    | 0.028 |
| N          | 0.03   | 0.08 | 0.001    | 0.003 |
| P          | 0.08   | 0.17 | 0.003    | 0.007 |

## DirectFET™ Part Marking



Note: For the most current drawing please refer to IR website at: <http://www.irf.com/package/>

# DirectFET™ Tape & Reel Dimension (Showing component orientation).



Note: For the most current drawing please refer to IR website at: <http://www.irf.com/package/>

## Qualification Information†

|                            |                                  |                                  |
|----------------------------|----------------------------------|----------------------------------|
| Qualification level        | Industrial†                      |                                  |
|                            | (per JEDEC JESD47F†† guidelines) |                                  |
| Moisture Sensitivity Level | DirectFET                        | MSL1<br>(per JEDEC J-STD-020D††) |
| RoHS Compliant             | Yes                              |                                  |

† Qualification standards can be found at International Rectifier's web site <http://www.irf.com/product-info/reliability>

†† Applicable version of JEDEC standard at the time of product release.

## Revision History

| Date       | Comments                                                                                                                                                                           |
|------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 10/25/2013 | <ul style="list-style-type: none"> <li>Updated Qualification level from "Consumer" to "Industrial" on page 9</li> <li>Updated data sheet with new IR corporate template</li> </ul> |
| 2/24/2014  | <ul style="list-style-type: none"> <li>Updated ordering information to reflect the End-Of-life (EOL) of the mini-reel option (EOL notice #264)</li> </ul>                          |

International  
 Rectifier

IR WORLD HEADQUARTERS: 101 N. Sepulveda Blvd., El Segundo, California 90245, USA

To contact International Rectifier, please visit <http://www.irf.com/whoto-call/>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[IRF9395MTR1PBF](#)