









Technical drawing of a mechanical part with dimensions:

- Overall width: 5.4
- Top width: ± 0.15
- Inner width: 3
- Inner width tolerance: ± 0.15
- Inner width tolerance: 2.0
- Overall height: 4
- Height tolerance: ± 0.15
- Bottom width: 4.2
- Bottom width tolerance: ± 0.15
- Left side dimension: (0.6)
- Right side dimension: (0.6)



(SCALE 10:1)



MATED CONDITION (REF.)
(SCALE 10:1)

TABLE 1


NO. OF CONTACTS(N)	A	B	C	D
30	7.0	9.0	10.0	9.5
40	9.5	11.5	12.5	12.0
50	12.0	14.0	15.0	14.5
60	14.5	16.5	17.5	17.0
70	17.0	19.0	20.0	19.5
80	19.5	21.5	22.5	22.0
120	29.5	31.5	32.5	32.0
160	39.5	41.5	42.5	42.0

TABLE 2

FINISH	CONTACT AREA	TERMINAL AREA
N 1	GOLD(0.1 μ m MIN) OVER NICKEL	GOLD FLASH OVER NICKEL

NOTE 1. COPLANARITY IS AS PER
APPLICABLE SPECIFICATION.

注1. 端子の振れ規定は適用仕様書による。

2	INSULATOR	1	GLASS FILLED PPS			UL94V-0 COLOR:BLACK
1	CONTACT	TABLE 1	PHOSPHOR BRONZE	TABLE 2		
符 号 NO.	名 称 DESCRIPTION	個 数 QTY.	材 料 MATERIAL	仕 上 FINISH	備 考 REMARKS	
仕様書 (SPECIFICATION)		第1版 (ORIGINAL DATE)		尺 度 (SCALE)	シリーズ (SERIES)	日本航空電子工業株式会社 JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.
JACS-1385-*		4.Dec.2003		5:1	WR	
公差 (GENERAL TOLERANCE)		製図 DR.	M.TANAKA	名称 (TITLE)	Reference Only	
寸法 (DIMENSION)		担当 CHK.	T.SHIODA	WR-*PB-VF50-N1		
角度 (ANGLES)		査閲 APPD.	K. Kawada			
. ± 0.8		承認 APPD.	S. Kashinaga			
.X ± 0.4						
.XX ± 0.1				重量 (WEIGHT)		
.XXX ±					図面番号 (DRAWING NO.) SJ100361	

LEAD FREE この製品は鉛フリー品です

JAE CONNECTOR DIV. PROPRIETARY.
COPYRIGHT (C) 2003, JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[WR-60PB-VF50-N1-R1300](#) [WR-160PB-VF50-N1-R1300](#) [WR-50PB-VF50-N1](#) [WR-70PB-VF50-N1](#) [WR-80PB-VF50-](#)
[N1](#)