


JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
E6522	6.0	.030	.025	0.31	10,000	C-2V
E79	6.0	.200	.600	7.54	1,000	C-2R
E84	6.3	.040	.030	0.40	20,000	C-2V
E86	6.3	.200	.400	5.03	20,000	C-2V
E12522	12.0	.030	.045	0.57	10,000	C-2F
E21203A	12.0	.100	.640	8.04	2,000	C-2V
E73	14.0	.080	.300	3.77	15,000	C-2V
E37	14.0	.090	.500	6.29	1,500	C-2F
E74	14.0	.100	.720	9.05	1,000	C-2V
E13522	24.0	.030	.160	2.01	5,000	C-2F
E85	28.0	.040	.300	3.77	10,000	C-2F
E17	28.0	.065	.650	8.17	5,000	C-2F

METRIC



THIRD ANGLE
PROJECTION

DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED

1 PL +/- 0.2
2 PL +/- 0.20
ANGLE +/- 0

JKL

COMPONENTS CORPORATION

TITLE

T-1 1/2 STANDARD GLASS WEDGE BASE

C DELETE * NOTE 7/6/11

B ADD DIM OVER WIRE, E84 LUMENS TO 0.40 12/1/10

A Pb FREE NOTE ADDED 8/25/04

RELEASED & CANCEL GW-STD-T1 1/2 5/5/00

REV. NO. DESCRIPTION/ECO NUMBER APPVD DATE

DRAWN BY
L. WENGSTROM

APPVD BY
L.W.

DATE
7/6/11

SIZE
A

FSCM NO.
55335

DRAWING
NO.

GLASS WEDGE BASE T-1 1/2

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

SCALE

NONE

RELEASED
DATE

5/5/00

REVISION
DATE

7/6/11

REV.
NO. C

SHEET
1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[E12522](#) [E17](#)