


JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	MSCP $\pm 25\%$	LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
1680	6.0	4.10	32.0	402.2	300	C-6
1295	12.5	3.00	50.0	628.5	300	C-2R
93	12.8	1.04	15.0	188.6	700	C-6
1156	12.8	2.10	32.0	402.2	1,200	C-6
305	28.0	.51	15.0	188.6	300	*C-2V
1691	28.0	.61	15.0	188.6	1,000	2C-2R
2232	28.0	.643	17.0	213.7	2,000	CC-8
307	28.0	.67	21.0	264.0	300	*C-2V
2233	28.0	.77	21.0	264.0	2,000	CC-8
1683	28.0	1.02	32.0	402.2	500	2C-6

* SUPPORTED

			<div>METRIC</div> <div></div> <div>THIRD ANGLE PROJECTION</div>		<div>DIMENSIONS ARE IN MILLIMETERS</div> <div>TOLERANCE UNLESS OTHERWISE SPECIFIED</div> <div>1 PL +/- 0.2</div> <div>2 PL +/- 0.20</div> <div>ANGLE +/- 0</div>		<div>JKL COMPONENTS CORPORATION</div>																	
							TITLE																	
							S-8 SINGLE CONTACT BAYONET BASE LAMP																	
B			DELETE PART NO'S 1073 & 1665		4/28/04		DRAWN BY		APPV'D BY		DATE		SIZE		FSCM NO.		DRAWING NO.		BAYONET SINGLE CONTACT S-8					
A			ADD PART NO. 2233		1/27/03		L. WENGSTROM		J.K.		4/28/04		A		55335									
			RELEASED AS CAD		5/4/01																			
REV. NO.		DESCRIPTION/ECO NUMBER				APPV'D DATE		- CAD DRAWING -						SCALE		RELEASED DATE		REVISION DATE		REV. NO.		SHEET		
								MANUAL REVISIONS NOT PERMITTED						NONE		5/4/01		4/28/04		B		1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[1156](#) [1295](#) [2232](#) [2233](#)