



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
11	2.5	.200	.200	2.51	500	C-2R
56	5.0	.115	.150	1.89	40,000	C-2R
79	6.0	.200	.630	7.92	1,000	C-2R
86	6.3	.200	.400	5.03	50,000	C-2F
18*	14.0	.040	.130	1.63	5,000	C-2F
73*	14.0	.080	.300	3.77	15,000	C-2F
37	14.0	.090	.500	6.29	2,500	C-2F
74	14.0	.100	.700	8.80	500	C-2F
85	28.0	.040	.300	3.77	25,000	C-2F
17	28.0	.065	.650	8.17	5,000	C-2F

*LAMP LEAD (Pb) FREE

CONTACT JKL FOR LEAD (Pb) FREE LOT IDENTIFICATION.

<p>METRIC DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0</p> <p>THIRD ANGLE PROJECTION</p>	<p>JKL COMPONENTS CORPORATION</p>	
	<p>TITLE T-1 3/4 STANDARD GLASS WEDGE BASE</p>	
<p>B CHANGE #18 TO LEAD (Pb) FREE 7/12/05</p> <p>A NOTE #73 TO LEAD (Pb) FREE 2/17/05</p> <p>RELEASED & CANCEL GW-STD-T1 3/4, 75X & 84 5/11/00</p>	<p>DRAWN BY L. WENGSTROM</p> <p>APPVD BY J.K. DATE 7/12/05</p>	<p>SIZE A</p> <p>FSCM NO. 55335</p> <p>DRAWING NO.</p>
<p>- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED</p>		<p>SCALE NONE</p> <p>RELEASED DATE 5/11/00</p> <p>REVISION DATE 7/12/05</p> <p>REV. NO. B</p> <p>SHEET 1 OF 1</p>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[74](#)