



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
11	2.5	.200	.200	2.51	500	C-2R
56	5.0	.115	.150	1.89	40,000	C-2R
79	6.0	.200	.630	7.92	1,000	C-2R
86	6.3	.200	.400	5.03	50,000	C-2F
18	14.0	.040	.130	1.63	5,000	C-2F
73*	14.0	.080	.300	3.77	15,000	C-2F
37	14.0	.090	.500	6.29	2,500	C-2F
74	14.0	.100	.700	8.80	500	C-2F
85	28.0	.040	.300	3.77	25,000	C-2F
17	28.0	.065	.650	8.17	5,000	C-2F

*LAMP LEAD (Pb) FREE

CONTACT JKL FOR LEAD (Pb) FREE LOT IDENTIFICATION.

METRIC THIRD ANGLE PROJECTION			DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION					
					TITLE T-1 3/4 STANDARD GLASS WEDGE BASE					
DRAWN BY L. WENGSTROM			APP'D BY J.K.		DATE 2/17/05		SIZE A		FSCM NO. 55335	DRAWING NO. GLASS WEDGE BASE T-1 3/4
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE		RELEASED DATE 5/11/00		REVISION DATE 2/17/05		REV. NO. A	SHEET 1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APP'D DATE
A	NOTE #73 TO LEAD (Pb) FREE RELEASED & CANCEL GW-STD-T1 3/4, 75X & 84	2/17/05 5/11/00

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[37](#) [73](#) [79](#)