



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
7732	2.5	.100	.100	1.25	10,000	C-2R
7022	5.0	.021	.034	0.43	10,000	C-2R
7263	5.0	.030	.030	.038	16,000	C-2R
7680	5.0	.060	.030	0.38	100,000	C-2R
7683	5.0	.060	.050	0.63	100,000	C-2R
7265	5.0	.060	.150	1.89	5,000	C-2R
7714	5.0	.075	.090	1.13	25,000	C-2R
7715	5.0	.115	.150	1.89	40,000	C-2R
7268	5.0	.125	.220	2.77	5,000	C-2R
8095	10.0	.027	.100	1.26	10,000	C-2F
CB44	12.0	.040	.090	1.13	10,000	C-2F
8097	12.0	.060	.150	1.89	16,000	C-2F
8098	14.0	.065	.150	1.89	16,000	C-2F
8099	18.0	.026	.150	1.89	16,000	C-2F
7839	28.0	.024	.150	1.89	16,000	CC-2F

NOTES:

1. GLASS ENVELOPE TO BE TIPLESS AND SEAMLESS.
2. BASE MATERIAL: NYLON OR EQUIVALENT.
3. BASE COLOR: WHITE.
4. PIN MATERIAL: NICKEL PLATED.
5. LAMPS TO BE 100% AGED FOR AN EQUIVALENT TO A MINIMUM OF TEN HOURS AT RATED VOLTAGES.
6. FINAL INSPECTION ON ALL LAMPS TO BE PER: MIL. STD. 105E TO AN AQL OF 2.5.
7. DIMENSIONS NOT PROVIDING TOLERANCES ARE REFERENCE DIMENSIONS ONLY.

<p>METRIC THIRD ANGLE PROJECTION</p>	<p>DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0</p>	<p>JKL COMPONENTS CORPORATION</p>									
		<p>TITLE T-1 STANDARD BI-PIN BASED LAMPS</p>									
<p>REV. NO.</p>	<p>DESCRIPTION/ECO NUMBER</p>	<p>APPVD DATE</p>	<p>DRAWN BY L. WENGSTROM</p>	<p>APPVD BY DATE L.R. 7/28/08</p>	<p>SIZE A</p>	<p>FSCM NO. 55335</p>	<p>DRAWING NO. BI-PIN T-1</p>	<p>RELEASED DATE 3/13/00</p>	<p>REVISION DATE 7/28/08</p>	<p>REV. NO. A</p>	<p>SHEET 1 OF 1</p>
<p>- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED</p>			<p>SCALE NONE</p>								

A	CHANGE PIN MATERIAL NOTE	7/28/08
	RELEASED - CANCEL SM-STDBP-T 1, CB81, 7255, 7260, 7261, CB23, CB43, 7264, CB45, CB48	3/13/00

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

JKL Components:

[7268](#) [7714](#) [7715](#) [7839](#) [8097](#) [7680](#) [8095](#) [7683](#) [7263](#) [7022](#) [8098](#) [8099](#) [7265](#)