


REV.	DESCRIPTION/ECO NO.	DATE
	RELEASE	1/27/14
A	ADD SIDE VIEW	8/20/15



NOTES:

1. OPERATION


1. GENTLY LIFT LATCH AT SIDE OF CONNECTOR.
2. SWING COVER OFF OF CONTACTS.
3. SLIDE THE FLEX TAPE INTO THE CONNECTOR PLACING THE EDGE OF THE FLEX TAPE UNDER 2 HOLD DOWN TABS. MAKE SURE THE POLARITY IS MATCHED BETWEEN THE FLEX TAPE AND THE CONNECTOR COVER.
4. FOLD OVER THE COVER AND PRESS IN PLACE UNTIL THE LATCH IS FULLY ENGAGED.

2. LIMIT CURRENT TO A MAXIMUM OF 5 AMPS.

4 PIN JOINER CONNECTOR
WIRE TYPE: UL1007, 22 AWG

USED WITH JKL RGB LED FLEX LIGHT RIBBON
PART NO.: ZFS-10504-RGB

JKL PART NO.: ZCH-170-RGB-J

METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN mm (INCHES)		JKL COMPONENTS CORPORATION			
	TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- 0		TITLE RGB FLEX RIBBON JOINER CONNECTOR HARNESS			
DRAWN BY L. WENGSTROM	APPV'D BY L.R.	DATE 8/20/15	SIZE A	FSCM NO. 55335	DRAWING NO. ZCH-170-RGB-J	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE	RELEASED DATE 1/27/14	REVISION DATE 8/20/15	REV. NO. A SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[ZCH-170-RGB-J](#)