


JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
E6522	6.0	.030	.025	0.31	10,000	C-2V
E79	6.0	.200	.600	7.54	1,000	C-2R
E84	6.3	.040	.030	0.38	20,000	C-2V
E86	6.3	.200	.400	5.03	20,000	C-2V
E12522	12.0	.030	.045	0.57	10,000	C-2F
E21203A	12.0	.100	.640	8.04	2,000	C-2V
E73	14.0	.080	.300	3.77	15,000	C-2V
E37	14.0	.090	.500	6.29	1,500	C-2F
E74*	14.0	.100	.720	9.05	1,000	C-2V
E13522	24.0	.030	.160	2.01	5,000	C-2F
E85	28.0	.040	.300	3.77	10,000	C-2F
E17	28.0	.065	.650	8.17	5,000	C-2F

\*PRODUCTION CHANGE TO Pb FREE GLASS, CONTACT JKL FOR LOT IDENTIFICATION.

METRIC



THIRD ANGLE PROJECTION

DIMENSIONS ARE IN MILLIMETERS

TOLERANCE UNLESS OTHERWISE SPECIFIED  
 1 PL +/- 0.2  
 2 PL +/- 0.20  
 ANGLE +/- 0

**JKL**

COMPONENTS CORPORATION

TITLE

T-1 1/2 STANDARD GLASS WEDGE BASE

A

Pb FREE NOTE ADDED

8/25/04

L. WENGSTROM

APPV'D BY DATE  
J.K. 8/25/04

SIZE  
A

FSCM NO.  
55335

DRAWING NO.

GLASS WEDGE BASE T-1 1/2

REV. NO.

DESCRIPTION/ECO NUMBER

APPV'D DATE

- CAD DRAWING -

MANUAL REVISIONS NOT PERMITTED

SCALE

NONE

RELEASED DATE

5/5/00

REVISION DATE

8/25/04

REV. NO.

A

SHEET

1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[E37](#) [E73](#) [E74](#) [E85](#) [E21203A](#)