



Part Number:

254-PB5022-ROX


Piezoelectric Buzzer
 (External Drive)

KT-400576

Electrical Specifications:

- Sound Pressure Level: 80dB min. at 4.0KHz/9Vp-p Square Wave/10cm
 70dB min. at 4.0KHz/1Vrms Sine Wave/10cm
- Capacitance: 15,000pF $\pm$ 30% at 120Hz
- Current Consumption: 3mA max. at 4.0KHz/9Vp-p Square Wave
- Allowable Input Voltage: 25Vp-p max.

Mechanical Specifications:

- Operating Temp. Range: -30°C to +85°C
- Storage Temp. Range: -40°C to +85°C

Note:

- RoHS Compliant by Exemption

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobitone:

[254-PB5022-ROX](#)