


Dimensions: mm (In)

**Mechanical Specifications:**

- Operation Force: 160±50gf Brown (N)
- Stroke: (6x6) 0.25±0.2/-0.1mm, (12x12) 0.35±0.1mm
- Operation Temperature Range: -25°C to +70°C
- Storage Temperature Range: -30°C to +80°C

Electrical Specifications:

- Electrical Life: 300,000 cycles for 320gf, 520gf; 500,000 cycles for 260gf; 1,000,000 cycles for 100gf, 160gf
- Rating: 50mA/12VDC
- Contact Resistance: 100mΩ max.
- Insulation Resistance: 100MΩ min. @ 500VDC
- Dielectric Strength: 250VAC for 1 minute
- Contact Arrangement: SPST

Materials:

- Cover: Steel, tin plated
- Base: Nylon thermoplastic, brown
- Stem: Nylon thermoplastic
- Contact Disc: Phosphor bronze with silver cladding
- Terminal: Brass with silver cladding
- Cap: Thermoplastic ABS

Note:

- RoHS Compliant and process compatible with 260° solder

Tactile Switch
101-TS6324T1605BC-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[101-TS6324T1605BC-EV](#)