


Surface Mount RF Termination

1 Watt, 50Ω



Description

The C1A50Z4 is high performance Alumina (Al_2O_3) surface mount termination intended as a low cost alternative to Aluminum Nitride (AlN). The termination is well suited for 3G, 4G & 5G Systems and is also RoHS compliant.

Features:

- RoHS Compliant
- 1 Watt
- Al_2O_3 Ceramic
- Non-Nichrome Resistive Element
- Low VSWR
- 100% Tested
- Small Size

General Specifications

Resistive Element	Thick film
Substrate	Al_2O_3 Ceramic
Terminal Finish	Matte Tin over Nickel Barrier
Operating Temperature	-55 to +150°C (see de-rating chart)



Tolerance is ± 0.005 ", unless otherwise specified. Designed to meet or exceed applicable portions of MIL-E-5400. All dimensions in inches.

Electrical Specifications



Impedance:	50 Ohms
Power:	1 Watt
Max Frequency:	DC-6.0 GHz
Return Loss:	>20 dB

Specification based on unit properly installed using suggested mounting instructions and a 50 ohm nominal impedance. **Specifications subject to change.**


Outline Drawing



Typical Performance:




Power De-rating:



Mounting Footprint:

Recommended Mounting Footprint
for 8 mil thick, Dk 3.66 PCB



Tape&Reel:






TABLE 1		
QUANTITY/REEL	REEL DIMENSIONS mm	
4000	$\varnothing A$	177.80
	B	8.00
	$\varnothing C$	50.80
	$\varnothing D$	13.00



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Anaren:](#)

[C1A50Z4](#)