

APPROVAL SHEET

RGCMA Series – 2010(0804)- RoHS Compliance

MULTILAYER CERAMIC
COMMON MODE FILTER ARRAY

P/N: RGCMA2010090V3T

*Contents in this sheet are subject to change without prior notice.

**FEATURES**

1. Miniature footprint: $2.00 \times 1.05 \text{ mm}^2$
2. Multilayer Low Temperature Ceramic Co-fired Technology.
3. Reflow solderable SMD Devices
4. Wide Pass Band (Cut-Off Frequency: $-3\text{dB@ } 3.5\text{GHz}$ Typical)
5. Characteristic Impedance (Differential) : 100Ω (Typical)
6. High Attenuation for common mode noise
7. Special 3D layout design to minimize phase shifting

APPLICATIONS

1. High Speed Transmission Lines.
2. DVI/ LVDS/ HDMI/ S-ATA/ PCI-E/ D-Port



CONSTRUCTION

Fig 1. Outline of 2010 size Common Mode Filter and Schematics

DIMENSIONS


Figure	Symbol	Dimension
	L	$2.00 \pm 0.15\text{mm}$
	W	$1.05 \pm 0.15\text{mm}$
	T	$0.90 \pm 0.1\text{mm}$
	A	$0.25 \pm 0.15\text{mm}$
	B	$0.25 \pm 0.1\text{mm}$
	C	$0.35 \pm 0.15\text{mm}$
	D	$0.20 \pm 0.15\text{mm}$
	E	$0.50 \pm 0.15\text{mm}$

**ELECTRICAL CHARACTERISTICS**


RGCMA2010090V3T	Specification
Cut-off Frequency	3.5 GHz (Typical)
Common Mode Impedance	90 ohm \pm 25% @ 100MHz
DC Resistance	Max. 1.0 Ω
Rated Current	300 mA
Characteristic Impedance (Differential)	100 Ω (Typical)
Operating Temperature	- 40 $^{\circ}$ C ~ +85 $^{\circ}$ C

Typical Electrical Chart


Insertion Loss vs Frequency Characteristic:



Impedance vs Frequency Characteristic:

**SOLDER LAND PATTERN**

Figure



Unit: mm

Line width to be designed to match 50 Ω characteristic impedance, depending on PCB material and thickness.

**RELIABILITY TEST**

Test item	Test condition / Test method	Specification
Solderability JIS C 0050-4.6 JESD22-B102D	*Solder bath temperature : $235 \pm 5^{\circ}\text{C}$ *Immersion time : 2 ± 0.5 sec *Solder : Sn3Ag0.5Cu for lead-free	At least 95% of a surface of each terminal electrode must be covered by fresh solder.
Leaching (Resistance to dissolution of metallization) IEC 60068-2-58	*Solder bath temperature : $260 \pm 5^{\circ}\text{C}$ *Leaching immersion time : 30 ± 0.5 sec *Solder : SN63A	Loss of metallization on the edges of each electrode shall not exceed 25%.
Resistance to soldering heat JIS C 0050-5.4	*Preheating temperature : $120 \sim 150^{\circ}\text{C}$, 1 minute. *Solder temperature : $270 \pm 5^{\circ}\text{C}$ *Immersion time : 10 ± 1 sec *Solder : Sn3Ag0.5Cu for lead-free Measurement to be made after keeping at room temperature for 24 ± 2 hrs	No mechanical damage. Samples shall satisfy electrical specification after test. Loss of metallization on the edges of each electrode shall not exceed 25%.
Drop Test JIS C 0044	*Height : 75 cm *Test Surface : Rigid surface of concrete or steel. *Times : 6 surfaces for each units ; 2 times for each side.	No mechanical damage. Samples shall satisfy electrical specification after test.
Adhesive Strength of Termination JIS C 0051- 7.4.3	*Pressurizing force : $5\text{N}(\leq 0603)$; $10\text{N}(> 0603)$ *Test time : 10 ± 1 sec	No remarkable damage or removal of the termination.
Bending test JIS C 0051- 7.4.1	The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1 mm/s per second until the deflection becomes 1mm/s and then pressure shall be maintained for 5 ± 1 sec. Measurement to be made after keeping at room temperature for 24 ± 2 hours	No mechanical damage. Samples shall satisfy electrical specification after test.



Temperature cycle JIS C 0025	1. 30±3 minutes at -40°C±3°C, 2. 10~15 minutes at room temperature, 3. 30±3 minutes at +85°C±3°C, 4. 10~15 minutes at room temperature, Total 100 continuous cycles Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Samples shall satisfy electrical specification after test.
Vibration JIS C 0040	*Frequency : 10Hz~55Hz~10Hz(1min) *Total amplitude : 1.5mm *Test times : 6hrs.(Two hrs each in three mutually perpendicular directions)	No mechanical damage. Samples shall satisfy electrical specification after test.
High temperature JIS C 0021	*Temperature : 85°C±2°C *Test duration : 1000+24/-0 hours Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Samples shall satisfy electrical specification after test.
Humidity (steady conditions) JIS C 0022	*Humidity : 90% to 95% R.H. *Temperature : 40±2°C *Time : 1000+24/-0 hrs. Measurement to be made after keeping at room temperature for 24±2 hrs ※ 500hrs measuring the first data then 1000hrs data	No mechanical damage. Samples shall satisfy electrical specification after test.
Low temperature JIS C 0020	*Temperature : -40°C±2°C *Test duration : 1000+24/-0 hours Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Samples shall satisfy electrical specification after test.

SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,




Fig 2. Infrared soldering profile


ORDERING CODE

RG	CMA	201009	0	V	3	T
Walsin RF device	Product Code CMA : Common Mode Filter Array	Dimension code 201009 = Width 20, Length 10, Thickness 9	Unit of dimension 0: 0.1 mm 1: 1.0 mm	Application V: High Speed Transmission Lines HDMI/ LVDS/ DVI/ PCI-E/ Display Port/ SATA	Specification Code from 0 ~ 9 dependent on different electrical specification	Packing T: Reeled


Minimum Ordering Quantity: 2000 pcs per reel.

PACKAGING

Paper Tape specifications (unit :mm)



Index	A ₀	B ₀	ΦD	T	W
Dimension(mm)	1.30±0.10	2.25±0.10	1.00±0.10	1.10±0.10	8.0±0.20
Index	E	F	P ₀	P ₁	P ₂
Dimension(mm)	1.75±0.10	3.5±0.05	4.0±0.10	4.0±0.10	2.0±0.05

**Reel dimensions**

Index	A	B	C
Dimension (mm)	Φ178.0	Φ60.0	Φ13.0

Taping Quantity:2000 pieces per 7" reel

CAUTION OF HANDLING**Limitation of Applications**

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection, which can be confirmed.
- (2) Storage environment condition.
 - Products should be storage in the warehouse on the following conditions.
 - Temperature : -10 to +40℃
 - Humidity : 30 to 70% relative humidity
 - Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
 - Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
 - Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
 - Products should be storage under the airtight packaged condition.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Walsin:

[RGCMA2010090V3T](#)