


Sample Kit Contents

KEMET Part Number	Capacitance	Size Code	Lead Spacing	Capacitance Tolerance	dV/dt	Quantity
	μF		mm	%	V/ μs	
F863BC104K310ALW0L	0.1	BK	15	10	400	10
F863BK224K310ALW0L	0.22	BK	15	10	400	10
F863BW474K310ALW0L	0.47	BW	15	10	400	10
F863BW564K310ALW0L	0.56	BW	15	10	400	10
F863DE474K310ALW0L	0.47	DE	22.5	10	200	10
F863DS105K310ALW0L	1.0	DS	22.5	10	200	10
F863DV155K310ALW0L	1.5	DV	22.5	10	200	10
F863FL225K310ALW0L	2.2	FL	27.5	10	150	10
F863RL475M310ALW0L	4.7	RL	37.5	10	100	10

Dimensions – Millimeters

Size Code	p		B		H		L		d	
	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance
BC	15.0	± 0.4	5.0	$+0.2$	11.0	$+0.1$	18.0	$+0.3$	0.6	± 0.05
BK	15.0	± 0.4	7.5	$+0.2$	13.5	$+0.1$	18.0	$+0.5$	0.6	± 0.05
BW	15.0	± 0.4	11.0	$+0.2$	19.0	$+0.1$	18.0	$+0.5$	0.8	± 0.05
DE	22.5	± 0.4	7.0	$+0.2$	16.0	$+0.1$	26.5	$+0.3$	0.8	± 0.05
DS	22.5	± 0.4	11.0	$+0.2$	20.0	$+0.1$	26.5	$+0.3$	0.8	± 0.05
DV	22.5	± 0.4	13.0	$+0.2$	22.0	$+0.1$	26.5	$+0.3$	0.8	± 0.05
FL	27.5	± 0.4	13.0	$+0.2$	25.0	$+0.1$	32.0	$+0.3$	0.8	± 0.05
RL	37.5	± 0.4	19.0	$+0.3$	32.0	$+0.1$	41.5	$+0.3$	1.0	± 0.05

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KEMET:

FLM ENG KIT 24