

Technical drawing of a mechanical part, showing side and end views with dimensions in inches and millimeters.

Side View Dimensions:

- Top diameter: $\pm .002 [\pm 0.05]$.145 [3.68] DIA.
- Second diameter: $\pm .002 [\pm 0.05]$.065 [1.65] DIA.
- Third diameter: .033 [0.84]
- Fourth diameter: .045 [1.14]
- Overall length: .360 [9.14]
- Internal feature depth: .156 [3.96]
- Bottom diameter: .031 [0.79]
- Overall length (including bottom feature): .312 [7.92]
- Bottom feature depth: .156 [3.96]
- Bottom diameter: $\pm .002 [\pm 0.05]$.053 [1.35] DIA.
- Bottom feature width: $\pm .002 [\pm 0.05]$.082 [2.08] DIA.
- Bottom diameter: $\pm .002 [\pm 0.05]$.187 [4.75] DIA.

End View Dimensions:

- Overall diameter: $\pm .002 [\pm 0.05]$.112 [2.84] DIA.

PART NO.	'L' DIM.
1545-2	.105 [2.67]
1545-3	.135 [3.43]
1545-4	.165 [4.19]

ASTORIA, N.Y. 11105-2017

TERMINAL

BRASS

TIN PLATE

BOONE

10.24.96

LN

4X

INCH	[MM]
------	------

DWG NO.	
---------	--

DECIMAL	$\pm .005$	$[\pm 0.15]$
---------	------------	--------------

© 1994

ANGULAR $\pm 1^\circ$
UNLESS OTHERWISE SPECIFIED

1545-

DATE _____

DESCRIPTION

REV.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[1545-3](#)