




### PCB LAYOUT

TOLERANCE  $\pm .002$  [ $\pm 0.05$ ]

.016 [0.40]  
(10) PLS



### PLUG SPECIFICATIONS:

SHELL: MAT'L- STEEL

FINISH- NICKEL PLATE

CONTACT: MAT'L- PHOSPHOR BRONZE

FINISH- GOLD FLASH OVER NICKEL

INSULATION: MAT'L- THERMOPLASTIC, UL 94V-0

### ELECTRICAL CHARACTERISTICS:

RATED VOLTAGE: 30V (RMS)

CONTACT CURRENT RATING: 1 Amp DC MAX.

CONTACT RESISTANCE: 15m  $\Omega$  min.

DIELECTRIC WITHSTANDING VOLTAGE: 750V AC FOR 1 MINUTE

### MECHANICAL CHARACTERISTICS:

OPERATING TEMPERATURE: -13°F (-25°C) TO 176°F (+80°C)

DURABILITY: 1500 CYCLES MIN.

THIS DOCUMENT IS THE PROPERTY OF  
KEYSTONE ELECTRONICS CORP. AND  
SHALL NOT BE REPRODUCED, DISTRIBUTED  
OR USED AS A BASIS FOR MANUFACTURE  
WITHOUT PRIOR WRITTEN PERMISSION  
FROM KEYSTONE ELECTRONICS CORP.

|   |  |        |         |
|---|--|--------|---------|
| <b>KEYSTONE ELECTRONICS CORP.</b>                               |  |        |         |
| www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900 |  |        |         |
| PART NAME   |  |        |         |
| USB 3.0 MICRO RECEPTACLE  |  |        |         |
| MATERIAL  |  |        |         |
| AS NOTED  |  |        |         |
| FINISH  |  | DRN BY | DATE    |
| AS NOTED  |  | NT     | 4.20.10 |
| TOLERANCES  |  | CODE   | DWG NO. |
| DECIMAL $\pm .004$ [ $\pm 0.10$ ]                               |  | LN     | SCALE   |
| ANGULAR $\pm 1^\circ$   |  | C/M    | 4X      |
| UNLESS OTHERWISE SPECIFIED                                      |  | 955    |         |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[955](#)