






ACTUAL SIZE



NOTE:

1. SHELL: MAT'L- STAINLESS STEEL
FINISH: NICKEL PLATE
2. CONTACT: MAT'L .005 [0.12] TH'K BRASS
GOLD PLATE
3. HOUSING: LCP, CLASS FILLED
4. OPERATING TEMPERATURE -55°C TO +85°C

5. CONTACT RESISTANCE:.

INITIAL: 20 milli OHMS MAX.

INSULATION RESISTANCE- 100 Mega OHMS MIN.

DIELECTRIC STRENGTH: 100 Vac Rms 60Hz. 1Min.

KEYSTONE ELECTRONICS CORP.

www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900

PART NAME

USB 3.1 TYPE-C RECEPTACLE- SMT TYPE

MATERIAL

AS NOTED

FINISH

AS NOTED

DRN BY

NT

DATE

4.13.15

APP'D

LN

SCALE

4X

TOLERANCES

INCH

[MM]

DECIMAL

± .005 [± 0.13]

ANGULAR

± 1°

UNLESS OTHERWISE SPECIFIED

CODE

C

DWG NO.

953

DATE

DESCRIPTION

REV.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[953](#)