

MOSFET

OptiMOS™ Power-Transistor, -150 V

Features



- P-channel
- Very low on-resistance $R_{DS(on)}$ @ $V_{GS}=4.5\text{ V}$
- Logic level
- 100% avalanche tested
- Enhancement mode
- Pb-free lead plating; RoHS compliant
- Halogen-free according to IEC61249-2-21

Product validation

Fully qualified according to JEDEC for Industrial Applications

Table 1 Key Performance Parameters

Parameter	Value	Unit
V_{DS}	-150	V
$R_{DS(on),max}$	1380	mΩ
I_D	-1.29	A
Q_{oss}	-3.6	nC
Q_G	-11.6	nC



RoHS

Type / Ordering Code	Package	Marking	Related Links
ISP14EP15LM	PG-SOT223-4	14EP15LM	-

Table of Contents

Description 1

Maximum ratings 3

Thermal characteristics 3

Electrical characteristics 4

Electrical characteristics diagrams 6

Package Outlines 10

Revision History 11

Trademarks 11

Disclaimer 11

1 Maximum ratings

at $T_A=25\text{ °C}$, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Continuous drain current ¹⁾	I_D	-	-	-1.29 -0.82 -0.81 -0.77	A	$V_{GS}=-10\text{ V}$, $T_C=25\text{ °C}$ $V_{GS}=-10\text{ V}$, $T_C=100\text{ °C}$ $V_{GS}=-4.5\text{ V}$, $T_C=100\text{ °C}$ $V_{GS}=-10\text{ V}$, $T_A=25\text{ °C}$, $R_{thJA}=70\text{ °C/W}^{2)}$
Pulsed drain current ³⁾	$I_{D,pulse}$	-	-	-5.2	A	$T_A=25\text{ °C}$
Avalanche energy, single pulse ⁴⁾	E_{AS}	-	-	90	mJ	$I_D=-0.8\text{ A}$, $R_{GS}=25\text{ }\Omega$
Gate source voltage	V_{GS}	-20	-	20	V	-
Power dissipation	P_{tot}	-	-	5.0 1.8	W	$T_C=25\text{ °C}$ $T_A=25\text{ °C}$, $R_{thJA}=70\text{ °C/W}^{2)}$
Operating and storage temperature	T_j , T_{stg}	-55	-	150	°C	IEC climatic category; DIN IEC 68-1: 55/150/56

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	25	°C/W	-
Thermal resistance, junction - ambient, 6 cm ² cooling area	R_{thJA}	-	-	70	°C/W	-

¹⁾ Rating refers to the product only with datasheet specified absolute maximum values, maintaining case temperature as specified. For other case temperatures please refer to Diagram 2. De-rating will be required based on the actual environmental conditions.

²⁾ Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 µm thick) copper area for drain connection. PCB is vertical in still air.

³⁾ See Diagram 3 for more detailed information

⁴⁾ See Diagram 13 for more detailed information

3 Electrical characteristics

at $T_j=25\text{ °C}$, unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	-150	-	-	V	$V_{GS}=0\text{ V}$, $I_D=-1\text{ mA}$
Gate threshold voltage	$V_{GS(th)}$	-1.0	-1.5	-2.0	V	$V_{DS}=V_{GS}$, $I_D=-270\text{ }\mu\text{A}$
Zero gate voltage drain current	I_{DSS}	-	-0.1 -10	-1.0 -100	μA	$V_{DS}=-150\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=25\text{ °C}$ $V_{DS}=-150\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=125\text{ °C}$
Gate-source leakage current	I_{GSS}	-	-10	-100	nA	$V_{GS}=-20\text{ V}$, $V_{DS}=0\text{ V}$
Drain-source on-state resistance	$R_{DS(on)}$	-	1133.6 1159.9	1380 1400	m Ω	$V_{GS}=-10\text{ V}$, $I_D=-0.8\text{ A}$ $V_{GS}=-4.5\text{ V}$, $I_D=-0.7\text{ A}$
Gate resistance	R_G	-	5.3	-	Ω	-
Transconductance	g_{fs}	-	2.9	-	S	$ V_{DS} \geq 2 I_D R_{DS(on)max}$, $I_D=-0.8\text{ A}$

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Input capacitance ¹⁾	C_{iss}	-	410	530	pF	$V_{GS}=0\text{ V}$, $V_{DS}=-75\text{ V}$, $f=1\text{ MHz}$
Output capacitance ¹⁾	C_{oss}	-	19	25	pF	$V_{GS}=0\text{ V}$, $V_{DS}=-75\text{ V}$, $f=1\text{ MHz}$
Reverse transfer capacitance ¹⁾	C_{rss}	-	6	11	pF	$V_{GS}=0\text{ V}$, $V_{DS}=-75\text{ V}$, $f=1\text{ MHz}$
Turn-on delay time	$t_{d(on)}$	-	10.46	-	ns	$V_{DD}=-75\text{ V}$, $V_{GS}=-10\text{ V}$, $I_D=-0.8\text{ A}$, $R_{G,ext}=1.6\text{ }\Omega$
Rise time	t_r	-	6.28	-	ns	$V_{DD}=-75\text{ V}$, $V_{GS}=-10\text{ V}$, $I_D=-0.8\text{ A}$, $R_{G,ext}=1.6\text{ }\Omega$
Turn-off delay time	$t_{d(off)}$	-	24.01	-	ns	$V_{DD}=-75\text{ V}$, $V_{GS}=-10\text{ V}$, $I_D=-0.8\text{ A}$, $R_{G,ext}=1.6\text{ }\Omega$
Fall time	t_f	-	14.25	-	ns	$V_{DD}=-75\text{ V}$, $V_{GS}=-10\text{ V}$, $I_D=-0.8\text{ A}$, $R_{G,ext}=1.6\text{ }\Omega$

¹⁾ Defined by design. Not subject to production test.

Table 6 Gate charge characteristics¹⁾

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	-1.06	-	nC	$V_{DD}=-75\text{ V}$, $I_D=-0.8\text{ A}$, $V_{GS}=0\text{ to }-4.5\text{ V}$
Gate charge at threshold	$Q_{g(th)}$	-	-0.62	-	nC	$V_{DD}=-75\text{ V}$, $I_D=-0.8\text{ A}$, $V_{GS}=0\text{ to }-4.5\text{ V}$
Gate to drain charge ²⁾	Q_{gd}	-	-3.0	-4.5	nC	$V_{DD}=-75\text{ V}$, $I_D=-0.8\text{ A}$, $V_{GS}=0\text{ to }-4.5\text{ V}$
Switching charge	Q_{sw}	-	-3.4	-	nC	$V_{DD}=-75\text{ V}$, $I_D=-0.8\text{ A}$, $V_{GS}=0\text{ to }-4.5\text{ V}$
Gate charge total ²⁾	Q_g	-	-6.0	-7.5	nC	$V_{DD}=-75\text{ V}$, $I_D=-0.8\text{ A}$, $V_{GS}=0\text{ to }-4.5\text{ V}$
Gate plateau voltage	$V_{plateau}$	-	-2.6	-	V	$V_{DD}=-75\text{ V}$, $I_D=-0.8\text{ A}$, $V_{GS}=0\text{ to }-4.5\text{ V}$
Gate charge total	Q_g	-	-11.6	-	nC	$V_{DD}=-75\text{ V}$, $I_D=-0.8\text{ A}$, $V_{GS}=0\text{ to }-10\text{ V}$
Output charge ²⁾	Q_{oss}	-	-3.6	-4.8	nC	$V_{DS}=-75\text{ V}$, $V_{GS}=0\text{ V}$

Table 7 Reverse diode

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Diode continuous forward current	I_S	-	-	-1.29	A	$T_C=25\text{ °C}$
Diode pulse current	$I_{S,pulse}$	-	-	-5.16	A	$T_C=25\text{ °C}$
Diode forward voltage	V_{SD}	-	-0.79	-1.2	V	$V_{GS}=0\text{ V}$, $I_F=-0.8\text{ A}$, $T_j=25\text{ °C}$
Reverse recovery time ²⁾	t_{rr}	-	32.46	64.92	ns	$V_R=-75\text{ V}$, $I_F=-0.8\text{ A}$, $di_F/dt=-100\text{ A}/\mu\text{s}$
Reverse recovery charge ²⁾	Q_{rr}	-	55.92	111.84	nC	$V_R=-75\text{ V}$, $I_F=-0.8\text{ A}$, $di_F/dt=-100\text{ A}/\mu\text{s}$

¹⁾ See "Gate charge waveforms" for parameter definition

²⁾ Defined by design. Not subject to production test.

4 Electrical characteristics diagrams







Diagram 5: Typ. output characteristics




$I_D = f(V_{DS})$, $T_j = 25^\circ\text{C}$; parameter: V_{GS}

Diagram 6: Typ. drain-source on resistance




$R_{DS(on)} = f(I_D)$, $T_j = 25^\circ\text{C}$; parameter: V_{GS}

Diagram 7: Typ. transfer characteristics




$I_D = f(V_{GS})$, $|V_{DS}| > 2|I_D|R_{DS(on)max}$; parameter: T_j

Diagram 8: Typ. drain-source on resistance




$R_{DS(on)} = f(V_{GS})$, $I_D = -0.8$ A; parameter: T_j

Diagram 9: Normalized drain-source on resistance




$R_{DS(on)} = f(T_j)$, $I_D = -0.8$ A, $V_{GS} = -10$ V

Diagram 10: Typ. gate threshold voltage




$V_{GS(th)} = f(T_j)$, $V_{GS} = V_{DS}$; parameter: I_D

Diagram 11: Typ. capacitances




$C = f(V_{DS})$; $V_{GS} = 0$ V; $f = 1$ MHz

Diagram 12: Forward characteristics of reverse diode




$I_F = f(V_{SD})$; parameter: T_j

Diagram 13: Avalanche characteristics




$I_{AS}=f(t_{AV})$; $R_{GS}=25\ \Omega$; parameter: $T_{j,start}$

Diagram 14: Typ. gate charge




$V_{GS}=f(Q_{gate})$, $I_D=-0.8\text{ A}$ pulsed, $T_j=25\text{ °C}$; parameter: V_{DD}

Diagram 15: Drain-source breakdown voltage




$V_{BR(DSS)}=f(T_j)$; $I_D=-1\text{ mA}$

Diagram Gate charge waveforms



5 Package Outlines



DIMENSION	MILLIMETERS	
	MIN.	MAX.
A	1.60	1.80
A1	-	0.10
A2	1.50	1.70
b	0.60	0.80
b2	2.90	3.10
c	0.24	0.32
D	6.30	6.70
E	6.70	7.30
E1	3.30	3.70
e	2.30	
e1	4.60	
L	0.75	-
O	0°	10°

DOCUMENT NO. Z8B00188348
REVISION 01
SCALE 10:1 0 1 2mm
EUROPEAN PROJECTION
ISSUE DATE 28.02.2018

Figure 1 Outline PG-SOT223-4, dimensions in mm

Revision History

ISP14EP15LM

Revision: 2021-05-10, Rev. 2.0

Previous Revision

Revision	Date	Subjects (major changes since last revision)
2.0	2021-05-10	Release of final version

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to:

erratum@infineon.com

Published by

Infineon Technologies AG

81726 München, Germany

© 2020 Infineon Technologies AG

All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[ISP14EP15LMXTSA1](#)