

## General Description


The PVI5033R Photovoltaic Isolator is a dual-channel, opto-isolated driver capable of directly driving gates of power MOSFETs or IGBTs. It utilizes a monolithic integrated circuit photovoltaic generator of novel construction as its output. The output is controlled by radiation from a GaAlAs light emitting diode (LED) which is optically isolated from the photovoltaic generator.

The PVI5033R is ideally suited for applications requiring high-current and/or high voltage switching with optical isolation between the low-level driving circuitry and high-energy or high-voltage load circuits. It can be used for directly driving gates of power MOSFETs. The dual-channel configuration allows its outputs to drive independent discrete power MOSFETs, or be connected in parallel or in series to provide higher-current drive for power MOSFETs or higher-voltage drive for IGBTs. PVI5033R employs a fast turn-off circuitry.

PVI5033R Photovoltaic Isolators are packaged in an 8-pin, molded DIP package with either thru-hole or "gull-wing" terminals. It is available in standard plastic shipping tubes or on tape-and-reel. Refer to Part Identification information.

## Features

- Monolithic construction
- 3,750 V<sub>RMS</sub> I/O isolation
- 1,200 V<sub>DC</sub> output-to-output isolation
- Dual-Channel application flexibility
- Solid-State Reliability
- UL Recognized



## Applications

- Telecommunications
- Load Distribution
- Industrial Controls
- Instrumentation and Measurement
- Electronic Ballast

## Part Identification

PVI5033RPBFHKL1	thru-hole
PVI5033RSPbF	SMT
PVI5033RSTPBFHUMA1	SMT, Tape and Reel

## Electrical Specifications (-40°C ≤ T<sub>A</sub> ≤ +85°C unless otherwise specified)


INPUT CHARACTERISTICS	Limits	Units
Min. Input Current (See Fig.1)	5.0	mA
Input Current Range (See Fig. 1)	3.0 to 25	mA
Max. Continuous Input Current @ T <sub>A</sub> =+25°C	40	mA
LED Forward Voltage Drop @ 5mA, T <sub>A</sub> =+25°C (See Fig. 3)	1.4	V
Max. Reverse Voltage	6.0	V
Max. Reverse Current @ -6V <sub>DC</sub> , T <sub>A</sub> =+25°C	10	μA

OUTPUT CHARACTERISTICS	Limits	Units
Min. Forward Voltage	8.0	V <sub>DC</sub>
Max. Reverse Current	10	μA <sub>DC</sub>

COUPLED CHARACTERISTICS	Limits	Units
Min. Output Voltage @ I <sub>LED</sub> = 10mA, R <sub>L</sub> = 10MΩ @ T <sub>A</sub> =0°C to +70°C (See Fig. 1 & 2)	5	V
Max. Output Voltage @ I <sub>LED</sub> = 10mA, R <sub>L</sub> = 10MΩ @ T <sub>A</sub> =0°C to +70°C (See Fig. 1 & 2)	10	V
Max. Voltage Differential Between Outputs @ I <sub>LED</sub> = 5mA, R <sub>L</sub> = 10MΩ	1.0	V
Min. Output Short-Circuit Current @ I <sub>LED</sub> = 5mA, @ T <sub>A</sub> =+25°C (See Fig. 1 & 2)	1.65	μA
Typical Output Short-Circuit Current @ I <sub>LED</sub> = 10mA, @ T <sub>A</sub> =+25°C (See Fig. 1 & 2)	5	μA
Max. Turn-On Time @ I <sub>LED</sub> = 5mA, C <sub>LOAD</sub> = 200pF (See Fig. 4)	2.5	ms
Max. Turn-Off Time @ I <sub>LED</sub> = 5mA, C <sub>LOAD</sub> = 200pF (See Fig. 4)	.5	ms
Off-State Clamping Resistance: minimum	350	Ω
maximum	1500	Ω

GENERAL CHARACTERISTICS	Limits	Units
Min. Dielectric Strength, Input-Output	3750	V <sub>RMS</sub>
Min. Dielectric Strength, Output-to-Output	1200	V <sub>DC</sub>
Min. Insulation Resistance, Input-to-Output @ T <sub>A</sub> =+25°C, 50%RH, 100V <sub>DC</sub>	10 <sup>12</sup>	Ω
Max. Capacitance, Input-Output	5.0	pF
Max. Pin Soldering Temperature (10 seconds max.)	+260	°C
Ambient Temperature Range: Operating	-40 to +85	°C
Storage	-40 to +125	°C

## Connection Diagram



International Rectifier does not recommend the use of this product in aerospace, avionics, military or life support applications. Users of this International Rectifier product in such applications assume all risks of such use and indemnify International Rectifier against all damages resulting from such use.




Figure 1. Typical Output Characteristics




Figure 2. Typical Variation of Output




Figure 3. Input Characteristics (Current Controlled)






Figure 4. Typical Response Time

## Case Outlines



**Qualification information**

Qualification level	Industrial (per JEDEC JESD47F <sup>†</sup> guidelines)	
Moisture Sensitivity Level	PVI5033RPBFHKL1	N/A
	PVI5033RSPbF	MSL4
	PVI5033RSTPBFUMA1	(per JEDEC J-STD-020E & JEDEC J-STD-033C) <sup>†</sup>
RoHS compliant	Yes	

<sup>†</sup> Applicable version of JEDEC standard at the time of product release.

**Revision History**

Date	Comment
24/05/2015	<ul style="list-style-type: none"> <li>Added Qualification Information table on page 5.</li> <li>Updated data sheet based on corporate template.</li> </ul>
12/06/2023	<ul style="list-style-type: none"> <li>Updated data sheet OPNs.</li> </ul>

## Trademarks of Infineon Technologies AG

μHVIC™, μIPM™, μPFC™, AU-ConvertIR™, AURIX™, C166™, CanPAK™, CIPOS™, CIPURSE™, CoolDP™, CoolGaN™, COOLiR™, CoolMOS™, CoolSET™, CoolSiC™, DAVE™, DI-POL™, DirectFET™, DrBlade™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPACK™, EconoPIM™, EiceDRIVER™, eupec™, FCOS™, GaNpowIR™, HEXFET™, HITFET™, HybridPACK™, iMOTION™, iRAM™, ISOFACE™, IsoPACK™, LEDriviR™, LITIX™, MIPAQ™, ModSTACK™, my-d™, NovalithiC™, OPTIGA™, OptiMOS™, ORIGA™, PowIRaudio™, PowIRstage™, PrimePACK™, PrimeSTACK™, PROFET™, PRO-SiL™, RASIC™, REAL3™, SmartLEWIS™, SOLID FLASH™, SPOC™, StrongIRFET™, SupIRBuck™, TEMPFET™, TRENCHSTOP™, TriCore™, UHVIC™, XHP™, XMC™

Trademarks updated November 2015

## Other Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2023-12-06**

**Published by**

**Infineon Technologies AG**

**81726 Munich, Germany**

**© 2023 Infineon Technologies AG.**

**All Rights Reserved.**

**Do you have a question about this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

**ifx1**

## IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or **characteristics ("Beschaffenheitsgarantie")**.

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document **is subject to customer's compliance with its obligations** stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in **customer's applications**.

The data contained in this document is exclusively intended for technically trained staff. It is the **responsibility of customer's technical departments** to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

## WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, **Infineon Technologies' products may not be used** in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[PVI5033RPBF](#) [PVI5033RS-TPBF](#) [PVI5033RSPBF](#) [PVI5033RPBFHKL1](#) [PVI5033RSTPBFHUMA1](#)