

8.1 GHz Surface Mount Bandpass Filter

B081RC0S

COMPEX • DLI • JOHANSON MFG
NOVACAP • SYFER • VOLTRONICS
www.knowlescapacitors.com

DESCRIPTION

One of DLI's surface mountable catalog bandpass filters. This filter utilizes DLI's low loss temperature stable materials which offer small size and minimal performance variation over temperature. The catalog BPF's are offered in a variety of frequency bands, which offers a drop in solution with highly repeatable performance.

FEATURES


- Small Size
- Fully Shielded Component
- Solder Surface Mount Package
- Moisture Sensitivity Level: MSL1
- Frequency Stable over Temperature
- Operating & Storage Temp: -55°C to +125°C
- Characteristic Impedance: 50Ω

SPECIFICATIONS*

Parameter	Frequency Range (GHz)	Min	Typ.	Max
Insertion Loss (dB)	6 - 11		1.8	2
Return Loss (dB)		13	15	
Low Side Rejection (dB)	DC - 5.5	23	25	
High Side Rejection (dB)	12 - 33	28	30	
Input Power (W)				TBD
Size (L x W x H)	0.190 x 0.100 x 0.090 in 4.83 x 2.54 x 2.29 mm			

*Electrical specifications based on typical probed performance at room temperature. Insertion loss shall vary ± 0.5 dB over temperature.

Typical Preliminary Simulated Performance




8.1 GHz Surface Mount Bandpass Filter

B081RC0S


COMPEX • DLI • JOHANSON MFG
NOVACAP • SYFER • VOLTRONICS
www.knowlescapacitors.com

Physical Dimensions

Units = inches



Recommended PCB Layout



L	W	D1	D2	R	r	A	A1	B	C
0.19	0.10	0.033	0.02	0.5*D2	R	L+0.002	L-D1	W+0.002	0.0065

- 50Ω trace dimensions are application specific.
- Ensure adequate grounding beneath the part.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Knowles:](#)

[B081RC0S](#)