


JLCXXEYYYTRSM**L****VARIABLE INDUCTOR COIL
(NONMAGNETIC)***U.S. PATENT No. 8,248,198*

FILE: AIROUT



NOTES:

1. a. DIMENSIONS: mm
b. DIMENSIONS: (inches) FOR REFERENCE ONLY
2. COIL :
a. MATERIAL:
COPPER ALLOY (COATED)
b. COATING ABLE TO WITHSTAND 275°C FOR 100 HOURS AS PER NEMA "CLASS 200". (REF ASTM D2307)
3. CORE :
a. MATERIAL:
PTFE / COPPER ALLOY
b. SELF-RESONANT FREQUENCY (SRF) IS MEASURED WITH THE CORE FULLY ENGAGED AS DEPICTED
c. L MIN MEASURED WITH CORE ENGAGING FULL WINDINGS. L MAX MEASURED WITH CORE ENGAGING A SINGLE TURN.
4. TINNING :
a. MATERIAL:
RoHS COMPLIANT "SAC" ALLOY

JMC P/N	L (nH)				Q (@ 100 MHz)	SRF (GHz)	TURNS	THD LGTH mm (in)
	MIN	NOM	MAX	NO CORE				
JLC02E030TRSM	32	33	34	39	90	1.2	2	6(.236)
JLC03E048TRSM	46	49	52	59	95	1.0	3	6(.236)
JLC03E055TRSM	50	55	60	64	95	1.0	3	6(.236)
JLC04E065TRSM	60	64	68	78	101	0.9	4	6(.236)
JLC05E088TRSM	74	81	87	99	114	0.9	5	8(.315)
JLC06E110TRSM	94	107	119	123	119	0.7	6	8(.315)
JLC07E130TRSM	104	118	133	142	121	0.7	7	10(.394)

READINGS TAKEN ON AGILENT/8358-A METER.

L	04/08/14	MAI	MAI	MAI	001221
K	01/10/14	SSH	MAI	MAI	001198
J	08/28/12	BFH	MAI	MAI	001102
LEVEL	DATE	DRN.	CHK.	APP.	ECN

REVISIONS

DRN.	CHK.	APP.	SCALE
MAI	MAI	MAI	NONE
DATE	DATE	DATE	.XX ± .762
03/19/09	03/19/09	03/19/09	.XXX ± .254

**JOHANSON MANUFACTURING CORPORATION**
 ROCKAWAY VALLEY ROAD, BOONTON, N.J. 07005 (973)334-2676 FAX (973)334-2954
 ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION

PROPRIETARY INFORMATION CONTAINED NOT TO BE USED WITHOUT JOHANSON MANUFACTURING CORPORATION APPROVAL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Knowles:

[JLC02E030TRVSM](#) [JLC03E048TRVSM](#) [JLC04E065TRVSM](#) [JLC06E110TRVSM](#) [JLC07E130TRSM](#)
[JLC07E130TRVSM](#) [JLC09E160TRSM](#) [JLC13E250TRSM](#) [JLC19E375TRSM](#)