

# IRF6894MPbF


## IRF6894MTRPbF

DirectFET<sup>®</sup>*plus* MOSFET with Schottky Diode ②

- RoHs Compliant Containing No Lead and Bromide ①
- Integrated Monolithic Schottky Diode
- Low Profile (<0.7 mm)
- Dual Sided Cooling Compatible ①
- Low Package Inductance
- Optimized for High Frequency Switching ①
- Ideal for CPU Core DC-DC Converters
- Optimized for Sync. FET socket of Sync. Buck Converter①
- Low Conduction and Switching Losses
- Compatible with existing Surface Mount Techniques ①
- 100% R<sub>g</sub> tested
- Footprint compatible to DirectFET<sup>™</sup>

Typical values (unless otherwise specified)

| V <sub>DSS</sub>   |                 | V <sub>GS</sub>  |                 | R <sub>DS(on)</sub> |                     | R <sub>DS(on)</sub> |  |
|--------------------|-----------------|------------------|-----------------|---------------------|---------------------|---------------------|--|
| 25V max            |                 | ±16V max         |                 | 0.9mΩ @ 10V         |                     | 1.4mΩ @ 4.5V        |  |
| Q <sub>g tot</sub> | Q <sub>gd</sub> | Q <sub>gs2</sub> | Q <sub>rr</sub> | Q <sub>oss</sub>    | V <sub>gs(th)</sub> |                     |  |
| 26nC               | 9.8nC           | 2.8nC            | 56nC            | 31nC                | 1.6V                |                     |  |



Applicable DirectFET Outline and Substrate Outline (see p.7,8 for details)①

|    |    |    |  |    |           |    |    |  |  |  |
|----|----|----|--|----|-----------|----|----|--|--|--|
| SQ | SX | ST |  | MQ | <b>MX</b> | MT | MP |  |  |  |
|----|----|----|--|----|-----------|----|----|--|--|--|

### Description

The IRF6894MPbF combines the latest HEXFET<sup>®</sup> Power MOSFET Silicon technology with the advanced DirectFET<sup>™</sup> packaging to achieve the lowest on-state resistance in a package that has the footprint of a SO-8 and less than 0.7 mm profile. The DirectFET package is compatible with existing layout geometries used in power applications, PCB assembly equipment and vapor phase, infra-red or convection soldering techniques. Application note AN-1035 is followed regarding the manufacturing methods and processes. The DirectFET package allows dual sided cooling to maximize thermal transfer in power systems, improving previous best thermal resistance by 80%.

The IRF6894MPbF balances industry leading on-state resistance while minimizing gate charge along with low gate resistance to reduce both conduction and switching losses. This part contains an integrated Schottky diode to reduce the Q<sub>rr</sub> of the body drain diode further reducing the losses in a Synchronous Buck circuit. The reduced losses make this product ideal for high frequency/high efficiency DC-DC converters that power high current loads such as the latest generation of microprocessors. The IRF6894MPbF has been optimized for parameters that are critical in synchronous buck converter's Sync FET sockets.

### Absolute Maximum Ratings

|                                        | Parameter                                         | Max. | Units |
|----------------------------------------|---------------------------------------------------|------|-------|
| V <sub>DS</sub>                        | Drain-to-Source Voltage                           | 25   | V     |
| V <sub>GS</sub>                        | Gate-to-Source Voltage                            | ±16  |       |
| I <sub>D</sub> @ T <sub>A</sub> = 25°C | Continuous Drain Current, V <sub>GS</sub> @ 10V ③ | 32   | A     |
| I <sub>D</sub> @ T <sub>A</sub> = 70°C | Continuous Drain Current, V <sub>GS</sub> @ 10V ③ | 25   |       |
| I <sub>D</sub> @ T <sub>C</sub> = 25°C | Continuous Drain Current, V <sub>GS</sub> @ 10V ④ | 160  |       |
| I <sub>DM</sub>                        | Pulsed Drain Current ⑤                            | 260  |       |
| E <sub>AS</sub>                        | Single Pulse Avalanche Energy ⑥                   | 410  | mJ    |
| I <sub>AR</sub>                        | Avalanche Current ⑤                               | 26   | A     |




Fig 1. Typical On-Resistance vs. Gate Voltage

Notes:

- ① Click on this section to link to the appropriate technical paper.
- ② Click on this section to link to the DirectFET Website.
- ③ Surface mounted on 1 in. square Cu board, steady state.




Fig 2. Typical Total Gate Charge vs. Gate-to-Source Voltage


- ④ T<sub>C</sub> measured with thermocouple mounted to top (Drain) of part.
- ⑤ Repetitive rating; pulse width limited by max. junction temperature.
- ⑥ Starting T<sub>J</sub> = 25°C, L = 1.18mH, R<sub>G</sub> = 50Ω, I<sub>AS</sub> = 26A.

## Static @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

|                                | Parameter                            | Min. | Typ. | Max. | Units                | Conditions                                                                        |
|--------------------------------|--------------------------------------|------|------|------|----------------------|-----------------------------------------------------------------------------------|
| $BV_{DSS}$                     | Drain-to-Source Breakdown Voltage    | 25   | —    | —    | V                    | $V_{GS} = 0V, I_D = 1.0mA$                                                        |
| $\Delta BV_{DSS}/\Delta T_J$   | Breakdown Voltage Temp. Coefficient  | —    | 0.02 | —    | V/ $^\circ\text{C}$  | $I_D = 10mA$ ( $25^\circ\text{C}$ - $125^\circ\text{C}$ )                         |
| $R_{DS(on)}$                   | Static Drain-to-Source On-Resistance | —    | 0.9  | 1.3  | $m\Omega$            | $V_{GS} = 10V, I_D = 33A$ ⑦                                                       |
|                                |                                      | —    | 1.4  | 1.8  |                      | $V_{GS} = 4.5V, I_D = 26A$ ⑦                                                      |
| $V_{GS(th)}$                   | Gate Threshold Voltage               | 1.1  | 1.6  | 2.1  | V                    | $V_{DS} = V_{GS}, I_D = 100\mu A$                                                 |
| $\Delta V_{GS(th)}/\Delta T_J$ | Gate Threshold Voltage Coefficient   | —    | -4.3 | —    | mV/ $^\circ\text{C}$ | $V_{DS} = V_{GS}, I_D = 10mA$                                                     |
| $I_{DSS}$                      | Drain-to-Source Leakage Current      | —    | —    | 500  | $\mu A$              | $V_{DS} = 20V, V_{GS} = 0V$                                                       |
| $I_{GSS}$                      | Gate-to-Source Forward Leakage       | —    | —    | 100  | nA                   | $V_{GS} = 16V$                                                                    |
|                                | Gate-to-Source Reverse Leakage       | —    | —    | -100 |                      | $V_{GS} = -16V$                                                                   |
| $g_{fs}$                       | Forward Transconductance             | 255  | —    | —    | S                    | $V_{DS} = 13V, I_D = 26A$                                                         |
| $Q_g$                          | Total Gate Charge                    | —    | 26   | 39   | nC                   | $V_{DS} = 13V$<br>$V_{GS} = 4.5V$<br>$I_D = 26A$<br>See Fig.15                    |
| $Q_{gs1}$                      | Pre-Vth Gate-to-Source Charge        | —    | 6.6  | —    |                      |                                                                                   |
| $Q_{gs2}$                      | Post-Vth Gate-to-Source Charge       | —    | 2.8  | —    |                      |                                                                                   |
| $Q_{gd}$                       | Gate-to-Drain Charge                 | —    | 9.8  | —    |                      |                                                                                   |
| $Q_{godr}$                     | Gate Charge Overdrive                | —    | 6.8  | —    |                      |                                                                                   |
| $Q_{sw}$                       | Switch Charge ( $Q_{gs2} + Q_{gd}$ ) | —    | 12.6 | —    |                      |                                                                                   |
| $Q_{oss}$                      | Output Charge                        | —    | 31   | —    | nC                   | $V_{DS} = 16V, V_{GS} = 0V$                                                       |
| $R_G$                          | Gate Resistance                      | —    | 0.3  | —    | $\Omega$             |                                                                                   |
| $t_{d(on)}$                    | Turn-On Delay Time                   | —    | 16   | —    | ns                   | $V_{DD} = 13V, V_{GS} = 4.5V$ ⑦<br>$I_D = 26A$<br>$R_G = 1.8\Omega$<br>See Fig.17 |
| $t_r$                          | Rise Time                            | —    | 42   | —    |                      |                                                                                   |
| $t_{d(off)}$                   | Turn-Off Delay Time                  | —    | 20   | —    |                      |                                                                                   |
| $t_f$                          | Fall Time                            | —    | 14   | —    |                      |                                                                                   |
| $C_{iss}$                      | Input Capacitance                    | —    | 4160 | —    | pF                   | $V_{GS} = 0V$<br>$V_{DS} = 13V$<br>$f = 1.0MHz$                                   |
| $C_{oss}$                      | Output Capacitance                   | —    | 1310 | —    |                      |                                                                                   |
| $C_{rss}$                      | Reverse Transfer Capacitance         | —    | 290  | —    |                      |                                                                                   |

## Diode Characteristics

|          | Parameter                                 | Min. | Typ. | Max. | Units | Conditions                                                              |
|----------|-------------------------------------------|------|------|------|-------|-------------------------------------------------------------------------|
| $I_S$    | Continuous Source Current<br>(Body Diode) | —    | —    | 33   | A     | MOSFET symbol<br>showing the<br>integral reverse<br>p-n junction diode. |
| $I_{SM}$ | Pulsed Source Current<br>(Body Diode) ⑤   | —    | —    | 260  |       |                                                                         |
| $V_{SD}$ | Diode Forward Voltage                     | —    | —    | 0.75 | V     | $T_J = 25^\circ\text{C}, I_S = 26A, V_{GS} = 0V$ ⑦                      |
| $t_{rr}$ | Reverse Recovery Time                     | —    | 28   | 42   | ns    | $T_J = 25^\circ\text{C}, I_F = 26A$                                     |
| $Q_{rr}$ | Reverse Recovery Charge                   | —    | 56   | 84   | nC    | $di/dt = 340A/\mu s$ ⑦                                                  |



### Notes:

⑦ Pulse width  $\leq 400\mu s$ ; duty cycle  $\leq 2\%$ .

### Absolute Maximum Ratings

|                                        | Parameter                  | Max.         | Units |
|----------------------------------------|----------------------------|--------------|-------|
| P <sub>D</sub> @ T <sub>A</sub> = 25°C | Power Dissipation ③⑩       | 2.1          | W     |
| P <sub>D</sub> @ T <sub>A</sub> = 70°C | Power Dissipation ③⑩       | 1.3          |       |
| P <sub>D</sub> @ T <sub>C</sub> = 25°C | Power Dissipation ④        | 54           |       |
| T <sub>P</sub>                         | Peak Soldering Temperature | 270          | °C    |
| T <sub>J</sub>                         | Operating Junction and     | -40 to + 150 |       |
| T <sub>STG</sub>                       | Storage Temperature Range  |              |       |

### Thermal Resistance

|                    | Parameter                | Typ.  | Max. | Units                     |
|--------------------|--------------------------|-------|------|---------------------------|
| $R_{\theta JA}$    | Junction-to-Ambient ③⑩   | —     | 60   | $^\circ\text{C}/\text{W}$ |
| $R_{\theta JA}$    | Junction-to-Ambient ⑧⑩   | 12.5  | —    |                           |
| $R_{\theta JA}$    | Junction-to-Ambient ⑨⑩   | 20    | —    |                           |
| $R_{\theta JC}$    | Junction-to-Case ④       | —     | 2.3  |                           |
| $R_{\theta J-PCB}$ | Junction-to-PCB Mounted  | 1.0   | —    |                           |
|                    | Linear Derating Factor ③ | 0.017 |      | $\text{W}/^\circ\text{C}$ |





Fig 3. Maximum Effective Transient Thermal Impedance, Junction-to-Ambient ③

#### Notes:


③ Used double sided cooling, mounting pad with large heatsink.

⑧ Mounted on minimum footprint full size board with metalized back and with small clip heatsink.


⑩  $R_{\theta}$  is measured at  $T_J$  of approximately  $90^\circ\text{C}$ .




③ Surface mounted on 1 in. square Cu (still air).




⑧ Mounted to a PCB with small clip heatsink (still air)




⑨ Mounted on minimum footprint full size board with metalized back and with small clip heatsink (still air)




**Fig 4.** Typical Output Characteristics




**Fig 5.** Typical Output Characteristics




**Fig 6.** Typical Transfer Characteristics




**Fig 7.** Normalized On-Resistance vs. Temperature




**Fig 8.** Typical Capacitance vs. Drain-to-Source Voltage




**Fig 9.** Typical On-Resistance vs. Drain Current and Gate Voltage




**Fig 10.** Typical Source-Drain Diode Forward Voltage




**Fig 11.** Maximum Safe Operating Area




**Fig 12.** Maximum Drain Current vs. Case Temperature




**Fig 13.** Typical Threshold Voltage vs. Junction Temperature




**Fig 14.** Maximum Avalanche Energy vs. Drain Current




**Fig 15a.** Gate Charge Test Circuit




**Fig 15b.** Gate Charge Waveform




**Fig 16a.** Unclamped Inductive Test Circuit




**Fig 16b.** Unclamped Inductive Waveforms



**Fig 17a.** Switching Time Test Circuit



**Fig 17b.** Switching Time Waveforms




**Fig 18.** Diode Reverse Recovery Test Circuit for HEXFET® Power MOSFETs

## DirectFET®*plus* Board Footprint, MX Outline (Medium Size Can, X-Designation).

Please see DirectFET application note AN-1035 for all details regarding the assembly of DirectFET®*plus*.

This includes all recommendations for stencil and substrate designs.




# IRF6894MTRPbF


International  
**IR** Rectifier

## DirectFET<sup>®</sup>*plus* Outline Dimension, MX Outline (Medium Size Can, X-Designation).


Please see DirectFET application note AN-1035 for all details regarding the assembly of DirectFET<sup>®</sup>*plus*. This includes all recommendations for stencil and substrate designs.



## DirectFET<sup>®</sup>*plus* Part Marking




## DirectFET<sup>®</sup>*plus* Tape & Reel Dimension (Showing component orientation).



NOTE: Controlling dimensions in mm  
Std reel quantity is 4800 parts. (ordered as IRF6894MTRPBF). For 1000 parts on 7" reel, order IRF6894MTR1PBF

| REEL DIMENSIONS            |        |      |          |       |                       |       |          |      |
|----------------------------|--------|------|----------|-------|-----------------------|-------|----------|------|
| STANDARD OPTION (QTY 4800) |        |      |          |       | TR1 OPTION (QTY 1000) |       |          |      |
|                            | METRIC |      | IMPERIAL |       | METRIC                |       | IMPERIAL |      |
| CODE                       | MIN    | MAX  | MIN      | MAX   | MIN                   | MAX   | MIN      | MAX  |
| A                          | 330.0  | N.C  | 12.992   | N.C   | 177.77                | N.C   | 6.9      | N.C  |
| B                          | 20.2   | N.C  | 0.795    | N.C   | 19.06                 | N.C   | 0.75     | N.C  |
| C                          | 12.8   | 13.2 | 0.504    | 0.520 | 13.5                  | 12.8  | 0.53     | 0.50 |
| D                          | 1.5    | N.C  | 0.059    | N.C   | 1.5                   | N.C   | 0.059    | N.C  |
| E                          | 100.0  | N.C  | 3.937    | N.C   | 58.72                 | N.C   | 2.31     | N.C  |
| F                          | N.C    | 18.4 | N.C      | 0.724 | N.C                   | 13.50 | N.C      | 0.53 |
| G                          | 12.4   | 14.4 | 0.488    | 0.567 | 11.9                  | 12.01 | 0.47     | N.C  |
| H                          | 11.9   | 15.4 | 0.469    | 0.606 | 11.9                  | 12.01 | 0.47     | N.C  |

LOADED TAPE FEED DIRECTION



NOTE: CONTROLLING  
DIMENSIONS IN MM

| DIMENSIONS |        |       |          |       |
|------------|--------|-------|----------|-------|
| CODE       | METRIC |       | IMPERIAL |       |
|            | MIN    | MAX   | MIN      | MAX   |
| A          | 7.90   | 8.10  | 0.311    | 0.319 |
| B          | 3.90   | 4.10  | 0.154    | 0.161 |
| C          | 11.90  | 12.30 | 0.469    | 0.484 |
| D          | 5.45   | 5.55  | 0.215    | 0.219 |
| E          | 5.10   | 5.30  | 0.201    | 0.209 |
| F          | 6.50   | 6.70  | 0.256    | 0.264 |
| G          | 1.50   | N.C   | 0.059    | N.C   |
| H          | 1.50   | 1.60  | 0.059    | 0.063 |

Data and specifications subject to change without notice.  
This product has been designed and qualified for the Consumer market.  
Qualification Standards can be found on IR's Web site.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[IRF6894MTR1PBF](#)