

# IRL3402PbF



HEXFET® Power MOSFET

- Advanced Process Technology
- Optimized for 4.5V-7.0V Gate Drive
- Ideal for CPU Core DC-DC Converters
- Fast Switching
- Lead-Free

## Description

These HEXFET Power MOSFETs were designed specifically to meet the demands of CPU core DC-DC converters. Advanced processing techniques combined with an optimized gate oxide design results in a die sized specifically to offer maximum efficiency at minimum cost.

The TO-220 package is universally preferred for all commercial-industrial applications at power dissipation levels to approximately 50 watts. The low thermal resistance and low package cost of the TO-220 contribute to its wide acceptance throughout the industry.



## Absolute Maximum Ratings

|                           | Parameter                                                         | Max.                   | Units |
|---------------------------|-------------------------------------------------------------------|------------------------|-------|
| $I_D @ T_C = 25^\circ C$  | Continuous Drain Current, $V_{GS} @ 5.0V$                         | 85 Ⓢ                   | A     |
| $I_D @ T_C = 100^\circ C$ | Continuous Drain Current, $V_{GS} @ 5.0V$                         | 54                     |       |
| $I_{DM}$                  | Pulsed Drain Current ①                                            | 340                    |       |
| $P_D @ T_C = 25^\circ C$  | Power Dissipation                                                 | 110                    | W     |
|                           | Linear Derating Factor                                            | 0.91                   | W/°C  |
| $V_{GS}$                  | Gate-to-Source Voltage                                            | $\pm 10$               | V     |
| $V_{GSM}$                 | Gate-to-Source Voltage<br>(Start Up Transient, $t_p = 100\mu s$ ) | 14                     | V     |
| $E_{AS}$                  | Single Pulse Avalanche Energy ②                                   | 290                    | mJ    |
| $I_{AR}$                  | Avalanche Current ①                                               | 51                     | A     |
| $E_{AR}$                  | Repetitive Avalanche Energy ①                                     | 11                     | mJ    |
| $dv/dt$                   | Peak Diode Recovery $dv/dt$ ③                                     | 5.0                    | V/ns  |
| $T_J$                     | Operating Junction and                                            | -55 to + 150           | °C    |
| $T_{STG}$                 | Storage Temperature Range                                         |                        |       |
|                           | Soldering Temperature, for 10 seconds                             | 300 (1.6mm from case ) |       |
|                           | Mounting torque, 6-32 or M3 screw                                 | 10 lbf•in (1.1N•m)     |       |

## Thermal Resistance


|                 | Parameter                           | Typ. | Max. | Units |
|-----------------|-------------------------------------|------|------|-------|
| $R_{\theta JC}$ | Junction-to-Case                    | —    | 1.1  | °C/W  |
| $R_{\theta CS}$ | Case-to-Sink, Flat, Greased Surface | 0.50 | —    |       |
| $R_{\theta JA}$ | Junction-to-Ambient                 | —    | 62   |       |

# IRL3402PbF

International  
IR Rectifier

## Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

|                                 | Parameter                            | Min. | Typ. | Max.  | Units    | Conditions                                           |
|---------------------------------|--------------------------------------|------|------|-------|----------|------------------------------------------------------|
| $V_{(BR)DSS}$                   | Drain-to-Source Breakdown Voltage    | 20   | —    | —     | V        | $V_{GS} = 0V, I_D = 250\mu A$                        |
| $\Delta V_{(BR)DSS}/\Delta T_J$ | Breakdown Voltage Temp. Coefficient  | —    | 0.02 | —     | V/°C     | Reference to $25^\circ\text{C}$ , $I_D = 1mA$        |
| $R_{DS(on)}$                    | Static Drain-to-Source On-Resistance | —    | —    | 0.010 | $\Omega$ | $V_{GS} = 4.5V, I_D = 51A$ ②                         |
|                                 |                                      | —    | —    | 0.008 |          | $V_{GS} = 7.0V, I_D = 51A$ ③                         |
| $V_{GS(th)}$                    | Gate Threshold Voltage               | 0.70 | —    | —     | V        | $V_{DS} = V_{GS}, I_D = 250\mu A$                    |
| $g_{fs}$                        | Forward Transconductance             | 65   | —    | —     | S        | $V_{DS} = 10V, I_D = 51A$                            |
| $I_{DSS}$                       | Drain-to-Source Leakage Current      | —    | —    | 25    | $\mu A$  | $V_{DS} = 20V, V_{GS} = 0V$                          |
|                                 |                                      | —    | —    | 250   |          | $V_{DS} = 16V, V_{GS} = 0V, T_J = 150^\circ\text{C}$ |
| $I_{GSS}$                       | Gate-to-Source Forward Leakage       | —    | —    | 100   | nA       | $V_{GS} = 10V$                                       |
|                                 | Gate-to-Source Reverse Leakage       | —    | —    | -100  |          | $V_{GS} = -10V$                                      |
| $Q_g$                           | Total Gate Charge                    | —    | —    | 78    | nC       | $I_D = 51A$                                          |
| $Q_{gs}$                        | Gate-to-Source Charge                | —    | —    | 18    |          | $V_{DS} = 10V$                                       |
| $Q_{gd}$                        | Gate-to-Drain ("Miller") Charge      | —    | —    | 30    |          | $V_{GS} = 4.5V$ , See Fig. 6 ④                       |
| $t_{d(on)}$                     | Turn-On Delay Time                   | —    | 10   | —     | ns       | $V_{DD} = 10V$                                       |
| $t_r$                           | Rise Time                            | —    | 140  | —     |          | $I_D = 51A$                                          |
| $t_{d(off)}$                    | Turn-Off Delay Time                  | —    | 80   | —     |          | $R_G = 5.0\Omega, V_{GS} = 4.5V$                     |
| $t_f$                           | Fall Time                            | —    | 120  | —     |          | $R_D = 0.19\Omega$ , ④                               |
| $L_D$                           | Internal Drain Inductance            | —    | 4.5  | —     | nH       | Between lead,<br>6mm (0.25in.)                       |
| $L_S$                           | Internal Source Inductance           | —    | 7.5  | —     |          | from package<br>and center of die contact            |
| $C_{iss}$                       | Input Capacitance                    | —    | 3300 | —     | pF       | $V_{GS} = 0V$                                        |
| $C_{oss}$                       | Output Capacitance                   | —    | 1400 | —     |          | $V_{DS} = 15V$                                       |
| $C_{rss}$                       | Reverse Transfer Capacitance         | —    | 510  | —     |          | $f = 1.0MHz$ , See Fig. 5                            |



## Source-Drain Ratings and Characteristics

|          | Parameter                                 | Min.                                                                        | Typ. | Max. | Units | Conditions                                                              |
|----------|-------------------------------------------|-----------------------------------------------------------------------------|------|------|-------|-------------------------------------------------------------------------|
| $I_S$    | Continuous Source Current<br>(Body Diode) | —                                                                           | —    | 85   | A     | MOSFET symbol<br>showing the<br>integral reverse<br>p-n junction diode. |
| $I_{SM}$ | Pulsed Source Current<br>(Body Diode) ①   | —                                                                           | —    | 340  |       |                                                                         |
| $V_{SD}$ | Diode Forward Voltage                     | —                                                                           | —    | 1.3  | V     | $T_J = 25^\circ\text{C}, I_S = 51A, V_{GS} = 0V$ ④                      |
| $t_{rr}$ | Reverse Recovery Time                     | —                                                                           | 72   | 110  | ns    | $T_J = 25^\circ\text{C}, I_F = 51A$                                     |
| $Q_{rr}$ | Reverse Recovery Charge                   | —                                                                           | 160  | 240  | nC    | $di/dt = 100A/\mu s$ ④                                                  |
| $t_{on}$ | Forward Turn-On Time                      | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S + L_D$ ) |      |      |       |                                                                         |

### Notes:


① Repetitive rating; pulse width limited by max. junction temperature.

② Starting  $T_J = 25^\circ\text{C}$ ,  $L = 220\mu H$   
 $R_G = 25\Omega$ ,  $I_{AS} = 51A$ .


③  $I_{SD} \leq 51A$ ,  $di/dt \leq 82A/\mu s$ ,  $V_{DD} \leq V_{(BR)DSS}$ ,  
 $T_J \leq 150^\circ\text{C}$

④ Pulse width  $\leq 300\mu s$ ; duty cycle  $\leq 2\%$ .


⑤ Calculated continuous current based on maximum allowable junction temperature; for recommended current-handling of the package refer to Design Tip # 93-4




**Fig 1.** Typical Output Characteristics



**Fig 2.** Typical Output Characteristics




**Fig 3.** Typical Transfer Characteristics




**Fig 4.** Normalized On-Resistance Vs. Temperature

# IRL3402PbF


International  
**IR** Rectifier




**Fig 5.** Typical Capacitance Vs. Drain-to-Source Voltage




**Fig 6.** Typical Gate Charge Vs. Gate-to-Source Voltage




**Fig 7.** Typical Source-Drain Diode Forward Voltage




**Fig 8.** Maximum Safe Operating Area




**Fig 9.** Maximum Drain Current Vs. Case Temperature




**Fig 10.** Maximum Avalanche Energy Vs. Drain Current



**Fig 11.** Maximum Effective Transient Thermal Impedance, Junction-to-Case



**Fig 12.** On-Resistance Vs. Drain Current





**Fig 13.** On-Resistance Vs. Gate Voltage

## TO-220AB Package Outline

Dimensions are shown in millimeters (inches)

## IRL3402PbF



### NOTES:

- 1 DIMENSIONING & TOLERANCING PER ANSI Y14.5M, 1982.
- 2 CONTROLLING DIMENSION : INCH

- 3 OUTLINE CONFORMS TO JEDEC OUTLINE TO-220AB.
- 4 HEATSINK & LEAD MEASUREMENTS DO NOT INCLUDE BURRS.


## TO-220AB Part Marking Information

EXAMPLE: THIS IS AN IRF1010

LOT CODE 1789

ASSEMBLED ON WW 19, 1997  
IN THE ASSEMBLY LINE "C"

**Note:** "P" in assembly line  
position indicates "Lead-Free"



Data and specifications subject to change without notice.

Note: For the most current drawings please refer to the IR website at:  
<http://www.irf.com/package/>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[IRL3402SPBF](#)