Series PVT312PbF

Microelectronic Power IC

HEXFET[®] Power MOSFET Photovoltaic Relay Single-Pole, Normally-Open, 0-250V, 190mA AC/DC

General Description

The PVT312 Photovoltaic Relay is a single-pole, normally open solid-state relay that can replace electromechanical relays in many applications. It utilizes International Rectifier's proprietary HEXFET power MOSFET as the output switch, driven by an integrated circuit photovoltaic generator of novel construction. The output switch is controlled by radiation from a GaAIAs light emitting diode (LED) which is optically isolated from the photovoltaic generator.


This SSR is specifically designed for telecom applications. PVT312L employs an active current-limiting circuitry enabling it to withstand current surge transients.

PVT312 Relays are packaged in a 6-pin, molded DIP package with either thru-hole or surface mount

("gull-wing") terminals. It is available in standard plastic shipping tubes or on tape-and-reel. Please refer to the Part Identification information opposite.

Features

- HEXFET Power MOSFET output
- Bounce-free operation
- 4,000 V_{RMS} I/O isolation
- Load current limiting
- Linear AC/DC operation
- Solid-State Reliability
- UL recognized and BABT certified;
- ESD Tolerance: 4000V Human Body Model 500V Machine Model



Applications

- On/Off Hook switch
- Dial-Out relay
- Ring injection relay
- Ground start
- General switching

Part Identification

PVT312LPbF PVT312LSPbF PVT312LS-TPbF

PVT312PbF PVT312SPbF PVT312S-TPbF current limit, thru-hole current limit, surface-mount current limit, surface-mount, tape and reel no current limit, thru-hole no current limit, surface-mount no current limit, surface-mount tape and reel

(HEXFET is the registered trademark for International Rectifier Power MOSFETs)

Electrical Specifications (-40°C \leq T_A \leq +85°C unless otherwise specified)


| INPUT CHARACTERISTICS | | art Ni | Units | |
|---|-----|-----------|--------|------------------|
| | PVT | 312L | PVT312 | |
| Minimum Control Current (see figures 1 and 2) | 2.0 | | mA | |
| Maximum Control Current for Off-State Resistance @ T _A =+25°C | 0.4 | | mA | |
| Control Current Range (Caution: current limit input LED, see figure 6) | | 2.0 | to 25 | mA |
| Maximum Reverse Voltage | | 6.0 | | V |
| OUTPUT CHARACTERISTICS | PVT | 312L | PVT312 | |
| Operating Voltage Range | | 0 to ±250 | | V(DC or AC peak) |
| Maximum Load Current @ T _A =+40°C, 5mA Control (see figures 1 and 2) | | | | , |
| A Connection | 17 | '0 | 190 | mA (AC or DC) |
| B Connection | 19 | 0 | 210 | mA (DC) |
| C Connection | 30 | 0 | 320 | mA (DC) |
| Maximum On-State Resistance @T _A =+25°C for 50mA pulsed load | | | | |
| 5mA Control (see figure4) | | | | |
| A Connection | 1 | 5 | 10 | Ω |
| B Connection | 8 | } | 5.5 | Ω |
| C Connection | 4.2 | 25 | 3 | Ω |
| Maximum Off-State Leakage @T _A =+25°C, ±250V (see figure 5) | | 1.0 | | μA |
| Current Limit @T _A =+25°C, 5mA Control | | | | |
| Connection: | A | С | | |
| Minimum | 190 | 330 | n/a | mA |
| Maximum | 300 | 560 | n/a | mA |
| Maximum Turn-On Time @T _A =+25°C (see figure 7) | | 3.0 | | ms |
| for 50mA, 100 V _{DC} load, 5mA Control | | | | |
| Maximum Turn-Off Time @T _A =+25°C (See Fig. 6) | 0.5 | | ms | |
| For 50mA, 100 V _{DC} load, 5mA Control | | | | |
| Maximum Output Capacitance @ 50VDC | 50 | | pF | |
| GENERAL CHARACTERISTICS | | ALL M | ODELS | |
| Minimum Dielectric Strength, Input-Output | | 4000 | | V _{RMS} |
| Minimum Insulation Resistance, Input-Output @T _A =+25°C, 50%RH, 100V _{DC} | + | |)12 | |
| | | | | |


| Minimum Insulation Resistance, Input- | Output @1 _A =+25°C, 50%RH, 100V _{DC} | 1012 | Ω |
|---------------------------------------|--|-------------|----|
| Maximum Capacitance, Input-Output | | 1.0 | pF |
| Maximum Pin Soldering Temperature (| 10 seconds maximum) | +260 | °C |
| Ambient Temperature Range: | Operating | -40 to +85 | °C |
| | Storage | -40 to +100 | |


International Rectifier does not recommend the use of this product in aerospace, avionics, military or life support applications. Users of this International Rectifier product in such applications assume all risks of such use and indemnify International Rectifier against all damages resulting from such use.



Connection Diagrams







C" Connection




Figure 1. Typical Current Derating Curves




Figure 3. Linearity Characteristics





Figure 2. Typical Current Derating Curves










Figure 5. Typical Normalized Off-State Leakage




Figure 7. Typical Delay Times




Figure 6. Input Characteristics (Current Controlled)




Figure 8. Delay Time Definitions





Figure 9. Typical Output Capacitance



Case Outlines



Note: For the most current drawing please refer to IR website at: <u>http://www.irf.com/package/</u>



Qualification information[†]

| Qualification level | Industrial (per JEDEC JESD47I ^{††} guidelines) | | | | |
|-------------------------------|--|--|--|--|--|
| Moisture Sensitivity Level | PVT312LPbF | N/A | | | |
| | PVT312PbF | N/A | | | |
| | PVT312LSPbF | MSL4 | | | |
| | PVT312LS-TPbF | IVISL4 | | | |
| | PVT312SPbF | | | | |
| | PVT312S-TPbF | (per JEDEC J-STD-020E & JEDEC J-STD-033C | | | |
| RoHS compliant | Yes | | | | |

† Qualification standards can be found at International Rectifier's web site: http://www.irf.com/product-info/reliability

the time of product release

Revision History

| Date | Comments | |
|-----------|---|--|
| 5/18/2015 | Added Qualification Information Table on page 6 | |
| | Updated data sheet with new IR corporate template | |



IR WORLD HEADQUARTERS: 101 N. Sepulveda Blvd., El Segundo, California 90245, USA Data and specifications subject to change without notice To contact International Rectifier, please visit <u>http://www.irf.com/whoto-call/</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Infineon:

PVT312LPBF PVT312LS-TPBF PVT312PBF PVT312S-TPBF PVT312LSPBF PVT312SPBF