



## SPECIFICATIONS: LINEAR POWER SUPPLY IHAAS-1.5/OVP

**MADE IN THE U.S.A.**

<b>VAC INPUT:</b> <ul style="list-style-type: none"><li>100/120/220/240 VAC, +10%, -13%</li><li>TOLERANCE FOR 230 VAC IS +15%, -10%</li><li>FREQUENCY RANGE: 47-63HZ</li></ul>	<b>VAC JUMPERING AND FUSING REQUIREMENTS:</b> SILKSCREENED ON CHASSIS FOR TRANSFORMER PRIMARY TERMINALS <table><tr><td>For Use at</td><td>100VAC</td><td>120VAC</td><td>220VAC</td><td>230/240VAC</td></tr><tr><td>Jumper</td><td>1&amp;3, 2&amp;4</td><td>1&amp;3, 2&amp;4</td><td>2&amp;3</td><td>2&amp;3</td></tr><tr><td>Apply AC</td><td>1&amp;5</td><td>1&amp;4</td><td>1&amp;5</td><td>1&amp;4</td></tr><tr><td>Max Current / Fuse Rating</td><td colspan="2">0.5A</td><td colspan="2">0.25A</td></tr></table>	For Use at	100VAC	120VAC	220VAC	230/240VAC	Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3	Apply AC	1&5	1&4	1&5	1&4	Max Current / Fuse Rating	0.5A		0.25A	
For Use at	100VAC	120VAC	220VAC	230/240VAC																	
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3																	
Apply AC	1&5	1&4	1&5	1&4																	
Max Current / Fuse Rating	0.5A		0.25A																		
<b>VDC OUTPUT:</b> <ul style="list-style-type: none"><li>+/-5 VDC @ 1.5 AMP</li></ul>	<b>OVERVOLTAGE PROTECTION:</b> <ul style="list-style-type: none"><li>PROVIDED. FACTORY SET AT 6.2VDC, +/- 0.4VDC</li></ul> <b>SHORT CIRCUIT PROTECTION:</b> <ul style="list-style-type: none"><li>AUTOMATIC FOLDBACK</li></ul> <b>OVERLOAD PROTECTION:</b> <ul style="list-style-type: none"><li>AUTOMATIC CURRENT LIMIT</li></ul>																				
<b>LINE REGULATION:</b> <ul style="list-style-type: none"><li>+/- 0.05% FOR A 10% LINE CHANGE</li></ul>	<b>LOAD REGULATION:</b> <ul style="list-style-type: none"><li>+/- 0.05% FOR A 50% LOAD CHANGE (DERATE OUTPUT CURRENT 10% FOR 50 HZ OPERATION)</li></ul>																				
<b>OUTPUT RIPPLE:</b> 5.0 mV PK-PK MAXIMUM	<b>TRANSIENT RESPONSE:</b> < 50 μsec per 50% LOAD CHANGE																				
<b>TEMPERATURE RATINGS:</b> <ul style="list-style-type: none"><li>OPERATING: 0°C TO 50°C FULL RATED DERATED LINEARLY TO 40% @ 70°C</li><li>STORAGE: -40°C TO +85°C</li></ul>	<b>TEMPERATURE COEFFICIENT:</b> <ul style="list-style-type: none"><li>TYPICAL: 0.01%/DEGREE C</li><li>MAXIMUM: 0.03%/DEGREE C</li></ul>																				
<b>STABILITY:</b> +/- 0.3% FOR 24 HOURS AFTER 1 HOUR WARM-UP	<b>EFFICIENCY (TYPICAL): 45%</b>																				
<b>VIBRATION:</b> <ul style="list-style-type: none"><li>MIL-STD-810G, METHOD 514.6, CATEGORY 1, PROCEDURE1</li><li>RANDOM VIBRATION 10Hz - 2KHz, 6.15 grams (3 axis)</li></ul>	<b>SHOCK:</b> <ul style="list-style-type: none"><li>MIL-STD-810G, METHOD 516.6, PROCEDURE III</li><li>OPERATING: 20 GPK</li></ul>																				
<b>REMOTE SENSING:</b> NOT PROVIDED	<b>EMI/RFI:</b> INHERENT LOW CONDUCTED AND REDIATED NOISE LEVELS. <ul style="list-style-type: none"><li>EMI: FCC CFR TITLE 47 PART 15 SUB-PART B</li><li>RFI: EN55022/CISPR22-LEVEL B COMPATIBILITY</li></ul>																				

UL recognized for US and Canada – File#E133338/ CE Mark: LVD 92/59/EEC/ RoHs-5 Lead in Solder Exemption  
 US and Canadian (Bi-National) standards: ANSI/UL 60950-1/-21; CAN/CSA C22.2 #60950-1/-21; IEC 60950-1




## CASE SIZE: AA

### AA Case

Overall Size: 6.50" x 4.00" x 2.10"

165.10mm x 101.60mm x 53.34mm

Weight 2 lbs.



	INCH	mm
A	4.00	101.60
B	3.375	85.73
C	6.50	165.10
D	5.750	146.05
E	0.75	19.05
F	0.450	11.43
G	1.62	41.15
H	0.25	6.35
J	0.50	12.70
K	0.955	24.26
L	2.37	60.20
M	0.57	14.48

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[International Power:](#)

[IHA5-1.5/OVP](#)