


4

3

2

1



2X $\varnothing 5 \pm 0.10$ MAX
M6X1.0 - 6H ± 0.05 MIN
SEE NOTE 1

NEGATIVE
TERMINAL

AXIS A

2° Draft

(4.60)

2° Draft

(6.55)

AXIS B

2X $\varnothing 5 \pm 0.10$ MAX
M6X1.0 - 6H ± 0.05 MIN
SEE NOTE 1



NOTES: 1. Axes A-B, Max Angular Offest $\pm 3^\circ$

UNLESS OTHERWISE SPECIFIED; DIMENSIONS ARE IN MILLIMETERS. TOLERANCES ARE AS FOLLOW: 1 PLACE ±0.1 2 PLACE ±0.05 ANGULAR ±0.5° CONCENTRICITY .05 TIR			TITLE: 2.7V, 1200F ULTRACAPACITOR
			PART NUMBER: RSC2R7128LR
INFORMATION IN THIS DRAWING IS FOR REFERENCE ONLY.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IOXUS:](#)

[RSC2R7128LR](#)