



0.4mm Pitch, Stacking Type  
Board-to-Board Connector


## WP6 Series

CONNECTOR


MB-0230-2

March 2014

### RoHS Compliant



Plug



Receptacle

The WP6 Series is a low-profile stacking type board-to-board (FPC) connector with 0.4mm pitch spacing that is ideal for high-density mounting in slim information communication devices like mobile phones, smartphones, and notebook PC. To satisfy different product function requirements, plug and receptacle with different heights (mating height: 0.6mm, 0.8mm) are available with the same mounting pattern.

### Features

- 0.4mm pitch, 2 rows, stacking height 0.6mm and 0.8mm.
  - Contact structure ensures high wear-resistance and high contact reliability.
  - Secure hold-downs prevent insulator breakage and peeling from FPC.
  - 2-point contact design to resist twisting stress.
  - Pb-free. Ni barrier on contact prevents solder wicking.
- \* Inspection jig connector for both plug and receptacle are available. (Note 1)

### General Specifications

■No. of Contacts: 10 to 80 pos.  
(Please refer to Development Status on the last page regarding development of contacts.)

■Pitch: 0.4mm, 2 rows

■Operating Temperature:  
-40 Deg. C to +85 Deg. C

■Contact Resistance: 70mΩ max (initial)

■Life Time: 30 mating cycles

■Rated Current:  
AC, DC 0.3A each per terminal

■Rated Voltage: AC, DC 50V

■Insulation Resistance: 100MΩ min. (initial)

■Dielectric Withstanding Voltage:  
AC250Vr.m.s for 1 minute

■Total Insertion Force: 1.5N x n max. (n: No. of pos.)

■Total Extraction Force: 0.1N x n min. (n: No. of pos.)

■Less than 20 pos. Total Insertion Force: 2.5N x n max. (n: No. of pos.)


■Less than 20 pos. Total Extraction Force: 0.2N x n min. (n: No. of pos.)

Note 1) Please contact us for specifications of inspection jig connector.


## Materials and Finishes

Component	Material / Finish
Contact	Contact area: Cu alloy / Au plating (0.1 μm min.) Mounting area: Cu alloy / Au plating (0.05 μm min.)
Insulator	Heat-resistant plastic
Hold-Down	Plug: Cu alloy / Au plating (0.1μm min.) Receptacle: Cu alloy / Sn plating

## Ordering Information (Plug)



## Ordering Information (Receptacle)




Note 1) An embossed tape reel contains 6,000 pieces of standard product, or 300 pieces of inspection jig product. Please contact us for details on embossed tape specifications.



## WP6 (Height 0.6mm) Plug



## WP6 (Height 0.6mm) Receptacle





WP6 (Height 0.8mm) Plug



JA-E PMK Div. Proprietary. Copyright © 2014, Japan Aviation Electronics Industry, Ltd. 5/8

## WP6 (Height 0.8mm) Receptacle



Note 1) Dimension  $3.9 \pm 0.05$  is recommended in case repair is needed.

## Technical Documents

Series	WP6
Drawing No. (Plug, Height 0.6mm)	Individual Product: SJ111683 Embossed Reel: SJ111685
Drawing No. (Receptacle, Height 0.6mm)	Individual Product: SJ111684 Embossed Reel: SJ111686
Drawing No. (Plug, Height 0.8mm)	Individual Product: SJ111687 Embossed Reel: SJ111689
Drawing No. (Receptacle, Height 0.8mm)	Individual Product: SJ111688 Embossed Reel: SJ111690
Specification	JACS-10797
Handling Instruction	JAHL-10798
Summary Report	SR-C-1002

Development Status
--------------------

No. of Contacts	Height 0.6mm	Height 0.8mm
10	Samples available	Now in mass-production
12		Now in mass-production
14	Now in mass-production	
16	Samples available	Now in mass-production
20	Samples available	Now in mass-production
24	Now in mass-production	Now in mass-production
26	Samples available	
30	Samples available	Now in mass-production
34	Samples available	
40	Samples available	Samples available
50	Samples available	Now in mass-production
60	Now in mass-production	Samples available
80	Samples available	Samples available

## Japan Aviation Electronics Industry, Limited

Product Marketing Division  
Aobadai Building, 3-1-19, Aobadai, Meguro-ku, Tokyo 153-8539  
Phone: +81-3-3780-2787 FAX: +81-3-3780-2946

**Notice:** Products shown in this brochure are made for the applications listed below. However, if the above-mentioned products are to be used in aerospace devices, marine cable-connection devices, atomic power control systems, medical equipment for life-support systems, or any other specific application requiring extremely high reliability, please contact JAE for further information.

Recommended applications: Computers, Office machines, Measuring devices, Telecommunication devices (Terminals, Mobile devices), AV devices, Household applications, FA devices, etc.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## JAE Electronics:

<a href="#"><u>WP6-S010VA2-R6000</u></a>	<a href="#"><u>WP6-P010VA2-R6000</u></a>	<a href="#"><u>WP6-P012VA2-R6000</u></a>	<a href="#"><u>WP6-P016VA2-R6000</u></a>	<a href="#"><u>WP6-P020VA2-R6000</u></a>
<a href="#"><u>WP6-P024VA2-R6000</u></a>	<a href="#"><u>WP6-P030VA2-R6000</u></a>	<a href="#"><u>WP6-P050VA2-R6000</u></a>	<a href="#"><u>WP6-S012VA2-R6000</u></a>	<a href="#"><u>WP6-S016VA2-R6000</u></a>
<a href="#"><u>WP6-S020VA2-R6000</u></a>	<a href="#"><u>WP6-S024VA2-R6000</u></a>	<a href="#"><u>WP6-S030VA2-R6000</u></a>	<a href="#"><u>WP6-S050VA2-R6000</u></a>	