


SYM.	DCN NO.	DESCRIPTION	DATE	DRAWN	CHECKED	APP'D	APP'D
------	---------	-------------	------	-------	---------	-------	-------



NOTE 1.NO PLATING ON THE SHEARED EDGES OF CONTACT.

NOTE 2.CRIMP TYPE ARE MARKED AS INDICATED.

NOTE 3.APPLICABLE WIRE SIZE IS MENTIONED BELOW.

TABLE 1

CRIMP TYPE	APPLICABLE WIRE		DIMENSIONS
	WIRE SIZE	INSULATION OUTER DIA.	A
C 1	AWG #14~16 (1.25mm~2mm)	φ 3.8MAX.	3.7
C 2	AWG #16~20 (1.25mm~0.5mm)	φ 3.8MAX.	3
C 3	AWG #20~24 (0.5mm~0.2mm)	φ 3.8MAX.	2.2

1	#16PIN CONTACT	1	COPPER ALLOY	SILVER PLATING	
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARKS
UNLESS OTHERWISE SPECIFIED: T700142		DATE 21. Apr. '95		TITLE ST-JL05-16P-C*	
DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON : (INCHES) FRACTIONS DECIMALS ANGLES		DRAWN M. OOWA		JAE-CONNECTOR.COM Reference Only JAPAN AVIATION ELECTRONICS INDUSTRY, LTD. MUSASHINO, AKISHIMA-SHI TOKYO, JAPAN DWG. NO. SJ025424-E	
		CHECKED S. NANA O			
		APP'D T. MORITA			
		APP'D M. Takagi			
		SERIES JL05		SCALE 3/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[ST-JL05-16P-C2-100](#) [ST-JL05-16P-C3-100](#) [ST-JL05-16P-C1-100](#)