

FOX3 Series

Telematics Gateway



ConsoleFlow™



LANTRONIX
Connectivity Services



ADVANCED TELEMATICS GATEWAY

Lantronix, Inc., a 30-year storied M2M and IoT specialist, designs, manufactures, and sells worldwide state-of-the-art devices, services, and solutions ideally suited to numerous applications: fleet management, car-sharing, usage-based insurance, asset and workforce tracking and security, precision farming, and more.

The Complete Package to Successfully Deploy Your Telematics Projects

Many projects fail due to the lack of integration between hardware, connectivity from service providers, critical accessories such as antennas, and the lack of adaptation to the field. Lantronix provides a versatile telematics gateway that connects the featured scenarios, connectivity, advanced support, and a device management platform, ConsoleFlow™; for device performance, location, and real-time notifications of critical events.

A Large Choice Of Hardware Interface To Connect Your Vehicle Globally

The FOX3 Series gateways are customizable, compact all-in-one devices combining cellular data connection with the latest GNSS technology and various inputs and outputs. Want to deploy in a complex industrial environment or urban canyon? The FOX3 is designed to operate with internal or external antennas and dead reckoning mode, which dramatically simplifies logistics, installation, and post-installation support.

Protect and Process in the Edge; Do Your Own Customization

Connect the FOX3 gateway to any telematics platform with powerful PFAL scripting language or the highly popular LUA. The FOX3 also supports MQTT, Azure, and REST API to ease your hardware integration and shorten your time to market.

ConsoleFlow™ Centralized Device Management Platform

Monitor, manage, and control your devices from anywhere, at any time, with the ready-to-use software platform web application. The easy-to-use platform provides software-defined automation with zero-touch provisioning across all your devices and the capture of device telemetry data for event management and analytics.

Connectivity Services - IoT Cellular Platform

Lantronix's cloud-based Connectivity Services platform allows users to activate, monitor and manage connectivity for all devices. The easy-to-use dashboard and analytics tools provide critical insights into connectivity solution operations. In addition, extensive diagnostics help troubleshoot any connectivity issues that may arise.

Perfect For



Fleet
Management



Car-sharing



Commercial
Vehicle



Asset &
Workforce
Tracking



Precision
Farming



Logistics

FOX3 Highlights

- Send to the cloud only what you need with the FOX3 edge processing and local data storage to reduce your recurring cost and ensure the fastest response time from your device.
- Keep critical data safe from cyber-attacks using advanced encryption such as AES, SSL/TLS.
- Collect vehicle information such as tachograph (FMS), RPM (x1000), temperature, and fuel levels with high accuracy using Lantronix's "Premium Features."
- Collect ID, buzz, magnetic detection, movement, and temperature using BLE sensors "approved by Lantronix" or bring your own.

LANTRONIX

General

4G /3G / 2G bands: (refer to the table below)

Internet (TCP/UDP/HTTP/SMTP)

Multi channel GNSS

(GPS/Galileo/GLONASS/BeiDou)

A-GPS (online / offline / autonomous)

Protocols: NMEA, FALCOM (binary)

Accuracy: **GPS** **GLONASS**

Position: 2.5 m 4.0 m

Acquisition / Sensitivity:

Cold Start: 29 s 30 s

Tracking: -161 dBm -158 dBm

Sensitivity: -148 dBm -145 dBm

GPS Operational limits:

Velocity: 500 m/s (972 knots)

Altitude: 50.000 m

Update rate: 1 Hz

GSM / GNSS AntennasInternal and external²⁾ with automatic/manual**Electrical Characteristics**

Power supply: +10.8 V~ 60 V DC

Internal 1000 mAh rechargeable battery¹⁾**Average Power Consumption**

Normal operation: 50mA @ 12 VDC

Sleep mode: < 1mA @ 12 VDC

Environmental Data

Operating temp.: -40°C to +85°C

Storage temp.: -40°C to +85°C

GSM³⁾: -40°C to +85°CBattery⁴⁾ Discharging temp.: -20°C to +60°C

Charging temp.: 0°C to +45°C

Physical Characteristics

Dimensions (LxWxH): 105 mm x 83 mm x 28 mm

Interfaces

3 x Digital/analog IO ports (user-configurable)

1 x Predefined digital input (Ignition)

3 x LED indicators (user-configurable)

2 x RS-232 Ports (1xV.24 level; 1xRS-232/RS-485²⁾⁵⁾)1 x 10pin Mini-USB connector (for IOBOX-MINI¹⁾,IOBOX-CAN¹⁾ or IOBOX-WLAN¹⁾)

1 x 1-Wire interface (incl. 5V Phantom Power)

1 x I²C interface1 x 4pin audio jack interface (2.5mm)⁶⁾1 x CAN-Bus Interface²⁾⁵⁾ (uses 2 of 3 I/Os)

1 x Inside SIM card holder for 1,8/3 V SIM cards

1 x USB 2.0 interface

Sensor / Measurement Range

3-axis Acceleration/Temperature

- 3DG: ± 8g (programmable)

- Temperature: - 50 to + 120°C (programmable)

Processor Core

RTC

8 MB Flash (History / Firmware / Configuration)

1) Optional / Accessory.

2) Activation with PFAL-Command.

3) The GSM/GPRS module is fully functional (-20°C to + 55°C meets the 3GPP specifications).

4) Applicable with backup battery.

Storage and using conditions of the device with battery option are limited to the battery temperature range.

5) Hardware Premium Features: CAN-interface.

6) Available on FOX3-3G-AU and FOX3-2G only.

- 3000 programmable Geofences
- 2000 programmable Waypoints
- 250 programmable Alarms
- ECO-Drive-GPS functions
- Customizable firmware configuration


- Passive/active RFID based applications
- NFC based applications
- Internal GSM/GNSS antennas & connectors for optional external antennas¹⁾
- Hardware expandable via IOBOX-MINI¹⁾, IOBOX-CAN¹⁾ or IOBOX-WLAN¹⁾
- PROMOTION KIT providing all necessary

- hardware, software, documentation, SIM Card and trial access to the ConsoleFlow™ centralized management platform including 8h technical training support
- ConsoleFlow device management platform to monitor, diagnose, control and update your devices

- Real time online tracking
- Fleet management / monitoring
- Car sharing
- Waste management
- Theft protection

- Public transportation
- Real time satellite navigation
- Territory management
- Route verification
- Trip management / distance calculations
- Driving behaviour / Eco-Drive monitoring

- Security / Emergency / Insurance services (UBI)
- Toll collection / Pay-As-You-Drive (PAYD)
- Compatible with ConsoleFlow centralized management and easily adaptable to other tracking servers



Part Number	Description
F33H002S	FOX3 4G M1 FB - Worldwide - 4G CatM1/NB1 Bands 2, 3, 4, 5, 8, 12, 13, 20 -2G FB - GNSS - Accelerometer, int & ext ant - Mini Sim - 2 X RS232 - 3 I/O - I2C - RTC - 1 Wire - Mini USB - AVL Software
F33HGZ2S	FOX3 4G M1 FB BLE-WORLDWIDE-4G CATM1/NB1 BANDS 2, 3, 4, 5, 8, 12, 13, 20-2G FB-GNSS-ACCELEROMETER, INT/EXT ANT-BT LE 4.1 -MINI SIM - 2 X RS232 -3 I/O - I2C - RTC - 1 WIRE - MINI USB - AVL SOFTWARE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lantronix:

[F35R00FS](#) [F38H000S](#) [F35H01FS](#) [F35HGZFS](#) [F33H002S](#) [F35H00FS](#)