



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
11	2.5	.200	.200	2.51	500	C-2R
56	5.0	.115	.150	1.89	40,000	C-2R
79	6.0	.200	.630	7.92	1,000	C-2R
86	6.3	.200	.400	5.03	50,000	C-2F
18	14.0	.040	.130	1.63	5,000	C-2F
73	14.0	.080	.300	3.77	15,000	C-2F
37	14.0	.090	.500	6.29	2,500	C-2F
74	14.0	.100	.700	8.80	500	C-2F
85	28.0	.040	.300	3.77	25,000	C-2F
17	28.0	.065	.650	8.17	5,000	C-2F

			METRIC		DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION			
			THIRD ANGLE PROJECTION		TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE			
					1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		T-1 3/4 STANDARD GLASS WEDGE BASE			
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	DRAWN BY	APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.	GLASS WEDGE BASE T-1 3/4	
C	DELETE LEAD (Pb) FREE NOTES	1/31/08				A	55335			
B	CHANGE #18 TO LEAD (Pb) FREE	7/12/05								
A	NOTE #73 TO LEAD (Pb) FREE	2/17/05	L. WENGSTROM	L.R.	1/31/08					
	RELEASED & CANCEL GW-STD-T1 3/4, 75X & 84	5/11/00								
			- CAD DRAWING -			SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET
			MANUAL REVISIONS NOT PERMITTED			NONE	5/11/00	1/31/08	C	1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[85](#) [86](#)