

# SRS2F Series

## Stand-alone RS232 Remotely Managed Media Converter

### RS232 Copper to Fiber



SRS2F3111-100

The SRS2F Series stand-alone serial RS232 to fiber converters allow you to extend the distance between serial connections with the use of fiber optic cable. These full-featured stand-alone converters transmit the full complement of RS232 flow control/handshaking signals optically and supports full or half-duplex asynchronous data transmission at speeds up to 115 Kbps. Link a remote terminal to a host computer: Connect multiple devices, such as security scanners, POS devices, remote terminals and building access/alarming systems to a host computer. Ideal for campus or business environments where remote devices can be networked in a point-to-point configuration where distances are greater than the 15 meter limitation of conventional copper serial cables.

In addition, these stand-alone media converters can also be managed from remote locations, in-band, over the fiber, when linked to a CRS2F Series installed in a managed Point System™ chassis.

## Features

- Remote Management
- Local or Remote Loopback on copper and fiber
- DTE/DCE switch for easy installation with straight-through cabling
- Full/Half-duplex asynchronous transmission at speeds up to 115 Kbps
- Supports the following flow control signaling:
  1. DCD - Data Carrier Detect
  2. RXD - Receive Data
  3. TXD - Transmit Data
  4. DTR - Data Terminal Ready
  5. SG - Signal Ground
  6. DSR - Data Set Ready
  7. RTS - Request To Send
  8. CTS - Clear To Send

## Specifications

Standards	EIA/TIA-574 EIA/TIA RS-232E
Data Rate	115 Kbps
Switches	DTE/DCE: Select appropriate position Loopback: Norm = normal operation; Loop = Fiber and copper loopback
Status LEDs	P: (Power): Lit for normal operation RX: Steady = Copper Link; Flashing = Rx Data FL: Steady = Fiber Link; Flashing = Loopback mode
Dimensions	Width: 3.3" [84 mm] Depth: 4.8" [122 mm] Height: 1.2" [30 mm]
Power Consumption	5 Watts
Power Supply	External AC/DC; 12 VDC, 0.5A min output; 120-240VAC input
Environment	Operating: 0°C to 50°C Humidity: 5% to 95% (non-condensing) Altitude: 0 – 10,000 ft.
Weight	2 lbs. [0.90 kg]
Compliance	Safety: Wall Mount Power Supply: UL Listed and CSA certified Emissions: CISPR22/EN55022 Class A + EN55024, EN60950 Class A, FCC Class A, CE Mark
Warranty	Lifetime

## Ordering Information

### SRS2F3111-100

DB-9 [15 m/49 ft.]  
to 1300nm multimode (ST) [2 km/1.2 mi.]  
Link Budget: 11.0 dB

### SRS2F3113-100

DB-9 [15 m/49 ft.]  
to 1300nm multimode (SC)  
[2 km/1.2 mi.] Link Budget: 11.0 dB

### SRS2F3114-100

DB-9 [15 m/49 ft.]  
to 1310nm single mode (SC) [20 km/12.4 mi.]  
Link Budget: 16.0 dB

**Optional Accessories** (sold separately)

### Wide Input (24 - 60 VDC) Power Supplies

#### SPS-2460-PS

Piggy Back Power Supply

#### SPS-2460-SA

Stand-Alone Power Supply

### Mounting Options

#### E-MCR-05

12-Slot Media Converter Rack

#### RMS19-SA4-02

4-Slot Media Converter Shelf

#### WMBD

DIN Rail Bracket 5" [127 mm]

#### WMBD-F

DIN Rail Bracket (flat) 3.3" [84 mm]

#### WMBL

Wall Mount Bracket 4" [102 mm]

#### WMBV

Vertical Wall Mount Bracket 5" [127 mm]

## Power Supply Included

To order the corresponding country specific power supply, add the extension from the list below to the end of the SKU; Ex: SRS2F3111-100-NA

### -NA = Country Code

-NA = North America  
-LA = Latin America  
-EU = Europe  
-UK = United Kingdom  
-SA = South Africa  
-JP = Japan  
-OZ = Australia  
-BR = Brazil

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Lantronix:

[SRS2F3111-100](#) [SRS2F3111-100-AR](#) [SRS2F3111-100-BR](#) [SRS2F3111-100-EU](#) [SRS2F3111-100-JP](#) [SRS2F3111-100-LA](#) [SRS2F3111-100-NA](#) [SRS2F3111-100-OZ](#) [SRS2F3111-100-SA](#) [SRS2F3111-100-UK](#) [SRS2F3113-100](#) [SRS2F3113-100-AR](#) [SRS2F3113-100-BR](#) [SRS2F3113-100-EU](#) [SRS2F3113-100-JP](#) [SRS2F3113-100-LA](#) [SRS2F3113-100-NA](#) [SRS2F3113-100-OZ](#) [SRS2F3113-100-SA](#) [SRS2F3113-100-UK](#) [SRS2F3114-100](#) [SRS2F3114-100-EU](#) [SRS2F3114-100-JP](#) [SRS2F3114-100-LA](#) [SRS2F3114-100-NA](#) [SRS2F3114-100-OZ](#) [SRS2F3114-100-SA](#) [SRS2F3114-100-UK](#)