

TILT SENSOR SWITCH

Item No.	RBS200124	Description	Ball-Contact	Version	14
Page	1 of 5		Publish Date	May 29, 2018	

● FUNCTIONS

Rotation Detection at 45° in vertical position.

● APPLICATIONS

Rotation Detection for kinds of monitor

● FEATURES

1. Suitable for vertical PCB.
2. Switch State: DIP Normal Close.
3. Tiny size, suitable for small space.
4. Gold-plated ball and terminals, low possibility of oxidization.
5. Housing made of high insulation plastic material, free from electric conduction and rust problem.
6. All plastic materials subject to industrial purpose, resist high temperature and meet fireproof function.
7. Simple ON and OFF signals, easy for design.
8. RoHS compliance, an ideal substitute for mercury switch.
9. A more economical tilt and vibration detection option than IC design solution.
10. All made in Taiwan and examined before shipment.



● PATENTS

1. Taiwan Patent No. I 239025
2. U.S.A. Patent No. US 7,045,724 B1
3. China Patent No. ZL 200410091589.7
4. China Patent No. 201220308500.8







TILT SENSOR SWITCH

Item No.	RBS200124	Description	Ball-Contact	Version	14
Page	2 of 5		Publish Date	May 29, 2018	

● DIMENSIONS / OPERATION / P.C.B. LAYOUT (Unit: mm, Tolerance: $\pm 0.25\text{mm}$)

Fig. 1

<p>RBS 20 01 24</p> 	<p>Operation Diagram</p> <p>[Tile Angle $45^\circ \pm 25^\circ$]</p>  <p>Signal change angle $\theta = 45^\circ \pm 25^\circ$</p> <p>Stable angle $\alpha < 30^\circ$</p>
<p>P.C.B. Layout<DIP>/Top View</p> 	<p>Application Circuit</p>  <p>RBS200124 (Equivalent Circuit)</p> <p>[Using keyboard scanning (Polling method) to detect the four positions]</p> <p>1 : High/Low Input Control 2 : Output Signal 3 : High/Low Input Control 4 : Output Signal</p>



TILT SENSOR SWITCH

Item No.	RBS200124	Description	Ball-Contact	Version	14
Page	3 of 5		Publish Date	May 29, 2018	

● Current/Voltage Suggested

Input Current (mA)	Operating Voltage (V)	Condition
1.0	5	--

● ELECTRICAL CHARACTERISTICS

1	Contact Rating	10 mA, 5 VDC
2	Contact Resistance	10 Ω max.
3	Operation Diagram	Refer to Fig. 1
4	Insulation Resistance	1000 MΩ min., 100 VDC
5	Dielectric Strength	500 VDC min., 1 minute
6	Capacitance	5 pF max.
7	Conductive Rate:	96% min.

● RELIABLE TEST ITEMS

Reliable Test for RBS200124

	Test Item	Contents
1	Operating Temperature	-25°C ~ 85°C
2	Storage Temperature	-40°C ~ 85°C
3	Humidity	40 °C / 95 %RH
4	Mechanical Life	2 Hz horizontal 1,000,000 times
5	Electrical Life	100,000 times



TILT SENSOR SWITCH

Item No.	RBS200124	Description	Ball-Contact	Version	14
Page	4 of 5		Publish Date	May 29, 2018	

● SOLDERING CONDITION

Following soldering conditions are for reference only, please use soldering information that solder paste manufacturer recommends.

Condition Suitable Production Process	Soldering Temperature	Soldering Time	Wattage of Manual Soldering	Type
Wave Soldering	260±5°C	< 5 seconds max.	-	DIP
Manual Soldering	300±5°C	< 3 seconds max.	30W or Temperature- controlled manual soldering	DIP

● PACKAGE

	Part Number	Package	Quantity	Total Quantity	Dimension(mm)
1.	RBS200124	PE bag	500 pcs	500 pcs	127L*178W
		Inner box	10 PE bags	5,000 pcs	348L*191W*85H
		Carton	3 Boxes	15,000 pcs	364L*278W*213H

※ Package shown as below for reference.



PE bag



Inner box



Carton



TILT SENSOR SWITCH

Item No.	RBS200124	Description	Ball-Contact	Version	14
Page	5 of 5		Publish Date	May 29, 2018	

● NOTES

1. Suggestion for usage: For vibration usage or application, we suggest to add hysteresis for IC; if vibration is heavy, optical type of sensor switch is recommended.
2. For the continued product improvement as one of the company policy, specifications may change or update without notice. The latest information can be obtained through our sales offices. Normally, all products are supplied under our standard conditions.
3. If buyer's products will stay in power supply for a long time which needs very high stability, optical sensor switch is strongly recommended.

● PRECAUTIONS FOR USE

1. If the products are intended to be used for other endurance equipment requiring higher safety and reliability such as life support system, space and aviation devices, disaster and safety system, it's necessary to make verification of conformity or contact us for the details before using.
2. Do not try to clean the switch with a solvent or similar substance after the soldering process.
3. Use water-soluble flux may damage the switch.
4. Please follow the soldering instruction accordingly, otherwise might lead to defective.
5. Do not use switch in the environment of high humidity, because such an environment may cause the leakage current between the terminals.
6. Please do not exceed the rated load as there will be a risk of disabling the product function.
7. In the circuit, switch should not be near or directly connected with the magnetic component solder joints (for example: relays, transformers, etc.).



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[OncQue:](#)

[RBS200124](#)