



## HVAC TRMS DIGITAL MULTIMETER WITH TEMPERATURE

# FLIR DM64™

The FLIR DM64 is the only multimeter HVAC technicians need, providing an unmatched feature set and high-quality measurements at an affordable price. This digital multimeter is easy to use and has been built to last, offering long term stability and robust build quality for field use. The DM64 is the right choice for professionals installing, inspecting and maintaining HVAC systems.

[www.flir.com/ProfessionalDMMs](http://www.flir.com/ProfessionalDMMs)



### EVERYTHING YOU NEED IN ONE TOOL

Rich feature is ideal for HVAC professionals

- Diagnose complex systems with high and low voltage measurement capabilities
- Assess temperatures up to 400°C (752°F) with Type-K thermocouple
- Test flame sensors with microamps feature
- Readily and precisely identify live wires with probe-contact voltage detection



### FAST, EFFICIENT INSPECTIONS

Designed to make your job easier

- Work quickly and comfortably thanks to user-friendly design, intuitive interface, and enhanced ergonomics
- Easily identify deviations from normal conditions by comparing new readings to stored data
- Navigate the meter's on-screen menu system easily



### TOUGH, STABLE, & HIGH-QUALITY

This all-in-one tool is built to last

- Swap batteries easily from the "no-tool" battery compartment
- Durable and drop-tested, with an IP40 ingress protection rating
- Safety rated to CAT IV-300V, CAT III-600V
- Rely on the protection of FLIR's Limited Lifetime warranty

## SPECIFICATIONS

Measurement	DM64	
True RMS	Yes	
	Range	Basic Accuracy
AC / DC Volts	600.0 V	±1% / 0.4%
AC / DC mV	600.0 mV	±1% / 0.4%
VFD AC Volts	600.0 V RMS	±1%
AC / DC LoZ V	600.0 V	±2.0%
AC / DC Amps	10.00 A	±1.5% / 1.0%
AC / DC mAmps	600.00 mA	±1.0% / 0.7%
AC / DC $\mu$ Amps	6000 $\mu$ A	±1.5% / 1.0%
Resistance	60.00 M $\Omega$	±0.9%
Capacitance	2000 $\mu$ F	±1.5%
Diode Test	3.000 V	±0.9%
Frequency Counter	5.00 kHz	±0.1%
Temperature, Type-K Thermocouple	-40.0 to 752.0°F -40.0 to 400.0°C	±1.0% + 2°F ±1.0% + 1°C
Additional Measurements		
Continuity Check	30 $\Omega$ and 480 $\Omega$	
Measuring Rate	5 samples per second	
Min/Max/Avg	Yes	
Relative Mode	Yes	
LoZ Mode	Yes	
Non-Contact Voltage Detection (NCV)	Yes	
Data Hold	Yes	

### General Information

Auto Power Off	Yes
Battery	2 AAA batteries
Drop Test	2 meters
IP Rating	IP40
Category Rating	CAT IV-300V, CAT III-600V
Size (H x W x L)	161 x 80 x 50 mm (6.3 x 3.2 x 2.0 in)
Weight	334 g (11.8 oz)
Warranty	Limited lifetime warranty

### Box Contents

DM64 multimeter, 2x AAA Alkaline batteries, silicone test leads, Type-K thermocouple, soft carrying case

### Ordering Information

### Order #

FLIR DM64 HVAC TRMS Digital Multimeter with Temperature 793950381649

For a complete list of available accessories, go to: [flir.com/store/instruments/testaccessories](http://flir.com/store/instruments/testaccessories)

Specifications are subject to change without notice. For the most up-to-date specs, go to [www.flir.com](http://www.flir.com)

#### CORPORATE HEADQUARTERS

FLIR Systems, Inc.  
27700 SW Parkway Ave.  
Wilsonville, OR 97070  
PH: +1 877.773.3547

#### NASHUA

FLIR Systems, Inc.  
9 Townsend West  
Nashua, NH 03063  
USA  
PH: +1 866.477.3687

#### LATIN AMERICA

FLIR Systems Brasil  
Av. Antonio Bardella, 320  
Sorocaba, SP 18085-852  
Brasil  
PH: +55 15 3238 7080

#### CANADA

FLIR Systems, Ltd.  
920 Sheldon Court  
Burlington, ON L7L 5K6  
Canada  
PH: +1 800.613.0507

[www.flir.com](http://www.flir.com)  
NASDAQ: FLIR

Equipment described herein is subject to US export regulations and may require a license prior to export. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2017 FLIR Systems, Inc. All rights reserved. 10/02/17

17-2489-INS-TAM



The World's Sixth Sense®

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[DM64](#) [DM64-NIST](#)