




BUILDING APPLICATIONS

FLIR EXX-SERIES™

The FLIR E75, E85, E95, and the entry-level E53 Advanced Thermal Imaging Cameras bring superior sensitivity and a true 42° field of view* together in a user-friendly, handheld platform. These cameras feature a vibrant 4" LCD that makes it easy to spot the subtle indications of building deficiencies and moisture intrusion. With built-in tools such as laser-assisted autofocus*, on-screen area measurement†, and Wi-Fi capability, the FLIR Exx-Series will help you quantify and document air leaks, moisture, and other building problems.

www.flir.com/Exx-Series



Find Hidden Deficiencies

Uncover hard-to-find building envelope deficiencies and moisture penetration

- Detects temperature differences down to 0.03°C for early identification of air leaks and moisture
- MSX® image enhancements add perspective to scenes, with edge detail on windows and doors
- The true 42° field of view* (FOV) standard lens allows for surveys of wide areas with a single lens
- Measure the area (m² or ft²) of moisture intrusion on screen† with data from laser-assisted autofocus*



Document Problems Quickly

Report problems in buildings for insurance claims, pre-insurance audits, and inspections

- Built-in voice annotation and customizable work folders makes finding and documenting problems easier and more efficient
- Connect over Wi-Fi to the FLIR Tools mobile app for faster reporting and sharing of images
- Append images with FLIR moisture meter data via the METERLiNK® connection
- Streamlined reporting features through FLIR Tools+ simplifies insurance claims and inspection paperwork



Inspect More Efficiently

FLIR designed all four Exx-Series cameras to make your work faster, safer, and more efficient

- Vibrant, 4" touchscreen with 160° viewing angle
- Comfort-designed handle and convenient buttons enable safe, one-handed operation
- Rugged, water-tight chassis and scratch-resistant Dragontrail™ cover glass
- Backed by FLIR's industry-leading 2-5-10 warranty

*E75, E85, E95 models
†E85, E95 models

SPECIFICATIONS

Features By Camera	E53	E75	E85	E95
IR Resolution	240 × 180 (43,200 pixels)	320 × 240 (76,800 pixels)	384 × 288 (110,592 pixels)	464 × 348 (161,472 pixels)
UltraMax®	—	307,200 pixels	442,368 pixels	645,888 pixels
Object Temperature Range	-20°C to 120°C (-4°F to 248°F) 0°C to 650°C (32°F to 1200°F)	-20°C to 120°C (-4°F to 248°F) 0°C to 650°C (32°F to 1200°F) Optional 300°C to 1000°C (572°F to 1830°F)	-20°C to 120°C (-4°F to 248°F) 0°C to 650°C (32°F to 1200°F) 300°C to 1200°C (572°F to 2192°F)	-20°C to 120°C (-4°F to 248°F) 0°C to 650°C (32°F to 1200°F) 300°C to 1500°C (572°F to 2732°F)
Focus	Manual	Continuous, one-shot laser distance meter (LDM), one-shot contrast, manual	Continuous, one-shot laser distance meter (LDM), one-shot contrast, manual	Continuous, one-shot laser distance meter (LDM), one-shot contrast, manual
Field of View (FOV)	24° × 18°	42° × 32° (10 mm lens), 24° × 18° (18 mm lens), 14° × 10° (29 mm lens)	42° × 32° (10 mm lens), 24° × 18° (18 mm lens), 14° × 10° (29 mm lens)	42° × 32° (10 mm lens), 24° × 18° (18 mm lens), 14° × 10° (29 mm lens)
Time-lapse (Infrared)	—	—	—	10 sec to 24 hours
Laser Area Measurement	—	—	Yes	Yes
Laser Distance Measurement	—	Yes, on-screen	Yes, on-screen	Yes, on-screen
Measurement Presets	No measurement, center spot, hot spot, cold spot, 3 spots, hot spot-spot ¹	No measurement, center spot, hot spot, cold spot, User Preset 1, User Preset 2	No measurement, center spot, hot spot, cold spot, User Preset 1, User Preset 2	No measurement, center spot, hot spot, cold spot, User Preset 1, User Preset 2
Spotmeter	3 in live mode	3 in live mode	3 in live mode	3 in live mode
Area	1 in live mode	1 in live mode	3 in live mode	3 in live mode
Picture-in-Picture	Centered infrared area on the visual image	Resizable and movable	Resizable and movable	Resizable and movable

Common Features

Detector Type and Pitch	Uncooled microbolometer, 17 µm
Thermal Sensitivity (NETD)	<0.04°C @ 30°C (86°F), 24° lens
Spectral Range	7.5 - 14.0 µm
Image Frequency	30 Hz
F-Number	f/1.3
Lens Identification	Automatic
Digital Zoom	1-4x continuous

Image Presentation and Modes

Display	4", 640 × 480 pixel touch screen LCD with auto-rotation
Digital Camera	5 MP, 53° × 41° FOV
Color Palettes	Iron, Gray, Rainbow, Arctic, Lava, Rainbow HC
Image Modes	Infrared, visual, MSX®, Picture-in-Picture
MSX®	Embosses visual details on full resolution thermal image

Measurement and Analysis

Accuracy	±2°C (±3.6°F) or ±2% of reading for ambient temperature 15°C to 35°C (59°F to 95°F) and object temperature above 0°C (32°F)
Alarms	Moisture alarm, insulation alarm, measurement alarms
Color Alarm (Isotherm)	Above/below/interval/condensation/insulation
Compass, GPS	Yes; automatic GPS image tagging
METERLINK®	Yes; several readings
Laser Pointer	Yes; dedicated button

¹Hot spot to center spot Delta measurement

Specifications are subject to change without notice.
For the most up-to-date specs, go to www.flir.com

Image Storage

Storage Media	Removable SD card (8 GB)
Image File Format	Standard JPEG with measurement data included

Video Recording and Streaming

Radiometric IR Video Recording	Real-time radiometric recording (.csq)
Non-Radiometric IR or Visual Video	H.264 to memory card
Radiometric IR Video Streaming	Yes, over UVC or Wi-Fi
Non-Radiometric IR Video Streaming	H.264 or MPEG-4 over Wi-Fi; MJPEG over UVC or Wi-Fi
Communication Interfaces	USB 2.0, Bluetooth, Wi-Fi, DisplayPort
Video Out	DisplayPort over USB Type-C

Additional Data

Battery Type	Li-ion battery, charged in camera or on separate charger
Battery Operating Time	Approx. 2.5 hours at 25°C (77°F) ambient temperature and typical use
Operating Temperature Range	-15°C to 50°C (5°F to 122°F)
Storage Temperature Range	-40°C to 70°C (-40°F to 158°F)
Shock/Vibration/Encapsulation/Safety	25 g / IEC 60068-2-27, 2 g / IEC 60068-2-6, IP 54 / IEC 60529; EN/UL/CSA/PSE 60950-1
Weight/Dimensions	1 kg (2.2 lbs), 27.8 × 11.6 × 11.3 cm (11.0 × 4.6 × 4.4 in)

Box Contents

Infrared camera with lens, battery (2 ea), battery charger, front protection, straps (hand, wrist), hard transport case, lanyards, lens caps, lens cleaning cloth, power supplies, 8 GB SD card, Torx wrench, cables (USB 2.0 A to USB Type-C, USB Type-C to USB Type-C, USB Type-C to HDMI)

CORPORATE HEADQUARTERS
FLIR Systems, Inc.
27700 SW Parkway Ave.
Wilsonville, OR 97070
USA
PH: +1 877.773.3547

NASHUA
FLIR Systems, Inc.
9 Townsend West
Nashua, NH 03063
USA
PH: +1 866.477.3687

CANADA
FLIR Systems, Ltd.
3430 South Service Road
Suite 103
Burlington, ON L7N 3T9
Canada
PH: +1 800.613.0507

LATIN AMERICA
FLIR Systems Brasil
Av. Antonio Bardella, 320
Sorocaba, SP 18085-852
Brasil
PH: +55 15 3238 8070

www.flir.com
NASDAQ: FLIR

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2019 FLIR Systems, Inc. All rights reserved. (02/19)

19-0546-INS-Exx BLD



The World's Sixth Sense®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Teledyne FLIR:](#)

[FLIR E75-24-14-NIST](#) [FLIR E75-24-42-KIT](#) [FLIR E75-24-42-NIST](#) [FLIR E85-24-14-42-KIT](#) [FLIR E85-24-14-42-NIST](#)
[FLIR E85-24-14-KIT](#) [FLIR E85-14](#) [FLIR E95-24-14-NIST](#) [FLIR E95-24-42-KIT](#) [FLIR E95-24-42-NIST](#) [FLIR E75-24-14-42-KIT](#) [FLIR E75-24-14-42-NIST](#) [FLIR E75-24-14-KIT](#) [FLIR E85-24-14-NIST](#) [FLIR E85-24-42-KIT](#) [FLIR E85-24-42-NIST](#) [FLIR E95-24-14-42-KIT](#) [FLIR E95-24-14-42-NIST](#) [FLIR E95-24-14-KIT](#)