

P/N: T199163

Copyright

© 2015, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T199163

Release:

Commit: 28462

Language: en-US

Modified: 2015-09-15

Formatted: 2015-10-17

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description

Front mounting plate kit for mounting a FLIR AX8 camera. Includes cooling bracket.



Physical data

Shipping information

Packaging, type	Cardboard box
List of contents	• Front mounting plate • Cooling bracket • Screws
Packaging, weight	0.269 kg (0.59 lb.)
Packaging, size	183 × 136 × 63 mm (7.2 × 5.4 × 2.5 in.)
EAN-13	4743254002135
UPC-12	845188011659
Country of origin	Sweden
	x


Compatible with the following products

- 71201-0101; FLIR AX8 9 Hz



SECTION A-A

Konstr/Drawn J. MÄKINEN	Datum/Date 2015-03-06	Kontr/Check HAOS	Material EN AW-5052 or EN AW-5754	
Ändrad av/Modified by J. MÄKINEN	Ändrad/Modified 2015-05-21	Ytjämnhet/Roughness Ra µm	Ytbehandling/Surface treatment	
Där ej annat anges/Unless otherwise stated Gen tol ISO 2768-mK Utdrag ur/Excerpt from ISO 2768-m	Benämning/Denomination Plate mounting front			Skala/Scale 1:1
0,5-6 ±0,1 Hålkälsradier (6)-30 ±0,2 Fillet radii (30)-120 ±0,3				Art.No.
			Ritn nr/Drawing No	Blad/Sheet 1(1)
				Size A4
				Rev



Keiser/Drawn P. MARCUS	2014-09-18	Kontr./Check JAWA	Material EN AW-6262 R
Art./id. n°/Modified by P. MARCUS	Art./id. Modified 2015-03-10	Yigmaned/Roughness Ra 3.2 µm	Yigmaned/Surface treatment Anodized colorless matt
Bracket cooling			
Detail of art. angles/Unless otherwise stated Gen to ISO 2768-mK	Tolerances/Denomination		
Ultragut/except from ISO 2768-m			
0.5-6 (6A-30)	0.1-0.3		
±0.1			
Halsradler			
Fillet radii			
±0.2			
±0.3			
Kenter burina			
(120-400)			
±0.5			
(400)-1000			
Edges broken			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Teledyne FLIR:](#)

[T199163](#)