


### Surface Mount Termination 8 Watts, 50Ω



#### Description

The 060120A15Z50-2 is high performance Alumina ( $Al_2O_3$ ) Surface Mount termination intended as a low cost alternative to Aluminum Nitride (AlN). The termination is well suited to all cellular frequency bands such as; AMPS, GSM, DCS, PCS, PHS and UMTS. The termination is also RoHS compliant!

#### General Specifications

<b>Resistive Element</b>	Thick film
<b>Substrate</b>	$Al_2O_3$ Ceramic
<b>Terminal Finish</b>	Matte Tin over Nickel Barrier
<b>Operating Temperature</b>	-55 to +125°C (see de rating chart)

Tolerance is  $\pm 0.010"$ , unless otherwise specified. Designed to meet or exceed applicable portions of MIL-E-5400. **All dimensions in inches.**

#### Electrical Specifications


<b>Resistance Value:</b>	50 Ohms, $\pm 2\%$
<b>Power:</b>	8 Watts
<b>Frequency Range:</b>	DC – 6.0 GHz
<b>Return Loss</b>	>19 dB

Specification based on unit properly installed using suggested mounting instructions and a 50 ohm nominal impedance. **Specifications subject to change.**



#### Features:

- RoHS Compliant
- 8 Watts
- DC – 6.0 GHz
- $Al_2O_3$  Ceramic
- Non-Nichrome Resistive Element
- Low VSWR
- 100% Tested
- Small Size


#### Outline Drawing




**Typical Performance:**




**Power De-rating:**



**Mounting Footprint and Procedure:**



**Tape and Reel:**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Anaren:](#)

[060120A15Z50-2](#)