

APPROVAL SHEET

PCB ANTENNA

863~870 MHz Working Frequency

Halogens Free Product

P/N: RFPCA791010IMRB301

Customer : _____
Customer 's Part No. : _____
Approval No. : _____
Issue Date : _____

*Contents in this sheet are subject to change without prior notice.

Version	Date	Description	Author
V01	2017 Jun.	New Release	SHLEE
V02	2017 Jun.	變更 Layout	SHLEE

Approval sheet
ELECTRICAL CHARACTERISTICS

Item	Specification
Working Frequency Range	863~870 MHz(Note-1)
Return Loss	-10 dB(Max)
Gain(peak)	-
VSWR	< 2.0
Impedance	50 Ohm Nominal
Radiation	Omni-directional
Polarization	Linear Vertical

*Note 1. Central Frequency should be defined after customers' application approval.

MATERIAL TABLE

Items	Description
Antenna	PCB FR4 T=0.4mm(黑漆板)
Double Tape	3M9888T
Cable	Ø1.13 Cable (Black)
Connector	IPEX (Gold)

ORDERING RULE


RF	PCA	7910	10	I	M	R	B	3	01
Type Code	Product Code	PCB Dimension (Unit: mm)	Cable Length (unit: cm)	Connector Brand	Type of Connector	Application	Project status	Wire Diameter	Project
Walsin RF Device	PCB Antenna	Per 2 digits of length, width e.g.: 4006 Length 40.5mm, Width 6mm	2 digits for cable length e.g.: 22 Length 22cm	A: N C: MCX D: IPEX III E: IPEX IV F: IPEX A13 H: Hirose I: IPEX M: MMCX S: SMA T: TNC U: MURATA N: None	A: Reverse Female B: Reverse Male F: Female M: Male N: None	0: 0GHz 3: 3GHz 5: 5GHz 6: 6GHz A: 2.4GHz ISM band B: GSM 900/1800 dual band G: GPS band L: 2.4/5.2/5.8 GHz tri-band N: NFC R: RFID T: LTE band W: WCDMA band	B: MP T: During Test X: Pile Run	0: None 1: Ø 0.81 2: Ø 1.32 3: Ø 1.13 4: Low Loss Ø 1.13 5: Ø 0.5 6: RG316 7: Ø 1.37 8: RG178 9: Low Loss Ø 1.37	01~99 series number

Dimensions


ELECTRICAL

Frequency : 863~870 MHz

NO	DESCRIPTION	QTY	REMARK
A	Body	1	PCB FR4(T=0.4mm),Black
B	Double Tape	1	3M9888T
C	Coaxial cable	1	($\phi 1.13$)(Black)
D	Connector	1	IPEX (Gold)



A - center conductor
B - Dielectric
C - Outer conductor
D - Jacket



IPEX方向:
100mm : $\pm 90^\circ$
200mm : $\pm 135^\circ$
200mm以上不管控

※標記□記號者, 為重點檢驗尺寸

設計 DR. SHLEE		2017.06.20		品名		版本 REV.	
核准 APP. Marco				ARTICLE		B	
變更Layout		2017.06.28 SHLEE		容許公差 TOLERANCE		RFPCA791010IMRB301	
LTR DESCRIPTION		DATE REQ. BY		6以下..... ± 0.2		單位 UNIT	
				6以上~30..... ± 0.5		比例 SCALE	
				30以上~120..... ± 0.8		張數 SHEET	
				120以上~315..... ± 1.2		1	
				315以上~1000..... ± 2.0		mm	
				1000以上~2000..... ± 3.0		****	



華新科技股份有限公司
Walsin Technology Corporation

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Walsin:](#)

[RFPCA791010IMRB301](#)