

# Specification

(Reference)

Title: FIXED THIN FILM CHIP RESISTORS;  
RECTANGULAR TYPE

Style: RNC06, 20, 32

RoHS COMPLIANCE ITEM
Halogen and Antimony Free

Product specification contained in this specification  
are subject to change at any time without notice  
If you have any questions or a Purchasing Specification for any quality  
Agreement is necessary, please contact our sales staff.



**釜屋電機株式會社**  
**KAMAYA ELECTRIC CO., LTD.**

Issue Dept.: Research & Development Department Hokkaido Research Center

1. Scope


1.1 This specification covers the detail requirements for fixed thin film chip resistors; rectangular type & precision, style of RNC06, 20, 32.

1.2 Applicable documents

- JIS C 5201-1: 1998, JIS C 5201-8: 1998, JIS C 5201-8-1: 1998
- IEC60115-1: 1999, IEC60115-8: 1989 Amendment 1: 1992, IEC60115-8-1: 1989
- EIAJ RC-2133B-2002

2. Classification

Type designation shall be the following form.



- 1 Fixed thin film chip resistors; rectangular type Style
- 2 Size
- 3 Temperature coefficient of resistance
 

E	±25×10 <sup>-6</sup> /°C
C	±50×10 <sup>-6</sup> /°C
- 4 Rated resistance Example; 1002 → 10kΩ
- 5 Tolerance on rated resistance
- 6 Packaging form

3. Rating

3.1 The ratings shall be in accordance with Table-1.

Table-1

Style	Rated dissipation (W)	Temperature coefficient of resistance (10 <sup>-6</sup> /°C)	Rated resistance range(Ω)	Preferred number series for resistors	Tolerance on rated resistance
RNC06	0.03	E: ±25	100~10k	E24,96	B(±0.1%)
	0.05	E: ±25	27~4.99k		D(±0.5%)
		C: ±50	5.1k~10k		B(±0.1%)
RNC20	0.1	E: ±25	100~130k		C(±0.25%), D(±0.5%)
			10~130k		B(±0.1%)
RNC32	0.125		100~180k		C(±0.25%), D(±0.5%)
			10~180k		

Style	Limiting element voltage (V)	Isolation Voltage (V)	Category temperature range(°C)
RNC06	15	50	-55~+155
RNC20	100	100	
RNC32	200		

3.2 Climatic category

55/125/56	Lower category temperature	-55 °C
	Upper category temperature	+155 °C
	Duration of the damp heat, steady state test	56days

3.3 Stability class

1%	Limits for change of resistance:	
	– for long - term tests	±(1.0%+0.05Ω)
	– for short - term tests	±(0.25%+0.05Ω)

3.4 Derating

The derated values of dissipation at temperature in excess of 70°C shall be as indicated by the following curve.




Figure-1 Derating curve

3.5 Rated voltage

d.c.or a.c.r.m.s.voltage calculated from the square root of the product of the rated resistance and the rated dissipation.

$$E = \sqrt{P \cdot R}$$

- E: Rated voltage (V)
- P: Rated dissipation (W)
- R: Rated resistance (Ω)

Limiting element voltage can only be applied to resistors when the resistance value is equal to or higher than the critical resistance value.

At high value of resistance, the rated voltage may not be applicable.

4. Packaging form

The standard packaging form shall be in accordance with Table-2.

Table-2

Symbol	Packaging form		Standard packaging quantity / units	Application
B	Bulk (loose package)		1,000 pcs.	RNC06, 20, 32
PA	Press pocket taping (paper taping)	8mm width, 2mm pitches	15,000 pcs.	RNC06
TP	Paper taping	8mm width, 4mm pitches	5,000 pcs.	RNC20, 32

5. Dimensions

5.1 The resistor shall be of the design and physical dimensions in accordance with Figure-2 and Table-3.




Figure-2

Table-3

Unit: mm

Style	L	W	H	c	d
RNC06	0.6±0.03	0.3±0.03	0.23±0.03	0.1±0.05	0.15±0.05
RNC20	2.0±0.15	1.25 <sup>+0.10</sup> <sub>-0.05</sub>	0.6±0.1	0.4±0.2	0.3 <sup>+0.2</sup> <sub>-0.1</sub>
RNC32	3.1±0.1	1.55 <sup>+0.10</sup> <sub>-0.05</sub>	0.6±0.1	0.45±0.20	0.3 <sup>+0.2</sup> <sub>-0.1</sub>

5.2 Net weight (Reference)

Style	Net weight(mg)
RNC06	0.16
RNC20	5
RNC32	9

6. Marking

The Rated resistance shall be marked in 3 digits (E24) or 4 digits (E96) and marked on over coat side.

The Rated resistance of RNC06 should not be marked.

(Example)

“123” → 12 × 10<sup>3</sup> [Ω] → 12 [kΩ]

“3R3” → 3.3 [Ω]

“5623” → 562 × 10<sup>3</sup> [Ω] → 562 [kΩ]

7. Performance

7.1 The standard condition for tests shall be in accordance with Sub-clause 4.2, JIS C 5201-1: 1998.

7.2 The performance shall be satisfied in Table-4.

Table-4(1)

No.	Test items	Condition of test (JIS C 5201-1)	Performance requirements
1	Visual examination	Sub-clause 4.4.1 Checked by visual examination.	As in 4.4.1 The marking shall be legible, as checked by visual examination.
2	Dimension  Resistance	Sub-clause 4.4.2  Sub-clause 4.5	As specified in Table-3 of this specification. As in 4.5.2 The resistance value shall correspond with the rated resistance taking into account the specified tolerance.
3	Voltage proof	Sub-clause 4.7 Method: 4.6.1.4(See Figure-5) Test voltage: Alternating voltage with a peak value of 1.42 times the insulation voltage. Duration: 60 s ± 5 s Insulation resistance Test voltage: Insulation voltage Duration: 1 min.	No breakdown or flash over     R ≥ 1 G Ω
4	Solderability	Sub-clause 4.17 Without ageing Flux: The resistors shall be immersed in a non-activated soldering flux for 2s. Bath temperature: 235 °C ± 5 °C Immersion time: 2 s ± 0.5 s	As in 4.17.4.5 The terminations shall be covered with a smooth and bright solder coating.
5	Mounting  Overload (in the mounted state)  Solvent resistance of the marking	Sub-clause 4.31 Substrate material: Epoxide woven glass Test substrate: Figure-3 Sub-clause 4.13 The applied voltage shall be 2.5 times the rated voltage or twice the limiting element voltage, whichever is the less severe. Duration: 2 s Visual examination Resistance Sub-clause 4.30 Solvent: 2-propanol Solvent temperature: 23 °C ± 5 °C Method 1 Rubbing material: cotton wool Without recovery	No visible damage ΔR ≤ ± (0.25%+0.05Ω) Legible marking

Table-4(2)

No	Test items	Condition of test (JIS C 5201-1)	Performance requirements
6	Mounting  Bound strength of the end face plating  Final measurements	Sub-clause 4.31 Substrate material: Epoxide woven glass Test substrate: Figure-4 Sub-clause 4.33 Bent value: 3 mm Resistance Sub-clause 4.33.6 Visual examination	$\Delta R \leq \pm (0.25\%+0.05\Omega)$  No visible damage
7	Resistance to soldering heat    Component solvent resistance	Sub-clause 4.18 Solder temperature: 260 °C ± 5 °C Immersion time: 10 s ± 0.5 s Visual examination  Resistance Sub-clause 4.29 Solvent: 2-propanol Solvent temperature: 23 °C ± 5 °C Method 2 Recovery: 48 h Visual examination Resistance	As in 4.18.3.4 No sign of damage such as cracks. $\Delta R \leq \pm (0.25\%+0.05\Omega)$  No visible damage $\Delta R \leq \pm (0.25\%+0.05\Omega)$
8	Mounting  Adhesion   Rapid change temperature	Sub-clause 4.31 Substrate material: Epoxide woven glass Test substrate: Figure-3 Sub-clause 4.32 Force: 5 N (RNC06: 3N) Duration: 10 s ± 1 s Visual examination Sub-clause 4.19 Lower category temperature: -55 °C Upper category temperature: +155 °C Duration of exposure at each temperature: 30 min. Number of cycles: 5 cycles. Visual examination Resistance	No visible damage      No visible damage $\Delta R \leq \pm(0.25\%+0.05\Omega)$

Table-4(3)


No	Test items	Condition of test (JIS C 5201-1)	Performance requirements
9	Climatic sequence -Dry heat  -Damp heat, cycle (12+12hour cycle) First cycle  -Cold  -Damp heat, cycle (12+12hour cycle) Remaining cycle  -D.C. load	Sub-clause 4.23 Sub-clause 4.23.2 Test temperature: + 155 °C Duration: 16 h  Sub-clause 4.23.3 Test method: 2 Test temperature: 55 °C [Severity(2)] Sub-clause 4.23.4 Test temperature -55 °C Duration: 2h  Sub-clause 4.23.6 Test method: 2 Test temperature: 55 °C [Severity (2)] Number of cycles: 5 cycles Sub-clause 4.23.7 The applied voltage shall be the rated voltage or the limiting element voltage whichever is the smaller. Duration: 1 min. Visual examination Resistance	No visible damage $\Delta R \leq \pm (1\%+0.05\Omega)$
10	Mounting  Endurance at 70 °C	Sub-clause 4.31 Substrate material: Epoxide woven glass Test substrate: Figure-3 Sub-clause 4.25.1 Ambient temperature: 70 °C ± 2 °C Duration: 1000 h The voltage shall be applied in cycles of 1.5 h on and 0.5 h. The applied voltage shall be the rated voltage or the limiting element voltage whichever is the smaller. Examination at 48 h, 500 h and 1000 h: Visual examination Resistance	No visible damage $\Delta R \leq \pm (1\%+0.05\Omega)$

Table-4(4)

No	Test items	Condition of test (JIS C 5201-1)	Performance requirements
11	Mounting  Variation of resistance with temperature	Sub-clause 4.31 Substrate material: Epoxide woven glass Test substrate: Figure-3 Sub-clause 4.8 +20 °C / +125°C	As in Table-1
12	Mounting  Damp heat, steady state	Sub-clause 4.31 Substrate material: Epoxide woven glass Test substrate: Figure-3 Sub-clause 4.24 Ambient temperature: 40 °C ± 2 °C Relative humidity : 93 $\pm$ <sub>3</sub> <sup>2</sup> % a) 1st group: without voltage applied. b) 2nd group: The d.c.voltage shall be applied continuously. The voltage shall be accordance with Sub-clause 4.24.2.1 b). without polarizing voltage [4.24.2.1, c)] Visual examination  Resistance	No visible damage Legible marking $\Delta R \leq \pm (1\%+0.05\Omega)$
13	Dimensions (detail)  Mounting  Endurance at upper category temperature	Sub-clause 4.4.3  Sub-clause 4.31 Substrate material: Epoxide woven glass Test substrate: Figure-3 Sub-clause 4.25.3 Ambient temperature: 155 °C ± 2 °C Duration: 1000 h Examination at 48 h, 500 h and 1000 h: Visual examination  Resistance	As in Table-3       No visible damage $\Delta R \leq \pm (1\%+0.05\Omega)$




8. Test substrate



Unit: mm

□ :Copper clad  
■ :Solder resist

RNC32 TEST SUBSTRATE



Unit: mm


□ :Copper clad  
■ :Solder resist

Style	a	b	c	d
RNC06	0.3	1.5	0.45	5.2
RNC20	1.2	4.0	1.5	4.3

RNC06, 20 TEST SUBSTRATE

Figure-3

- Remark 1). Material: Epoxide woven glass  
Thickness: 1.6mm Thickness of copper clad: 0.035mm
- 2). In the case of connection by connector, the connecting terminals are gold plated.  
However, the plating is not necessary when the connection is made by soldering.



Unit: mm

□ :Copper clad  
■ :Solder resist

Style	a	b	c	d
RNC06	0.3	1.1	0.45	2.15
RNC20	1.2	4.0	1.65	3.0
RNC32	2.5	5.0	2.0	2.5

RNC BOUND STRENGTH OF THE END FACE PLATING TEST TEST SUBSTRATE

Figure-4

Remark 1). Material: Epoxide woven glass

Thickness: 1.6mm Thickness of copper clad: 0.035mm





Figure-5

9. Taping

9.1 Applicable documents JIS C 0806-3: 1999, EIAJ ET-7103: 2004, EIAJ ET-7200B: 2003

9.2 Taping dimensions

9.2.1 Press pocket taping (Paper taping, 8mm width, 2mm pitches)

Taping dimensions shall be in accordance with Figure-6 and Table-5.




Figure-6

Table-5

Style	A	B	$t_1$	$t_2$	$t_3$
RNC06	$0.37 \pm 0.05$	$0.67 \pm 0.05$	$0.42 \pm 0.03$	$0.45 \pm 0.05$	$0.27 \pm 0.02$

9.2.2 Paper taping (8mm width, 4mm pitches)

Taping dimensions shall be in accordance with Figure-7 and Table-6.




Figure-7

Table-6

Style	A	B	$t_1$	$t_2$
RNC20	$1.65 \pm 0.15$	$2.5 \pm 0.2$	$0.8 \pm 0.1$	1.0max.
RNC32	$2.00 \pm 0.15$	$3.6 \pm 0.2$		

- 1). The cover tapes shall not cover the sprocket holes.
- 2). Tapes in adjacent layers shall not stick together in the packing.
- 3). Components shall not stick to the carrier tape or to the cover tape.
- 4). Pitch tolerance over any 10 pitches  $\pm 0.2\text{mm}$ .
- 5). The peel strength of the top cover tape shall be with in 0.1N to 0.5N on the test method as shown in the following RNC06: Figure-8, RNC20, 32: Figure-9.
- 6). When the tape is bent with the minimum radius for 25 mm, the tape shall not be damaged and the components shall maintain their position and orientation in the tape.
- 7). In no case shall there be two or more consecutive components missing.  
The maximum number of missing components shall be one or 0.1%, whichever is greater.
- 8). The resistors shall be faced to upward at the over coating side in the carrier cavity.




Figure-8




Figure-9

9.3 Reel dimension

Reel dimensions shall be in accordance with the following Figure-10 and Table-7.

Plastic reel (Based on EIAJ ET-7200B)

Unit: mm




Figure-10

Table-7

Unit: mm

Style	A	B	Note
RNC06, 20, 32	9 $\begin{smallmatrix} +1.0 \\ 0 \end{smallmatrix}$	11.4 ± 1.0	Injection molding
		13 ± 1.0	Vacuum forming

Note: Marking label shall be marked on a place of Marking A or two place of marking A and B.

9.4 Leader and trailer tape.

(Example)




Figure-11

10. Marking on package

The label of a minimum package shall be legibly marked with follows.

10.1 Marking A

(1) Classification

(Style, Temperature coefficient of resistance, Rated resistance, Tolerance on rated resistance, Packaging form)

(2) Quantity (3) Lot number (4) Manufacturer's name or trade mark (5) Others

10.2 Marking B (KAMAYA Control label)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Kamaya:

[RNC20E1372BTP](#) [RNC32E823BTP](#) [RNC32E1001BTP](#) [RNC20E682DTP](#) [RNC20E1001BTP](#) [RNC32E2002BTP](#)  
[RNC20E241BTP](#) [RNC20E1431BTP](#) [RNC20E2492BTP](#) [RNC20E2002BTP](#) [RNC32E272BTP](#) [RNC20E1501BTP](#)  
[RNC20E1000BTP](#) [RNC20E21R5DTP](#) [RNC20E7502BTP](#) [RNC32E513BTP](#) [RNC32E2550BTP](#) [RNC20E1003BTP](#)  
[RNC20E1241BTP](#) [RNC20E2152BTP](#) [RNC32E7502BTP](#) [RNC20E2002DTP](#) [RNC32E3010BTP](#) [RNC20E21R0DTP](#)  
[RNC20E1002BTP](#) [RNC20E5111BTP](#) [RNC06E512BPA](#) [RNC20E1331BTP](#) [RNC32E124BTP](#) [RNC32E3012BTP](#)  
[RNC20E4020BTP](#) [RNC20E152DTP](#) [RNC32E6192BTP](#) [RNC32E2701BTP](#) [RNC20E2400BTP](#) [RNC32E8202BTP](#)  
[RNC20E1501DTP](#) [RNC32E1203BTP](#) [RNC06E5101BPA](#) [RNC20E6801DTP](#) [RNC32E5102BTP](#) [RNC20C1132FT](#)