

Technical drawing of a reel of tape, showing top and side views with dimensions.

Top View Dimensions:

- REEL DIA. REF. (Reference diameter)
- FEED DIRECTION (Arrow pointing right)
- .500 [12.7] DIA. HOLE THRU (Hole diameter)
- $\pm .005$ [± 0.13] (Tolerance for hole position)
- .157 [4.0] (Hole spacing)
- $\pm .005$ [± 0.13] (Tolerance for hole position)
- PITCH (Hole pitch)
- $\pm .005$ [± 0.13] (Tolerance for hole position)
- .059 [1.5] DIA. HOLE (TYP.) (Typical hole diameter)
- .079 [2.0] (Hole diameter)
- .413 [10.5] REF. (Reference dimension)

Side View Dimensions:

- WIDTH (Tape width)
- $\pm .005$ [± 0.13] (Tolerance for width)
- .787 [20.0] (Tape thickness)
- .016 [0.4] REF. (Reference dimension)
- FEED DIRECTION (Arrow pointing right)

NOTES:

TAPE AND REEL SPECIFICATIONS:

1. TAPE:

MAT'L - ALL CONDUCTIVE POLYSTYRENE CARRIER

ANSI/EIA-481 STANDARD

1.732 [44.0] WIDE; 1.260 [32.0] PITCH

2. REEL:

13.0 [330.2] DIA. 200 PIECES OF

PART NO. 1062 PER REEL.

6.19.07	CHANGE AS PER ECN 07-037	A
DATE	DESCRIPTION	REV.

<h1>KEYSTONE ELECTRONICS CORP.</h1> <p>www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900</p>			
PART NAME <h2>20mm SM COIN CELL HOLDER ON TAPE</h2>			
MATERIAL <h2>AS NOTED</h2>			
FINISH <h2>AS NOTED</h2>		DRN BY <h2>BOONE</h2>	DATE <h2>5.8.00</h2>
		APP'D <h2>LN</h2>	SCALE <h2>X</h2>
TOLERANCES INCH [MM] DECIMAL $\pm .015$ [± 0.38] ANGULAR $\pm 1^\circ$ UNLESS OTHERWISE SPECIFIED	CODE <h2>C</h2>	DWG NO. <h1>1062TR</h1>	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[1062TR](#)